



Micro Commercial Components
20736 Marilla Street Chatsworth
CA 91311
Phone: (818) 701-4933
Fax: (818) 701-4939

MC79L05F

Features

- Internal Short Circuit Current Limiting
- Internal Thermal Overload Protection
- No External Components Required

Absolute Maximum Ratings


Parameter	Symbol	Value	Unit
Input Voltage	V_1	30	V
Operating Junction Temperature	T_{OPR}	-30---+75	°C
Storage Temperature Range	T_{STG}	-40---+125	°C

**Electrical Characteristics($V_i=10V$, $I_o=40mA$, $0^\circ C < T_j < 125^\circ C$,
 $C_1=0.33\mu F$, $C_o=0.1\mu F$, unless otherwise specified)**

Parameter	Sym	Min	Typ	Max	Test conditions
Output Voltage	V_o	4.8V	5.0V	5.2V	$V_i=10V$, $I_o=40mA$
Load Regulation	$V_o - I_o$		7.0mV	60mV	$I_o=1mA-100mA$, $V_i=10V$
Line regulation	$V_o - V_i$		15mV	150mV	$7V \leq V_i \leq 20V$, $I_o=40mA$
Quiescent Current	I_q		3.5mA	6.0mA	$V_i=10V$, $I_o=40mA$
Output Noise Voltage	V_N		120 μV		10Hz $\leq f \leq$ 100KHz $V_i=10V$, $I_o=40mA$
Ripple Rejection	RR	41dB	71dB		$8V \leq V_i \leq 18V$, $I_o=40mA$ $f=120Hz$, $T_j=25^\circ C$ $e_{IN}=1V_{P-P}$


*Note: Bypass Capacitors are recommended for optimum stability and transient response and should be located as close as possible to the regulators

Typical Application:



Three-Terminal Low Current Negative Voltage Regulator

SOT-89



1. OUT
2. GND
3. IN

DIMENSINS					
DIM	INCHES		MM		NOTES
	MIN	MAX	MIN	MAX	
A	.173	.181	4.39	4.60	
B	.063	.071	1.60	1.80	
C	.154	.165	3.91	4.19	
D	.031	.039	0.80	1.00	
E	.092	.100	2.34	2.54	
F	.118	----	3.00	----	TYP
G	.013	.019	0.33	0.48	
H	.015	.021	0.38	0.53	
J	.015	.016	0.38	0.41	
K	.055	.063	1.40	1.60	