

**ARC LS-10167**  
***Lossy Foam***

**Description:** Flexible, low density, moderate to low loss, carbon impregnated polyurethane foam, LS-20/22 series.

**Standard Thickness:** 0.250" (6.35mm)

**Standard Sheet Size:** 24" x 24" (60.96 x 60.96cm)

**Resistance:** 800-1,000 ohms/sq

**Color:** Black

**Temp. Range:** -70°F to + 250°F (-56.7°C to 121.1°C)

**Features:**

- PSA: A high performance unsupported acrylic transfer film adhesive may be bonded to the back side. PSA thickness is .002" (0.05mm)
- Ground Film: Conductive Mylar when specified

**Typical Insertion Loss: 4.5 dB at 10GHz**

The technical information contained herein is consistent with the properties of this material but should not be used in the preparation of specifications as it is intended for reference only.



***Solutions for Interference Control***

ARC Technologies, Inc.  
11 Chestnut Street, Amesbury, MA 01913  
978-388-2993 Fax: 978-388-6866  
[www.arc-tech.com](http://www.arc-tech.com)