

THIS DRAWING IS UNPUBLISHED.


RELEASED FOR PUBLICATION, 19

© COPYRIGHT 19



BY AMP INCORPORATED. ALL INTERNATIONAL RIGHTS RESERVED.

LOC	DIST	P	F	REVISIONS				
				ZONE	LTR	DESCRIPTION	DATE	APPD
CH	11				D	EC 0B20-0791-98	30/JUN/98	DAP
				C	EC 0B20-0671-98	27/MAY/98	RNP	
				B	ECN 95013002	01-30-95	CMS	

1. MATERIAL: COPPER ALLOY
2. FINISH: 30 MICROINCHES MIN. GOLD OVER 50 MICROINCHES MIN. NICKEL.
3. WIRE BARREL WILL ACCEPT #8 AWG WIRE
4. MATES WITH AMP P/N 193991-X.
5. FINISH: 200 MICROINCHES MIN. SILVER OVER 40 MICROINCHES MIN. NICKEL.
6. ALL DIMENSIONS ARE REFERENCE ONLY.



RETENTION CLIP
MATERIAL: STAINLESS STEEL



OBSOLETE	5	193990-2
	2	193990-1
FINISH		PART NO

DO NOT SCALE PRINT. UNLESS SPECIFIED DIMENSIONS IN mm [INCHES] TOLERANCES ON: 2 PLC DEC ± - 3 PLC DEC ± - ANGLES ± -	DR 04-13-94 D.A.P.	AMP AMP Incorporated Harrisburg, PA 17105-3608	
	CHK -		
	APPD -	NAME SOCKET ASSEMBLY, TYPE XII HIGH CURRENT #8 AWG	
	APPD -		
MATERIAL 1	PRODUCT SPEC -	SIZE B	CAGE CODE 00779
FINISH 2 5	APPLICATION SPEC -	DRAWING NO C-193990	
WEIGHT -		SCALE	SHEET 1 OF 1

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.