





LOC	DIST	REVISIONS				
AF	50	P	LTR	DESCRIPTION	DATE	APVD
			U1	REVISED PER ECR-14-000489	11MAR2014	KB RP


- 1 DIM'S IN BRACKETS ARE IN INCHES
- 2 CONTINUOUS STRIP ON REELS
- 3 WIRE SIZE 0.8–2.0mm [#18–#14] AWG
- 4 INSULATION RANGE IS 3.05–4.32 [.120–.170] DIA.
- 5 MATING TAB THK IS 0.81±0.025 [.032±.001].
- 6 0.38 X 15° [.015 X 15°] SWAGE ON FRONT OF RECEPTACLE. FOR FOREIGN PRODUCTION ONLY.



VIEW A-A



SECT B-B



SECT C-C

TIN	BRASS	6 41274-1
TIN	BRASS	41274
FINISH	MATERIAL	PART NO.

F OR O	4.57 [.180]	6.4 [.252]	F	3.05 [.120]	1.90 [.075]	2.0mm [14]
					1.68 [.066]	1.3mm [16]
					1.55 [.061]	0.8mm [18]
TYPE	WIDTH	STRIP LENGTH ±.015	TYPE	WIDTH	±.051 [±.002] HEIGHT	WIRE
INSUL BARREL CRIMP	WIRE BARREL CRIMP					

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm [INCHES]

MATERIAL

BRASS

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC ± -

1 PLC ± -

2 PLC ± -

3 PLC ± 0.38[.015]

4 PLC ± -

ANGLES ± -

FINISH

TIN

DWN JR RUTH 2/5/86

CHK G YETTER 2/5/86

APVD R KUZO 2/5/86

PRODUCT SPEC

APPLICATION SPEC

WEIGHT -

CUSTOMER DRAWING

TE Connectivity

.250 SERIES FASTON RECEPTACLE

SIZE A3 CAGE CODE 00779 DRAWING NO C-41274

RESTRICTED TO -

SCALE 4:1 SHEET 1 OF 1 REV U1