




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
GP	00		S1	REVISED PER ECO-11-004835	11MAR11	RK	HMR

.050±.005 DIA

SECTION A—A
SCALE 10:1
10 PLACES



PC BOARD PATTERN

- 1 TO PREVENT THREAD STRIPPING, SCREW TORQUE SHOULD NOT EXCEED 9 IN LBS.
- 2 TAP HOLE IS 6-32UNC-2B, TWO MIN THREADS.
- 3 TAP HOLE IS M4 X 0.7, TWO MIN THREADS.
- 4 PACKAGED BULK.
- 5 PACKAGED INDIVIDUALLY.
- 6 NUT INCREASES TORQUE VALUE TO 26 IN LBS.
- 7 HOUSING: NYLON UL 94V-0.
TAP: COPPER ALLOY 735, .025 THICK.
- 8 TAP: .000150 TIN-LEAD OVER .000050 NICKEL.
- 9 CLEARANCE HOLE FOR A 6-32 SCREW.
- 10 TAP: .000150 TIN OVER .000050 NICKEL.

	4	10	2	BLACK	YES	993879-1	9-55556-0
	4	8	9	BLACK	6 YES (W/NUT)	NO	1-55556-3
	4	8	9	BLACK	6 YES (W/NUT)	993879-1	1-55556-2
OBSOLETE	5	8	2	BLACK	YES	993879-1	1-55556-1
SUPSD BY -9	-	8	3	BLACK	YES	NO	1-55556-0
	4	8	3	BLACK	YES	M4 X 0.7 X 6MM	55556-9
SUPSD BY -4	-	8	2	WHITE	YES	993879-1	55556-8
SUPSD BY -4	-	8	2	GREEN	YES	993879-1	55556-7
SUPSD BY -4	-	8	2	BLUE	YES	993879-1	55556-6
SUPSD BY -4	-	8	2	RED	YES	993879-1	55556-5
	4	8	2	BLACK	YES	993879-1	55556-4
	4	8	2	BLACK	YES	NO	55556-3
OBSOLETE	-	8	2	BLACK	NO	993879-1	55556-2
	-	8	2	BLACK	NO	NO	55556-1
PACKAGE	FINISH	HOLE TYPE	HOUSING COLOR	HOUSING AND TAP ASSEMBLED	SCREW	PART NO.	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	J.McCLINTON	1-11-88	TE Connectivity		
DIMENSIONS: INCHES		CHK	R.STONE	1-11-88			
		APVD	M.GALLOWAY	1-11-88	NAME TAP ASSEMBLY, POWER DISTRIBUTION		
		PRODUCT SPEC	108-11030				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	114-1100		SIZE	CAGE CODE	DRAWING NO
0 PLC ± -		WEIGHT			A2	00779	C=55556
1 PLC ± -		CUSTOMER DRAWING		SCALE	4:1	SHEET	1 OF 1
2 PLC ± -							REV
3 PLC ± .010							S1
4 PLC ± -							
ANGLES ± -							
FINISH							
MATERIAL							
7							