



BUK7905-40AI

N-channel TrenchPLUS standard level FET

Rev. 02 — 16 February 2009

Product data sheet

1. Product profile

1.1 General description

Standard level N-channel enhancement mode Field-Effect Transistor (FET) in a plastic package using TrenchMOS technology. The devices include TrenchPLUS current sensing. This product has been designed and qualified to the appropriate AEC standard for use in automotive critical applications.

1.2 Features and benefits

- Low conduction losses due to low on-state resistance
- Q101 compliant
- Reduced component count due to integrated current sensor
- Suitable for standard level gate drive sources

1.3 Applications

- Electrical Power Assisted Steering (EPAS)
- Variable Valve Timing for engines

1.4 Quick reference data



Table 1. Quick reference

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit |
|-------------------------------|---|---|-----|-----|-----|------|
| V_{DS} | drain-source voltage | $T_j \geq 25\text{ °C}$; $T_j \leq 175\text{ °C}$ | - | - | 40 | V |
| I_D | drain current | $V_{GS} = 10\text{ V}$; $T_{mb} = 25\text{ °C}$; see Figure 2 ; see Figure 3 ; | [1] | - | 155 | A |
| Static characteristics | | | | | | |
| $R_{DS(on)}$ | drain-source on-state resistance | $V_{GS} = 10\text{ V}$; $I_D = 50\text{ A}$; $T_j = 25\text{ °C}$; see Figure 7 ; see Figure 8 | - | 4.5 | 5 | mΩ |
| I_D/I_{sense} | ratio of drain current to sense current | $T_j > -55\text{ °C}$; $V_{GS} > 10\text{ V}$; $T_j < 175\text{ °C}$ | 450 | 500 | 550 | |

[1] Current is limited by power dissipation chip rating.

2. Pinning information

Table 2. Pinning information

| Pin | Symbol | Description | Simplified outline | Graphic symbol |
|-----|--------|-----------------------------------|--|---|
| 1 | G | gate |  |  |
| 2 | ISENSE | current sense | | |
| 3 | D | drain | | |
| 4 | KS | Kelvin source | | |
| 5 | S | source | | |
| mb | D | mounting base; connected to drain | | |
| | | | SOT263B (TO-220) | 03nI64 |

3. Ordering information

Table 3. Ordering information

| Type number | Package | | Version |
|--------------|---------|--|---------|
| | Name | Description | |
| BUK7905-40AI | TO-220 | plastic single-ended package; heatsink mounted; 1 mounting hole; 5-lead TO-220 | SOT263B |

4. Limiting values


Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

| Symbol | Parameter | Conditions | | Min | Max | Unit |
|-------------------------|--|---|---------------------|-----|------|------|
| V _{DS} | drain-source voltage | T _j ≥ 25 °C; T _j ≤ 175 °C | | - | 40 | V |
| V _{DGR} | drain-gate voltage | R _{GS} = 20 kΩ | | - | 40 | V |
| V _{GS} | gate-source voltage | | | -20 | 20 | V |
| I _D | drain current | T _{mb} = 25 °C; V _{GS} = 10 V; see Figure 2 ; | [1] | - | 155 | A |
| | | see Figure 3 ; | [2] | - | 75 | A |
| | | T _{mb} = 100 °C; V _{GS} = 10 V; see Figure 2 ; | [2] | - | 75 | A |
| I _{DM} | peak drain current | T _{mb} = 25 °C; t _p ≤ 10 μs; pulsed; see Figure 3 | | - | 620 | A |
| P _{tot} | total power dissipation | T _{mb} = 25 °C; see Figure 1 | | - | 272 | W |
| T _{stg} | storage temperature | | | -55 | 175 | °C |
| T _j | junction temperature | | | -55 | 175 | °C |
| Source-drain diode | | | | | | |
| I _S | source current | T _{mb} = 25 °C; | [1] | - | 155 | A |
| | | | [2] | - | 75 | A |
| I _{SM} | peak source current | t _p ≤ 10 μs; pulsed; T _{mb} = 25 °C | | - | 620 | A |
| Avalanche ruggedness | | | | | | |
| E _{DS(AL)S} | non-repetitive drain-source avalanche energy | I _D = 75 A; V _{sup} ≤ 40 V; R _{GS} = 50 Ω; V _{GS} = 10 V; T _{j(init)} = 25 °C; unclamped | | - | 1.46 | J |
| Electrostatic discharge | | | | | | |
| V _{esd} | electrostatic discharge voltage | HBM; C = 100 pF; R = 1.5 kΩ | | - | 4 | kV |


[1] Current is limited by power dissipation chip rating.

[2] Continuous current is limited by package.




$$P_{der} = \frac{P_{tot}}{P_{tot(25^{\circ}\text{C})}} \times 100\%$$

Fig 1. Normalized total power dissipation as a function of mounting base temperature



$$V_{GS} \geq 10\text{V}$$

Fig 2. Continuous drain current as a function of mounting base temperature



$$T_{mb} = 25^{\circ}\text{C}; I_{DM} \text{ is single pulse}$$

Fig 3. Safe operating area; continuous and peak drain currents as a function of drain-source voltage

5. Thermal characteristics

Table 5. Thermal characteristics

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit |
|----------------|---|------------------------------|-----|-----|------|------|
| $R_{th(j-a)}$ | thermal resistance from junction to ambient | vertical in still air | - | 60 | - | K/W |
| $R_{th(j-mb)}$ | thermal resistance from junction to mounting base | see Figure 4 | - | - | 0.55 | K/W |




Fig 4. Transient thermal impedance from junction to mounting base as a function of pulse duration


6. Characteristics

Table 6. Characteristics

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit |
|------------------------------------|---|---|------|------|------|------|
| Static characteristics | | | | | | |
| V _{(BR)DSS} | drain-source breakdown voltage | I _D = 0.25 mA; V _{GS} = 0 V; T _j = 25 °C | 40 | - | - | V |
| | | I _D = 0.25 mA; V _{GS} = 0 V; T _j = -55 °C | 36 | - | - | V |
| V _{GS(th)} | gate-source threshold voltage | I _D = 1 mA; V _{DS} = V _{GS} ; T _j = 25 °C; see Figure 9 | 2 | 3 | 4 | V |
| | | I _D = 1 mA; V _{DS} = V _{GS} ; T _j = 175 °C; see Figure 9 | 1 | - | - | V |
| | | I _D = 1 mA; V _{DS} = V _{GS} ; T _j = -55 °C; see Figure 9 | - | - | 4.4 | V |
| I _{DSS} | drain leakage current | V _{DS} = 40 V; V _{GS} = 0 V; T _j = 25 °C | - | 0.1 | 10 | μA |
| | | V _{DS} = 40 V; V _{GS} = 0 V; T _j = 175 °C | - | - | 500 | μA |
| I _{GSS} | gate leakage current | V _{DS} = 0 V; V _{GS} = 20 V; T _j = 25 °C | - | 2 | 100 | nA |
| | | V _{DS} = 0 V; V _{GS} = -20 V; T _j = 25 °C | - | 2 | 100 | nA |
| R _{DSon} | drain-source on-state resistance | V _{GS} = 10 V; I _D = 50 A; T _j = 25 °C; see Figure 7 ; see Figure 8 | - | 4.5 | 5 | mΩ |
| | | V _{GS} = 10 V; I _D = 50 A; T _j = 175 °C; see Figure 7 ; see Figure 8 | - | - | 9.5 | mΩ |
| I _D /I _{sense} | ratio of drain current to sense current | V _{GS} > 10 V; T _j > -55 °C; T _j < 175 °C | 450 | 500 | 550 | |
| R _{(D-ISENSE)on} | drain-ISENSE on-state resistance | V _{GS} = 10 V; I _D = 25 mA; T _j = 25 °C; see Figure 16 | 0.98 | 1.08 | 1.18 | Ω |
| | | V _{GS} = 10 V; I _D = 25 mA; T _j = 175 °C; see Figure 16 | 1.86 | 2.05 | 2.24 | Ω |
| Dynamic characteristics | | | | | | |
| Q _{G(tot)} | total gate charge | I _D = 25 A; V _{DS} = 32 V; V _{GS} = 10 V; T _j = 25 °C; see Figure 14 | - | 120 | 127 | nC |
| Q _{GS} | gate-source charge | | - | 19 | 22 | nC |
| Q _{GD} | gate-drain charge | | - | 50 | 60 | nC |
| C _{iss} | input capacitance | V _{GS} = 0 V; V _{DS} = 25 V; f = 1 MHz; T _j = 25 °C; see Figure 12 | - | 4300 | 5000 | pF |
| C _{oss} | output capacitance | | - | 1400 | 1670 | pF |
| C _{rss} | reverse transfer capacitance | | - | 820 | 1100 | pF |
| t _{d(on)} | turn-on delay time | V _{DS} = 30 V; R _L = 1.2 Ω; V _{GS} = 10 V; R _{G(ext)} = 10 Ω; T _j = 25 °C | - | 35 | - | ns |
| t _r | rise time | | - | 115 | - | ns |
| t _{d(off)} | turn-off delay time | | - | 155 | - | ns |
| t _f | fall time | | - | 110 | - | ns |
| L _D | internal drain inductance | measured from upper edge of drain mounting base to center of die; T _j = 25 °C | - | 2.5 | - | nH |
| L _S | internal source inductance | measured from source lead to source bond pad; T _j = 25 °C | - | 7.5 | - | nH |


Table 6. Characteristics ...continued

| Symbol | Parameter | Conditions | Min | Typ | Max | Unit |
|--------------------|-----------------------|--|-----|------|-----|------|
| Source-drain diode | | | | | | |
| V_{SD} | source-drain voltage | $I_S = 40\text{ A}$; $V_{GS} = 0\text{ V}$; $T_j = 25\text{ }^{\circ}\text{C}$; see Figure 17 | - | 0.85 | 1.2 | V |
| t_{rr} | reverse recovery time | $I_S = 20\text{ A}$; $di_S/dt = -100\text{ A}/\mu\text{s}$; $V_{GS} = -10\text{ V}$; | - | 96 | - | ns |
| Q_r | recovered charge | $V_{DS} = 30\text{ V}$; $T_j = 25\text{ }^{\circ}\text{C}$ | - | 224 | - | nC |




$T_j = 25\text{ }^{\circ}\text{C}; t_p = 300\mu\text{s}$

Fig 5. Output characteristics: drain current as a function of drain-source voltage; typical values




$T_j = 25\text{ }^{\circ}\text{C}; I_D = 50\text{ A}$

Fig 6. Drain-source on-state resistance as a function of gate-source voltage; typical values




$T_j = 25\text{ }^{\circ}\text{C}; t_p = 300\mu\text{s}$

Fig 7. Drain-source on-state resistance as a function of drain current; typical values




$$a = \frac{R_{DSon}}{R_{DSon(25\text{ }^{\circ}\text{C})}}$$

Fig 8. Normalized drain-source on-state resistance factor as a function of junction temperature




$I_D = 1\text{ mA}; V_{DS} = V_{GS}$

Fig 9. Gate-source threshold voltage as a function of junction temperature




$T_j = 25\text{ °C}; V_{DS} = 5\text{ V}$

Fig 10. Sub-threshold drain current as a function of gate-source voltage




$T_j = 25\text{ °C}; V_{DS} = 25\text{ V}$

Fig 11. Forward transconductance as a function of drain current; typical values




$V_{GS} = 0\text{ V}; f = 1\text{ MHz}$

Fig 12. Input, output and reverse transfer capacitances as a function of drain-source voltage; typical values




$V_{DS} = 25V$

Fig 13. Transfer characteristics: drain current as a function of gate-source voltage; typical values




$T_j = 25\text{ °C}; I_D = 25A$

Fig 14. Gate-source voltage as a function of turn-on gate charge; typical values




$I_D = 50A$

Fig 15. Drain-sense current ratio as a function of gate-source voltage; typical values



$I_{sense} = 25mA$

Fig 16. Drain-sense current on-state resistance as a function of gate-source voltage; typical values



$V_{GS} = 0V$

Fig 17. Drain current as a function of source-drain diode voltage; typical values

7. Package outline

Plastic single-ended package; heatsink mounted; 1 mounting hole; 5-lead TO-220 SOT263B




Fig 18. Package outline SOT263B (TO-220)

8. Revision history

Table 7. Revision history

| Document ID | Release date | Data sheet status | Change notice | Supersedes |
|----------------------------------|--|--------------------|---------------|-----------------|
| BUK7905-40AI_2 | 20090216 | Product data sheet | - | BUK7905_40AI-01 |
| Modifications: | <ul style="list-style-type: none">The format of this data sheet has been redesigned to comply with the new identity guidelines of NXP Semiconductors.Legal texts have been adapted to the new company name where appropriate. | | | |
| BUK7905_40AI-01 (9397 750 12346) | 20040209 | Product data sheet | - | - |

9. Legal information

9.1 Data sheet status

| Document status ^{[1][2]} | Product status ^[3] | Definition |
|-----------------------------------|-------------------------------|---|
| Objective [short] data sheet | Development | This document contains data from the objective specification for product development. |
| Preliminary [short] data sheet | Qualification | This document contains data from the preliminary specification. |
| Product [short] data sheet | Production | This document contains the product specification. |

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.nexperia.com>.

9.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Nexperia does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Nexperia sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

9.3 Disclaimers

General — Information in this document is believed to be accurate and reliable. However, Nexperia does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information.

Right to make changes — Nexperia reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Nexperia products are not designed, authorized or warranted to be suitable for use in medical, military, aircraft, space or life support equipment, nor in applications where failure or malfunction of a Nexperia product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Nexperia accepts no liability for inclusion and/or use of Nexperia products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Nexperia makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Quick reference data — The Quick reference data is an extract of the product data given in the Limiting values and Characteristics sections of this document, and as such is not complete, exhaustive or legally binding.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) may cause permanent damage to the device. Limiting values are stress ratings only and operation of the device at these or any other conditions above those given in the Characteristics sections of this document is not implied. Exposure to limiting values for extended periods may affect device reliability.

Terms and conditions of sale — Nexperia products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.nexperia.com/profile/terms>, including those pertaining to warranty, intellectual property rights infringement and limitation of liability, unless explicitly otherwise agreed to in writing by Nexperia. In case of any inconsistency or conflict between information in this document and such terms and conditions, the latter will prevail.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

9.4 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

10. Contact information

For more information, please visit: <http://www.nexperia.com>

For sales office addresses, please send an email to: salesaddresses@nexperia.com

11. Contents

1 Product profile1

1.1 General description1

1.2 Features and benefits1

1.3 Applications1

1.4 Quick reference data1

2 Pinning information2

3 Ordering information2

4 Limiting values3

5 Thermal characteristics5

6 Characteristics6

7 Package outline11

8 Revision history12

9 Legal information13

9.1 Data sheet status13

9.2 Definitions13

9.3 Disclaimers13

9.4 Trademarks13

10 Contact information13