


LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DATE DWN APVD
—	—		A1	ECR-15-009194	29JUN2015 KH CW



PROFIL 1:
ANWENDUNG: TIMER NR. 925 598 (925 575 Bd.)
MINI TIMER NR. 925 596 (925 590 Bd.)
CRIMP-BEREICH: 0,5 BIS 1,5mm² LEITERQUERSCHNITT




PROFIL 2:
ANWENDUNG: TIMER NR. 925 613 (925 612 Bd.)
MINI TIMER NR. 925 597 (925 595 Bd.)
CRIMP-BEREICH: 1,5 BIS 2,5mm² LEITERQUERSCHNITT



LEITERQUERSCHNITT		AUSZIEHKRÄFTE - PRÜFNORM	
mm	ENTSPR. AWG	DIN	AMP
0.5	20	80 N	90 N
0.75	18	120 N	130 N
1.0	17	160 N	170 N
1.5	15	200 N	220 N
2.5	13	250 N	280 N

Zeichnung geschützt durch
© Copyright 1975
AMP DEUTSCHLAND GmbH
Alle Rechte vorbehalten

Note:
825590-1 SUPERCEDED BY PN 539687-2

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN M.Delp 24.01.2007	 TE Connectivity		
		CHK M.Delp 24.01.2007			
		APVD M.Delp 24.01.2007			
		NAME			
DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	PRODUCT SPEC	HAND TOOL FOR TIMER CONTACTS Handzange fuer Timer kontakte		
	0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± -	APPLICATION SPEC	SIZE A3	CAGE CODE 00779	DRAWING NO C=825590
MATERIAL	FINISH	WEIGHT 0,000kg	RESTRICTED TO —		
CUSTOMER DRAWING			SCALE 1:1	SHEET 1 OF 1	REV A1