

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

.19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.



LOC	DIST	REVISIONS				
AA	22	P	LTR	DESCRIPTION	DATE	DWN
					APVD	
		C		REVISED; EC 0U1C-0037-99	24AUG99	DLD
						CMB

D

C

B

A




MATERIAL: HOUSING - HTN NYLON, BLACK, IR REFLOW COMPATIBLE, UL 94V-0.
TERMINALS - 0.33[.013] THICK PHOS BRONZE PLATED WITH 1.27 μ m[.000050] MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 3.81 μ m[.000150] MINIMUM THICK TIN-LEAD IN SOLDER AREA OVER 1.27 μ m[.000050] MINIMUM THICK NICKEL UNDERPLATE.




JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.

3. DIMENSIONS ARE NOMINAL UNLESS OTHERWISE SPECIFIED.



SUGGESTED PC BOARD LAYOUT
VIEW SHOWN IS TOP OF PC BOARD
(COMPONENT SIDE)



SUGGESTED PANEL CUTOUT

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN S. MAYBERRY 20 JUL 93	AMP AMP Incorporated Harrisburg, PA 17105-3608		
DIMENSIONS: mm [INCHES]		CHK B. FOX 03 AUG 93			
		APVD G. REED 03 AUG 93	NAME MODULAR JACK ASSEMBLY, 10 POSITION, SIDE ENTRY, KEYED, LOW PROFILE		
		PRODUCT SPEC —			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC —	SIZE A2		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±0.13[.005] 4 PLC ± ANGLES ± FINISH		WEIGHT —			
MATERIAL		CUSTOMER DRAWING	CAGE CODE 00779	DRAWING NO C-558066	SCALE 4:1
1		1	SHEET 1 OF 1	REV C	

D

C

B

A

558066