

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0010845060

Status:

Active

Overview:

MLX™ Power Connectors

Description:

6.35mm Pitch MLX™ Power Connector Header, Vertical, 6 Circuits, Polyester 94V-0, Tin (Sn) Plating, White

Documents:

3D Model

Drawing (PDF)

Product Specification PS-42022-0001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Overview

Product Name

UPC

PCB Headers

42002

Power, Wire-to-Board

Solder Type

MLX™ Power Connectors

MLX™

800753869042

Physical

Breakaway

Circuits (Loaded)

Circuits (maximum)

Color - Resin

Durability (mating cycles max)

First Mate / Last Break

Flammability

Glow-Wire Compliant

Guide to Mating Part

Keying to Mating Part

Lock to Mating Part

Material - Metal

Material - Plating Mating

Material - Resin

Net Weight

Number of Rows

Orientation

PC Tail Length

PCB Retention

PCB Thickness - Recommended

Packaging Type

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Polarized to PCB

Shrouded

Stackable

Surface Mount Compatible (SMC)

Temperature Range - Operating

Termination Interface: Style

No

6

6

Natural

50

No

94V-0

No

Yes

Yes

Yes

Phosphor Bronze

Tin

Polyester

3.805/g

3

Vertical

4.27mm

Yes

1.60mm

Bag

6.35mm

6.35mm

Yes

Yes

Fully

No

No

-55°C to +105°C

Through Hole

Electrical

Current - Maximum per Contact

13.5A, 20.0A



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Contains SVHC(2014 December 17): No

Halogen-Free

Status

Not Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

ELV

Green Image

Not Relevant

Search Parts in this Series

42002 Series

Mates With

42021 Plug

Voltage - Maximum	600V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Process Temperature max. C	260
Material Info	
Old Part Number	42002-06C1A1
Reference - Drawing Numbers	
Product Specification	PS-42022-0001
Sales Drawing	SDA-42002-*****

This document was generated on 06/23/2015

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION