


DO NOT SCALE

DIMENSIONS IN mm

METRIC



THIRD ANGLE
PROJECTION

REVISION




LTR	DESCRIPTION	DATE	DWN	APVD
K1	REV PER ECO-09-022178	17DEC09	KK	AEG

NOTES

- 1 FOR USE ON MINIATURE APPLICATORS (LEFT-RIGHT FEED)
AND STANDARD APPLICATORS (RIGHT-LEFT FEED).
- 2 BRASS ACC ASTM B36 ALLOY 260.
- 3 PH.BRONZE ACC ASTM B103.
- 4 GAGE 0,45 MUST NOT ENTER , GAGE 0,33 MUST ENTER.
- 5 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI



4 for 0,5mm tab thickness.



SECTION A-A

SECTION B-B

DIRECTION OFF TOP OF REEL



Terminal "U" up.

5 OBSOLETE

1/2	TINPLATED	BRASS	160666-5
1/3	TINPLATED	PH.BRONZE	160666-4
1/2	UNPLATED	BRASS	160666-3
1/3	GOLDPLATED	PH.BRONZE	160666-2
1/3	UNPLATED	PH.BRONZE	160666-1
NOTES	FINISH	MATERIAL	PARTNUMBER

CUSTOMER
DRAWINGFOR REFERENCE ONLY
WILL NOT BE UPDATED**AMP**

AMP-HOLLAND B.V.

's-Hertogenbosch, The Netherlands.

THIS DRAWING IS UNPUBLISHED RELEASED FOR PUBLICATION oct , 1986

© COPYRIGHT 1986 BY AMP-HOLLAND B.V.
ALL INTERNATIONAL RIGHTS RESERVED.
AMP PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENTS AND/OR
PATENTS PENDING.

DR.	DATE	WIRE RANGE	NAME	REV. DATE
R.v.Lokven	06.10.86	0,12-0,35mm ²		D M Y
CHK.	DATE	INSUL. RANGE		
A.B.	07.10.86	0,9-1,6mmDIA	.110 SRS FASTON RECEPTACLE. (short version).	06/10/86
APP.	DATE	SIZE	SHEET	DWG. No.
L.v.Soest	07.10.86	A3	1 OF 1	C-160666
				R1
				REV.LTR.
				K1