


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PPS PART NUMBER	"A" WIDTH in. [mm]	"B" HEIGHT in. [mm]	STD. PKG. QTY.
PPS0204	4.50 [114.3]	2.25 [57.2]	5
PPS0305	5.00 [127.0]	3.50 [88.9]	
PPS0507	7.00 [177.8]	5.00 [127.0]	
PPS0514	14.00 [355.6]	5.00 [127.0]	
PPS0710	7.00 [177.8]	10.00 [254.0]	1
PPS1007	10.00 [254.0]	7.00 [177.8]	
PPS1014	14.00 [335.6]	10.00 [254.0]	
PPS1209	9.00 [228.6]	12.00 [304.8]	
PPS1420	20.00 [508.0]	14.00 [335.6]	



PVS PART NUMBER	"A" WIDTH in. [mm]	"B" HEIGHT in. [mm]	STD. PKG. QTY.
PVS0109	9.00 [228.6]	1.50 [38.1]	5
PVS0305	5.00 [127.0]	3.50 [88.9]	
PVS0404	4.00 [101.6]	4.00 [101.6]	
PVS0505	5.00 [127.0]	5.00 [127.0]	
PVS0507	7.00 [177.8]	5.00 [127.0]	
PVS0509	9.00 [228.6]	5.00 [127.0]	1
PVS0705	5.00 [127.0]	7.00 [177.8]	
PVS0710	10.00 [254.0]	7.00 [177.8]	

NOTES:

1. MILLIMETERS ARE IN [].
2. VISIT www.Panduit.com to view legend images.
3. REFERENCE C10950, C10951, C10949 FOR ADDITIONAL PPS AND PVS STYLES.

										CAD FILENAME/LAYERS		100824BR-DC-C10952/01B							
										PANDUIT CORP. TINLEY PARK, ILLINOIS									
										CUSTOMER DRAWING Safety Sign PVS and PPS STYLE 1									
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .06 (XXX) ± .015 (.XX) ± .032 ANGLES ±		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.							
1	1/26/12	RVU	ML	ADD PN: PVS0705 ON TABLE. MOVE PVS0209 TO A50284.			6655	R			DRAWN BY RVU	MAT'L:							
0	12/5/11	RVU		DRAWING RELEASE.			6568	R			DATE 12/5/11	<table><tr><td>SIGN TYPE</td><td>MATERIAL CODE</td></tr><tr><td>PPS</td><td>PPS - POLYESTER WITH OVERLAMINATE</td></tr><tr><td>PVS</td><td>GMV1 VINYL</td></tr></table>	SIGN TYPE	MATERIAL CODE	PPS	PPS - POLYESTER WITH OVERLAMINATE	PVS	GMV1 VINYL	SCALE NTS
SIGN TYPE	MATERIAL CODE																		
PPS	PPS - POLYESTER WITH OVERLAMINATE																		
PVS	GMV1 VINYL																		
REV	DATE	BY	CHK	DESCRIPTION			ECN	R	CUST	SUP	CHK'D ML	DRAWING NO. C10952	DWG A SIZE						