




DESCRIPTION: 986 SERIES OVER-MOLD CANS



SERIES _____ 986-XXX-XXX-XX1
POSITIONS _____
009
015
025
037
050
MATERIAL _____
COLD ROLLED STEEL
PLATING: _____
12 = NICKEL
PUT-UPS _____
1 = KIT

	A	B	C	D	MAX. CABLE DIA.
9	.815 20.70	.410 10.41	1.200 30.48	.490 12.45	.375 9.50
15	1.150 29.21	.410 10.41	1.200 30.48	.490 12.45	.375 9.50
25	1.690 42.93	.410 10.41	1.200 30.48	.490 12.45	.375 9.50
37	2.340 59.44	.610 15.49	1.650 41.91	.490 12.45	.575 14.60
50	2.240 56.90	.580 14.73	1.650 41.91	.600 15.24	.575 14.60

NOTE:
WHEN USED WITH NORCOMP 170/171 SERIES CONNECTORS AND TOOLING, AN AXIAL PULL OF 35-40 LBS. CAN BE ACHIEVED.

MATERIAL: STEEL
PLATING: TIN



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OF SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
WAYNE ROBBINS

CHECKED:

DATE:
10-4-98

DATE:

SCALE:
1:1

SHEET
1 OF
1

DWG NO.
986-XXX-020-121

REV
2

NorComp