


Hubbell Raceway Systems
More Innovation. More Capacity. More Flexibility.

HUBBELL



Nobody delivers like Hubbell Commercial Solutions




The Raceway Story

For well over a century, Hubbell Wiring Systems, including Wiring Device-Kellems and Hubbell Premise Wiring, has continued its tradition of pioneering innovative products and quality solutions for industrial, commercial and institutional applications.

In 1986, Hubbell's commitment to this tradition led to the introduction of PolyTrak®, a line of ground-breaking non-metallic surface raceway that was designed and developed to exceed every customer's expectations.

Listening to and understanding the needs of our customers gave rise to several unique PolyTrak designs that meet virtually every raceway application. With products like BaseTrak®, Super BaseTrak®, LANTrak®, WallTrak®, PremiseTrak® and PlugTrak®, customers can easily install the right raceway system to provide the proper capacity, bend radius and aesthetically pleasing design for any power, data and telecommunication cable distribution.



Hubbell's innovative tradition continues today with the introduction of a new line of metal raceway. Only Hubbell Wiring Systems could take a familiar, mature product like metal raceway and make it better. How did we do it? We listened to our customers.

Through extensive interviews, in-depth focus groups and state-of-the-art research and development, we have delivered an improved metal raceway product line with all the enhancements and flexibility customers asked for. Technologies like the Hubbell Handi-Screw and



the Hubbell By-Pass divider along with rounded corners, single-seam box construction and enhanced datacom capabilities are just some of the features we incorporated to benefit customers. With maximum functionality, vital capacity, unmatched quality and easy installation, never before has there been a metal raceway like this.




Listening to the customer and developing and implementing innovative products to meet their needs are the fundamental principles that make Hubbell Wiring Systems a respected leader in the electrical and data communications industry. These same principles are the driving force behind the expansion and enhancement of our comprehensive surface raceway product line. That's our story.



HUBBELL Advantage

- Best in Class Products**
Industry leading datacom capacity and capabilities.
- Ease of Installation**
Hubbell Handi-Screw speeds installation through easy screw alignment.
- Application Solutions**
Flexibility to accommodate a wide range of power and datacom applications.

Hubbell Non-Metallic Raceway Product Applications



Catalog Number	Description	Catalog Number	Description
1 PDB12TGD	Two-Gang Deep Divided Box for WallTrak, LANTrak and PremiseTrak (Latching)	5 PP1IEBC	Internal Elbow (Base and Cover) for PremiseTrak (Latching)
2 PP1BC7	7 ft. PremiseTrak (Latching) Single Channel	6 PS3BC10	10 ft. (Base and Cover) Super BaseTrak Three Channel Raceway
3 PP1TCBC	Tee Fitting (Base and Cover) for PremiseTrak (Latching)	7 PS3FCIB3G	Three-Gang Full Capacity Raised Inline Box Super BaseTrak
4 PDB12LF	Round Lighting Fixture Box for WallTrak, LANTrak and PremiseTrak (Latching)	8 PS3IEBC	Internal Elbow (Base and Cover) for Super BaseTrak



Catalog Number		Description
9 PLP1CACF		Conduit Adapter/Ceiling Fitting for WallTrak, LANTrak and PremiseTrak (Latching)
10 PDB12LPB		Low Profile Box WallTrak, LANTrak and PremiseTrak (Latching)
11 PL1FEBC		Flat Elbow (Base and Cover) LANTrak
12 PT156112		PlugTrak 6 ft. 15 Amp Single Circuit Six Duplex Receptacles 12" Spacing

Catalog Number		Description
13 PB3RED		Reducer BaseTrak to WallTrak
14 PB3FCIB3G		Three-Gang Full Capacity Raised Inline Box BaseTrak
15 PB2IND2G		Two-Gang Inline Flush Box PB2 BaseTrak
16 PB2SPL10 PB2B10		10 ft. (Split Cover) 10 ft. (Base) PB2 BaseTrak Raceway

Non-Metallic Surface Raceway



Complete Line of Raceway

- PolyTrak Non-Metallic Surface Raceway is a complete system with raceway, fittings, boxes and devices.
- Sizes range from single channel PremiseTrak to three channel Super BaseTrak for all types of surface raceway requirements.
- Single and two channel latching raceways are dual-rated for both power and data applications, reducing inventory requirements.
- UL Listed and CSA Certified to 600 volts.
- Office white color.

Advantage HUBBELL



Non-Metallic PlugTrak

- Available as hard wired multi-outlet assembly or relocatable power tap.
- Hubbell designed and manufactured 15 or 20 Amp receptacles.
- UL Listed and CSA Certified.
- Office white color.

Hard wired multi-outlet PlugTrak:

- Available in 5 ft. or 6 ft. lengths.
- Available in single, two circuit and is inherently an isolated ground product.
- Multiple spacing configurations.
- Hard wired PlugTrak mates with LANTrak fittings and boxes.

Portable PlugTrak:

- Available in 3 ft. or 5 ft. lengths.
- 6 ft. length 15 or 20 Amp molded cord set allows reliable access.
- Pre-punched holes makes mounting easy.

Advantage HUBBELL

One Box, Three Systems

- Boxes have three cut-aways that can be utilized with WallTrak, LANTrak and PremiseTrak (Latching) systems.
- Reduces inventory requirements.
- Eliminates need to order three separate boxes.
- Boxes available in low, standard and deep profiles.
- Two-gang divided box available for power, data, voice, audio and video applications.
- Boxes utilize Hubbell KP plates or INFIneSTATION™ modules and bezels.



Advantage HUBBELL






Flush or Full Capacity Boxes

- Super BaseTrak and BaseTrak raceway offer multiple solutions for box installation.
- Super BaseTrak inline three-gang box allows maximum capacity in a flush design.
- Super BaseTrak and BaseTrak available in single, two and three-gang full capacity boxes.
- Three and two channel BaseTrak (PB3 and PB2) available with one and two-gang inline boxes.
- Full capacity in-line boxes eliminate the need to de-rate the wire-fill capacity due to the intrusion of datacom devices into the raceway channel.



Advantage HUBBELL


PT1 PremiseTrak® (Non-Latching) Non-Metallic Raceway

Raceway		Catalog Number	Length	Color
Base and Cover Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	 	PT1BC5 PT1BC7 A: .68" (17.30) B: .75" (18.90)	5 ft. 7 ft.	Office White
		PT1ABC5 PT1ABC7 A: .68" (17.30) B: .75" (18.90)	5 ft. 7 ft.	Office White
Switch and Receptacle Boxes		Catalog Number	Color	
One-Gang Low Profile Box For shallow switches and receptacles.	 	PT12LPB A: 3.25" (82.55) B: 4.90" (124.46) C: 1.12" (28.50)	Office White	
		PT12SBA A: 3.25" (82.55) B: 4.90" (124.46) C: 1.63" (41.40)	Office White	
One-Gang Standard Box For standard switches and receptacles.	 	PT12DBA A: 3.25" (82.55) B: 4.90" (124.46) C: 1.91" (48.40)	Office White	
		PT12TGB A: 5.06" (128.52) B: 4.90" (124.46) C: 1.91" (48.40)	Office White	
Two-Gang Deep Box For deep devices or applications where additional room is beneficial. Uses two-gang KP or DP plates for data application. Uses two-gang KP plate for power application.	 	PT12LFB A: 5.31" (134.87) B: 1.04" (26.50)	Office White	
		PT12LFB A: 5.31" (134.87) B: 1.04" (26.50)	Office White	
Round Box		Catalog Number	Color	
Round Lighting Fixture Box To hang fixtures.	 	PT12LFB A: 5.31" (134.87) B: 1.04" (26.50)	Office White	
		PT12LFB A: 5.31" (134.87) B: 1.04" (26.50)	Office White	

Fittings

Internal Elbow - Cover Only

For inside surfaces at right angles.




PT1IE

A: 1.34" (33.9)
B: 0.89" (22.7)
C: 1.34" (33.9)

Office
White

External Elbow - Cover Only

For outside surfaces at right angles.




PT1EE

A: 1.24" (27.69)
B: 0.88" (22.35)
C: 1.24" (27.69)

Office
White

Flat Elbow - Cover Only

For right angle turns on same surface.




PT1FE

A: 1.33" (33.78)
B: 1.33" (33.78)
C: 0.74" (18.70)

Office
White

Tee - Cover Only

Full capacity 1¼ in. bend radius. Tee.




PT1TC

A: 1.77" (44.90)
B: 1.33" (33.80)
C: 0.74" (18.70)

Office
White

Splice Cover

For covering potential openings where two lengths of raceway come together.




PT1SC

A: 1.00" (25.40)
B: 0.89" (22.61)
C: 0.74" (18.70)

Office
White

End Cap

For closing end of raceway.




PT1EC

A: 0.88" (22.35)
B: 0.74" (18.70)
C: 0.89" (22.70)

Office
White

Conduit Adapter/Ceiling Fitting

For connecting conduit to raceway.
Also use for ceiling feeds.


















PT12CA

A: 1.64" (41.60)
B: 1.62" (41.00)
C: 2.50" (63.50)









Office
White

PP1 PremiseTrak® (Latching) Non-Metallic Raceway

Raceway		Catalog Number	Length	Color
Base and Cover Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.		PP1BC5	5 ft.	Office
		PP1BC7 A: 0.77" (19.60) B: 0.84" (21.30)	7 ft.	White
Base and Cover (with adhesive) Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.		PP1ABC5	5 ft.	Office
		PP1ABC7 A: 0.77" (19.60) B: 0.84" (21.30)	7 ft.	White
Switch and Receptacle Boxes		Catalog Number	Color	
One-Gang Low Profile Box For shallow switches and receptacles.		PDB12LP A: 3.25" (82.55) B: 4.90" (124.46) C: 1.25" (31.75)	Office White	
One-Gang Standard Box For standard switches and receptacles.		PDB12S A: 3.25" (82.55) B: 4.90" (124.46) C: 1.78" (45.21)	Office White	
One-Gang Deep Box For deep devices or applications where additional room is beneficial.		PDB12D A: 3.25" (82.55) B: 4.90" (124.46) C: 2.44" (61.98)	Office White	
Two-Gang Deep Divided Box For deep switches, receptacles and communication devices.		PDB12TGD A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)	Office White	
Two-Gang Deep Undivided Box For low voltage applications only.		PDB12TGLV A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)	Office White	
Round Box		Catalog Number	Color	
Round Lighting Fixture Box To hang fixtures.		PDB12LF A: 5.31" (134.87) B: 1.29" (32.77)	Office White	

		Catalog Number		
Fittings		Cover Only	Base & Cover	Color
Internal Elbow Full capacity 1¼ in. bend radius internal elbow.		PP1IE A: 2.40" (60.96) B: 1.03" (26.16) C: 2.40" (60.96)	PP1IEBC A: 2.40" (60.96) B: 1.03" (26.16) C: 2.40" (60.96)	Office White
External Elbow Full capacity 1¼ in. bend radius external elbow.		PP1EE A: 4.47" (113.54) B: 1.03" (26.16) C: 4.47" (113.54)	PP1EEBC A: 4.47" (113.54) B: 1.03" (26.16) C: 4.47" (113.54)	Office White
Flat Elbow Full capacity 1¼ in. bend radius flat elbow.		PP1FE A: 2.62" (66.55) B: 2.62" (66.55) C: 0.85" (21.59)	PP1FEBC A: 2.62" (66.55) B: 2.62" (66.55) C: 0.85" (21.59)	Office White
Tee Full capacity 1¼ in. bend radius tee.		PP1TC A: 4.22" (107.19) B: 2.62" (66.55) C: 0.85" (21.59)	PP1TCBC A: 4.22" (107.19) B: 2.62" (66.55) C: 0.85" (21.59)	Office White
Splice Cover For covering potential openings where two lengths of raceway come together.		PP1SC A: 1.09" (27.69) B: 1.02" (25.91) C: 0.85" (21.59)		Office White
Safety Strap For preventing potential tampering with PP1 PremiseTrak cover. Can also be used as a splice cover.		PP1SS A: 0.62" (15.75) B: 1.94" (49.28) C: 0.86" (21.84)		Office White
End Cap For closing end of raceway.		PP1EC A: 1.00" (25.40) B: 0.84" (21.34) C: 0.77" (19.56)		Office White
Conduit Adapter/Ceiling Fitting For connecting conduit to raceway. Also use for ceiling feeds.			PLP1CACF A: 2.29" (58.17) B: 3.31" (84.07) C: 3.90" (99.06)	Office White

PL1 LANTrak® (Latching) Non-Metallic Raceway


Raceway		Catalog Number	Length	Color
Base and Cover Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	 	PL1BC5	5 ft.	Office
		PL1BC7 A: 1.04" (26.40) B: 1.38" (35.00)	7 ft.	White
Base and Cover (with adhesive) Single channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	 	PL1ABC5	5 ft.	Office
		PL1ABC7 A: 1.04" (26.40) B: 1.38" (35.00)	7 ft.	White
Switch and Receptacle Boxes		Catalog Number	Color	
One-Gang Low Profile Box For shallow switches and receptacles.	 	PDB12LP A: 3.25" (82.55) B: 4.90" (124.46) C: 1.25" (31.75)	Office White	
One-Gang Standard Box For standard switches and receptacles.	 	PDB12S A: 3.25" (82.55) B: 4.90" (124.46) C: 1.78" (45.21)	Office White	
One-Gang Deep Box For deep devices or applications where additional room is beneficial.	 	PDB12D A: 3.25" (82.55) B: 4.90" (124.46) C: 2.44" (61.98)	Office White	
Two-Gang Deep Divided Box For deep switches, receptacles and communication devices.	 	PDB12TGD A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)	Office White	
Two-Gang Deep Undivided Box For low voltage applications only.	 	PDB12TGLV A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)	Office White	
Round Box		Catalog Number	Color	
Round Lighting Fixture Box To hang fixtures.	 	PDB12LF A: 5.31" (134.87) B: 1.29" (32.77)	Office White	

Catalog Number

Fittings

Internal Elbow

Full capacity 1¼ in. bend radius internal elbow.



Cover Only

PL1IE

A: 2.51" (63.75)
B: 1.57" (39.88)
C: 2.51" (63.75)

Base & Cover


PL1IEBC

A: 2.51" (63.75)
B: 1.57" (39.88)
C: 2.51" (63.75)

Office
White

External Elbow

Full capacity 1¼ in. bend radius external elbow.



PL1EE

A: 5.06" (128.52)
B: 1.57" (39.88)
C: 5.06" (128.52)


PL1EEBC

A: 5.06" (128.52)
B: 1.57" (39.88)
C: 5.06" (128.52)

Office
White

Flat Elbow

Full capacity 1¼ in. bend radius flat elbow.



PL1FE

A: 3.19" (81.03)
B: 3.19" (81.03)
C: 1.11" (28.19)


PL1FEBC

A: 3.19" (81.03)
B: 3.19" (81.03)
C: 1.11" (28.19)

Office
White

Tee

Full capacity 1¼ in. bend radius tee.



PL1TC

A: 4.75" (120.65)
B: 3.15" (80.01)
C: 1.11" (28.19)


PL1TCBC

A: 4.75" (120.65)
B: 3.15" (80.01)
C: 1.11" (28.19)

Office
White

Splice Cover

For covering potential openings where two lengths of raceway come together.




PL1SC

A: 1.12" (28.45)
B: 1.55" (39.37)
C: 1.11" (28.19)

Office
White

Safety Strap

For preventing potential tampering with PL1 LANTrak cover. Can also be used as a splice cover.




PL1SS

A: 0.62" (15.75)
B: 2.68" (68.07)
C: 1.12" (28.45)

Office
White

End Cap

For closing end of raceway.




PL1EC

A: 1.00" (25.40)
B: 1.39" (35.31)
C: 1.04" (26.42)

Office
White

Conduit Adapter/Ceiling Fitting

For connecting conduit to raceway. Also use for ceiling feeds.






















PLP1CACF

A: 2.29" (58.17)
B: 3.31" (84.07)
C: 3.90" (99.06)








Office
White

PW2 WallTrak® (Latching) Non-Metallic Raceway

Raceway		Catalog Number	Length	Color
Base and Cover Two channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	 	PW2BC5 PW2BC7 A: 1.04" (26.40) B: 2.12" (53.85)	5 ft. 7 ft.	Office White
Base and Cover (with adhesive) Two channel raceway. Available in 5 ft. (1.5m) and 7 ft. (2.1m) lengths.	 	PW2ABC5 PW2ABC7 A: 1.04" (26.40) B: 2.12" (53.85)	5 ft. 7 ft.	Office White
Switch and Receptacle Boxes		Catalog Number		Color
One-Gang Low Profile Box For shallow switches and receptacles.	 	PDB12LP A: 3.25" (82.55) B: 4.90" (124.46) C: 1.25" (31.75)		Office White
One-Gang Standard Box For standard switches and receptacles.	 	PDB12S A: 3.25" (82.55) B: 4.90" (124.46) C: 1.78" (45.21)		Office White
One-Gang Deep Box For deep devices or applications where additional room is beneficial.	 	PDB12D A: 3.25" (82.55) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
One-Gang Divider For use with PDB12S and PDB12D one-gang boxes. Required when two services are passing through box.	 	PDB1DIV A: 2.79" (70.86) B: 1.40" (35.56) C: 0.94" (23.88)		Office White
Two-Gang Deep Divided Box For deep devices or applications where additional room is beneficial.	 	PDB12TGD A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Two-Gang Divider For use with PDB12TGD two-gang box only. Required when two services are passing through box and mounting devices perpendicular to raceway.	 	PDB2DIV A: 4.62" (117.35) B: 2.76" (70.10) C: 0.94" (23.88)		Office White
Two-Gang Deep Undivided Box For low voltage applications only.	 	PDB12TGLV A: 5.06" (128.52) B: 4.90" (124.46) C: 2.44" (61.98)		Office White
Round Box		Catalog Number		Color
Round Lighting Fixture Box To hang fixtures.	 	PDB12LF A: 5.31" (134.87) B: 1.29" (32.77)		Office White

		Catalog Number		
Fittings		Cover Only	Base & Cover	Color
Internal Elbow Full capacity 1¼ in. bend radius internal elbow.		PW2IE A: 2.83" (71.88) B: 2.32" (58.93) C: 2.83" (71.88)	PW2IEBC A: 2.83" (71.88) B: 2.32" (58.93) C: 2.83" (71.88)	Office White
External Elbow Full capacity 1¼ in. bend radius external elbow.		PW2EE A: 5.00" (127.00) B: 2.32" (58.93) C: 5.00" (127.00)	PW2EEBC A: 5.00" (127.00) B: 2.32" (58.93) C: 5.00" (127.00)	Office White
Flat Elbow Full capacity 1¼ in. bend radius flat elbow.		PW2FE A: 3.94" (100.08) B: 3.94" (100.08) C: 1.11" (28.19)	PW2FEBC A: 3.94" (100.08) B: 3.94" (100.08) C: 1.11" (28.19)	Office White
Tee Full capacity 1¼ in. bend radius tee.		PW2TC A: 5.42" (137.67) B: 3.91" (99.31) C: 1.90" (48.26)	PW2TCBC A: 5.42" (137.67) B: 3.91" (99.31) C: 1.90" (48.26)	Office White
Splice Cover For covering potential openings where two lengths of raceway come together.		PW2SC A: 1.11" (28.19) B: 2.30" (58.42) C: 1.11" (28.19)		Office White
Safety Strap For preventing potential tampering with PW2 WallTrak cover. Can also be used as a splice cover.		PW2SS A: 0.62" (15.75) B: 3.43" (87.12) C: 1.12" (28.45)		Office White
End Cap For closing end of PW2 WallTrak to surface.		PW2EC A: 1.00" (25.40) B: 2.14" (54.36) C: 1.04" (26.42)		Office White
Reducer Reduces from PW2 WallTrak Raceway to one or two PP1 PremiseTrak Raceway.			PW2RED A: 1.62" (41.15) B: 2.40" (60.96) C: 1.15" (29.21)	Office White
Conduit Adapter/Ceiling Fitting For connecting conduit to raceway. Also use for ceiling feeds.			PW2CACF A: 4.18" (106.17) B: 3.32" (84.33) C: 4.20" (106.68)	Office White

PB2 BaseTrak® Non-Metallic Raceway

Raceway		Catalog Number	Length	Color
Base Two channel raceway. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.		PB2B5	5 ft.	Office
		PB2B10 A: 1.42" (36.00) B: 4.50" (114.30)	10 ft.	White
Cover Cover allows access to multiple channels. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.		PB2C5	5 ft.	Office
		PB2C10 B: 4.50" (114.30)	10 ft.	White
Split Cover Cover allows separation of channels and access to a single channel.		PB2SPL5	5 ft.	Office
		PB2SPL10 B: 2.22" (56.30)	10 ft.	White
Wire Clip For holding conductors in place.		PB2WC		Office White
Box		Catalog Number	Color	
Two-Gang InLine Box For switches, receptacles and communication devices. Provides flush look. Accepts KP style plates.		PB2IND2G	Office	
		A: 7.66" (194.56) B: 4.74" (120.40) C: 1.84" (46.74)	White	
Fittings		Catalog Number	Color	
Internal Elbow - Base and Cover Full capacity 1¼ in. bend radius internal elbow.		PB3IEBCA	Office	
		A: 4.36" (110.74) B: 4.72" (119.89) C: 4.36" (110.74)	White	
External Elbow - Base and Cover Full capacity 1¼ in. bend radius external elbow.		PB3EEBCA	Office	
		A: 6.48" (164.59) B: 4.72" (119.89) C: 6.48" (164.59)	White	
Flat Elbow - Base and Cover Full capacity 1¼ in. bend radius flat elbow.		PB3FEBCA	Office	
		A: 7.64" (194.66) B: 7.64" (194.66) C: 1.71" (43.43)	White	

Fittings

Tee - Base and Cover

Full capacity 1¼ in. bend radius tee.



Catalog Number

PB3TCBCA

A: 7.37" (187.20)
B: 7.08" (179.83)
C: 2.72" (69.09)

Color

Office
White

Splice Cover

For covering potential openings where two lengths of raceway come together.




PB3SC

A: 1.56" (39.62)
B: 4.74" (120.40)
C: 1.69" (42.93)

Office
White

Safety Strap

For preventing potential tampering with PB2 BaseTrak cover. Can also be used as a splice cover.




PB3SS

A: 1.50" (38.10)
B: 6.01" (152.65)
C: 1.74" (44.20)

Office
White

End Cap

For closing end of PB2 BaseTrak Raceway.



PB3ECA

A: 2.02" (51.31)
B: 4.68" (118.97)
C: 1.72" (43.69)

Office
White

Reducer

Reduces from PB2 BaseTrak Raceway to PW2 WallTrak Raceway.



PB3REDA

A: 3.50" (88.90)
B: 4.72" (119.89)
C: 1.73" (43.94)

Office
White

Conduit Adapter/Ceiling Fitting

For connecting conduit to raceway. Also use for ceiling feeds.




PB2CACF

A: 4.72" (119.89)
B: 5.22" (132.70)
C: 6.30" (160.02)

Office
White

Surface Panel Connector

For connecting PB2 Raceway with surface type panel boxes.



















PB3SPCA

A: 2.22" (56.39)
B: 5.66" (143.76)
C: 1.60" (40.64)








Office
White









PB3 BaseTrak® Non-Metallic Raceway

Raceway		Catalog Number	Length	Color
Base and Cover Three channel raceway. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.		PB3BC5	5 ft.	Office
		PB3BC10 A: 1.63" (41.40) B: 4.50" (114.30)	10 ft.	White
Wire Clip For holding conductors in place.		PB3WC		Office White
Boxes		Catalog Number		Color
One-Gang Inline Box For switches, receptacles and communication devices. Provides flush look. Accepts KP style plates.		PB3IND A: 7.70" (195.58) B: 4.84" (122.94) C: 2.02" (51.30)		Office White
				
Two-Gang InLine Box For switches, receptacles and communication devices. Barriers allow separation of power and datacom. Removal of barriers allows for expanded capacity. Accepts KP style plates.		PB3IND2G A: 7.00" (177.80) B: 4.75" (120.65) C: 3.22" (81.78)		Office White
				
One-Gang Full Capacity Box Single gang box that allows full capacity from PB3 raceway to box for either power or datacom applications. Accepts KP style plates and one-gang DP plates.		PB3FCIB A: 4.38" (111.25) B: 4.80" (121.92) C: 3.17" (80.52)		Office White
				
Two-Gang Full Capacity Box Two-Gang box that allows full capacity from PB3 raceway to box for any combination of power and datacom applications. Accepts KP style plates and one-gang DP plates.		PB3FCIB2G A: 7.20" (182.88) B: 4.80" (121.92) C: 3.17" (80.52)		Office White
				
Three-Gang Full Capacity Box Three gang box that allows full capacity from PB3 raceway to box for any combination of power and datacom applications. Accepts KP style plates and one-gang DP plates.		PB3FCIB3G A: 9.96" (252.98) B: 4.80" (121.92) C: 3.17" (80.52)		Office White
				
		Catalog Number		
Fittings		Cover Only	Base & Cover	Color
Internal Elbow Full capacity 1¼ in. bend radius internal elbow.		PB3IE A: 4.36" (110.74) B: 4.72" (119.89) C: 4.36" (110.74)	PB3IEBCA A: 4.36" (110.74) B: 4.72" (119.89) C: 4.36" (110.74)	Office White
				
External Elbow Full capacity 1¼ in. bend radius external elbow.		PB3EE A: 6.48" (164.59) B: 4.72" (119.89) C: 6.48" (164.59)	PB3EEBCA A: 6.48" (164.59) B: 4.72" (119.89) C: 6.48" (164.59)	Office White
				

		Catalog Number		
Fittings		Cover Only	Base & Cover	Color
Flat Elbow Full capacity 1¼ in. bend radius flat elbow.		PB3FE A: 7.64" (194.66) B: 7.64" (194.66) C: 1.71" (43.43)	PB3FEBCA A: 7.64" (194.66) B: 7.64" (194.66) C: 1.71" (43.43)	Office White
Tee Full capacity 1¼ in. bend radius tee.			PB3TCBCA A: 7.37" (187.20) B: 7.08" (179.83) C: 2.72" (69.09)	Office White
Splice Cover For covering potential openings where two lengths of raceway come together.		PB3SC A: 1.56" (39.62) B: 4.74" (120.40) C: 1.69" (42.93)		Office White
Safety Strap Prevents potential tampering with PB3 BaseTrak cover. Can also be used as a splice cover.		PB3SS A: 1.50" (38.10) B: 6.01" (152.65) C: 1.74" (44.20)		Office White
End Cap For closing end of PB3 BaseTrak Raceway.		PB3ECA A: 2.02" (51.31) B: 4.68" (118.97) C: 1.72" (43.69)		Office White
Reducer Reduces from PB3 BaseTrak Raceway to PW2 WallTrak Raceway.			PB3REDA A: 3.50" (88.90) B: 4.72" (119.89) C: 1.73" (43.94)	Office White
Conduit Adapter/Ceiling Fitting For connecting conduit to raceway. Also use for ceiling feeds.			PB3CACF A: 4.72" (119.89) B: 5.22" (132.70) C: 6.30" (160.02)	Office White
Surface Panel Connector For connecting PB3 Raceway with surface type panel boxes.		PB3SPCA A: 2.22" (56.39) B: 5.66" (143.76) C: 1.60" (40.64)		Office White
Transition Fitting Transitions horizontal PB3 BaseTrak to vertical PW2 WallTrak, PL1 LANTrak or PP1 PremiseTrak.			PB3TRBC A: 3.22" (81.79) B: 7.28" (184.91) C: 2.42" (61.47)	Office White
Transition Fitting Transitions from BT3 (old style) BaseTrak Raceway to PB3 (new style) BaseTrak Raceway.		BTPB3TF A: 2.22" (56.39) B: 5.66" (143.76) C: 1.35" (34.29)		Office White

PS3 Super BaseTrak® Non-Metallic Raceway

Raceway		Catalog Number	Length	Color
Base and Cover Three channel raceway. Available in 5 ft. (1.5m) and 10 ft. (3m) lengths.		PS3BC5	5 ft.	Office
		PS3BC10 A: 1.97" (50.00) B: 6.70" (170.20)	10 ft.	White
Wire Clip For holding conductors in place.		PS3WC		Office White
Boxes		Catalog Number	Color	
Three-Gang Inline Box For any combination of power and datacom applications. Provides flush look. Accepts KP style plates and bezels.		PS3IND A: 7.00" (177.80) B: 6.95" (176.53) C: 2.28" (57.91)	Office White	
One-Gang Full Capacity Box Single gang box that allows full capacity from PS3 raceway to box for either power or datacom applications. Accepts KP style plates and one-gang DP plates.		PS3FCIB A: 4.38" (111.25) B: 6.95" (176.53) C: 3.46" (87.88)	Office White	
Two-Gang Full Capacity Box Two-Gang box that allows full capacity from PS3 raceway to box for any combination of power and datacom applications. Accepts KP style plates and one-gang DP plates.		PS3FCIB2G A: 7.20" (182.88) B: 6.95" (176.53) C: 3.46" (87.88)	Office White	
Three-Gang Full Capacity Box Three gang box that allows full capacity from PS3 raceway to box for any combination of power and datacom applications. Accepts KP style plates and one-gang DP plates.		PS3FCIB3G A: 9.96" (252.98) B: 6.95" (176.53) C: 3.46" (87.88)	Office White	
		Catalog Number		
Fittings		Cover Only	Base & Cover	Color
Internal Elbow Full capacity 1¼ in. bend radius internal elbow.		PS3IE A: 4.36" (110.74) B: 6.93" (176.02) C: 4.36" (110.74)	PS3IEBC A: 4.36" (110.74) B: 6.93" (176.02) C: 4.36" (110.74)	Office White
External Elbow Full capacity 1¼ in. bend radius external elbow.		PS3EE A: 6.81" (172.97) B: 6.93" (176.02) C: 6.81" (172.97)	PS3EEBC A: 6.81" (172.97) B: 6.93" (176.02) C: 6.81" (172.97)	Office White

		Catalog Number		
Fittings		Cover Only	Base & Cover	Color
Flat Elbow Full capacity 1¼ in. bend radius flat elbow.		PS3FE A: 9.85" (250.19) B: 9.85" (250.19) C: 2.08" (52.83)	PS3FEBC A: 9.85" (250.19) B: 9.85" (250.19) C: 2.08" (52.83)	Office White
Tee Full capacity 1¼ in. bend radius tee.			PS3TCBC A: 10.00" (254.00) B: 9.68" (245.87) C: 3.30" (83.82)	Office White
Splice Cover For covering potential openings where two lengths of raceway come together.		PS3SC A: 1.56" (39.62) B: 6.95" (176.53) C: 2.03" (51.62)		Office White
Safety Strap Prevents potential tampering with PS3 Super BaseTrak cover. Can also be used as a splice cover.		PS3SS A: 1.50" (38.10) B: 8.24" (209.30) C: 2.08" (52.85)		Office White
End Cap For closing end of PS3 Super BaseTrak Raceway.		PS3EC A: 1.50" (38.10) B: 6.88" (174.75) C: 2.06" (52.32)		Office White
Reducer Reduces from PS3 Super BaseTrak Raceway to PB3 BaseTrak Raceway.			PS3RED A: 4.81" (122.17) B: 6.93" (176.02) C: 2.05" (52.07)	Office White
Conduit Adapter/Ceiling Fitting For connecting conduit to raceway. Also use for ceiling feeds.			PS3CACF A: 6.93" (176.02) B: 4.32" (109.73) C: 6.29" (159.77)	Office White
Surface Panel Connector To connect PS3 Raceway with surface type panel boxes.		PS3SPC A: 1.00" (25.40) B: 7.87" (199.90) C: 2.54" (64.52)		Office White

Non-Metallic PlugTrak®








Non-Metallic PlugTrak® - 5 Ft. Base and Cover

Catalog Numbers	Amps	Circuits	# Duplex Receptacles	Receptacle Spacing (in)
PT155112	15	Single	5	12"
PT155212	15	Two	5	12"
PT155115	15	Single	4	15"
PT155130	15	Single	2	30"
PT205112	20	Single	5	12"
PT205212	20	Two	5	12"
PT205115	20	Single	4	15"
PT205215	20	Two	4	15"
PT205130	20	Single	2	30"



Non-Metallic PlugTrak® - 6 Ft. Base and Cover

Catalog Numbers	Amps	Circuits	# Duplex Receptacles	Receptacle Spacing (in)
PT156112	15	Single	6	12"
PT156212	15	Two	6	12"
PT156118	15	Single	4	18"
PT156124	15	Single	3	24"
PT206106	20	Single	12	6"
PT206206	20	Two	12	6"
PT206112	20	Single	6	12"
PT206212	20	Two	6	12"
PT206118	20	Single	4	18"
PT206218	20	Two	4	18"
PT206124	20	Single	3	24"
PT206224	20	Two	3	24"
PT206136	20	Single	2	36"



Non-Metallic Portable PlugTrak®




Catalog Numbers	Amp	Length	Cord Length	# Duplex Receptacles
PT153112P	15	3 Foot	6 Foot	3
PT155112P	15	5 Foot	6 Foot	5
PT203112P	20	3 Foot	6 Foot	3
PT205112P	20	5 Foot	6 Foot	5

PL1MC (Mounting Clip)


Plates and Outlets for Non-Metallic Raceway

UL CSA UL Listed, CSA Certified

One-Gang Flush "KP" Plates



One-Gang Smooth "DP" Plates




Communication Outlets



Plates and Frame Modules

Front loading plate will accept any modules in three unit combinations. Angled fixtures to be used in bottom opening only.



Keystone Opening


Hole size for mounting all Hubbell Jacks



A: .580 in. (14.73)
B: .760 in. (19.30)

Snap-In Connector Fittings (flush outlets) and Outlet Plates

Snap-in connectors to be used with DP, DF, HPS1DOW, P8DOW and communication inserts. Not recommended for use with KP plates.



SC Duplex Adapter Use with plate and frame modules only.

SIFSC




SC to ST Duplex Adapter Use with plate and frame modules only.

SIFSCST



Communication Outlets (Jacks)



Jack Color Options (replaces "OW" Suffix)

OW = Office White
BK = Black
OR = Orange
B = Blue
R = Red
AL = Almond
GY = Gray
W = White
EI = Elec. Ivory
GN = Green
Y = Yellow

Technical Data - Non-Metallic Surface Raceway

Non–Metallic Raceway Wire Fill Capacities														
			Power (THHN/T90 Nylon)			Voice		Data (Copper Cables)				Data (Multimode Fiber Optic Cables)		
			14 AWG	12AWG	10AWG	4–Pair	25–Pair	Type RG59U	Category 5e	Category 6	Augmented Cat 6	(2) or (4) Fiber Round Cable	Fiber Optic Jumpers	Fiber Optic Zip Cord
			Wire O.D. (in.):			0.19	0.41	0.242	0.21	0.25	0.35	0.19	0.118	.12 X .24
			Wire Area (sq. in.):			0.0283	0.1320	0.0460	0.0346	0.0491	0.0962	0.0283	0.0109	0.0288
Series	Channel	Channel Area (sq. in.)	UL Temperature Rise Test			40%	40%	40%	40%	40%	40%	40%	40%	40%
PT1	A	0.29	5	8	5	4	1	3	3	2	1	4	11	4
PP1	A	0.38	12	11	8	5	1	3	4	3	2	5	14	5
PL1	A	1.03	42	34	22	15	3	9	12	8	4	15	38	14
PW2	A+B	1.6	41	36	22	23	5	14	18	13	7	23	59	22
A B	A	0.81	12	22	12	11	2	7	9	7	3	11	30	11
	B	0.79	12	22	10	11	2	7	9	6	3	11	29	11
PB2	A+B	5.72	60	36	45	81	17	50	66	47	24	81	210	79
A B	A or B	2.86	42	30	28	40	9	25	33	23	12	40	105	40
PB3	A+B+C	5.57	60	36	45	79	17	48	64	45	23	79	204	77
A B C	A or C	1.8	42	30	28	25	5	16	21	15	7	25	66	25
	B	1.97	42	30	28	28	6	17	23	16	8	28	72	27
PS3	A+B+C	10.58	72	66	78	150	32	92	122	86	44	150	388	147
A B C	A or C	3.41	42	36	42	48	10	30	39	28	14	48	125	47
	B	3.76	42	36	42	53	11	33	43	31	16	53	138	52
Note: Pathway (Raceway) fill shall be 40% Maximum. Raceway fittings and outlets/receptacles reduce the cross section of the raceway system, thus reducing overall cable fill capacity.														

Note: Pathway (Raceway) fill shall be 40% Maximum. Raceway fittings and outlets/receptacles reduce the cross section of the raceway system, thus reducing overall cable fill capacity.

Physical Properties

(When tested in accordance with UL 5A)
Impact Resistance5 ft. lbs.
Crush Resistance300 lbs.
Temperature Range-25.6° to 158° F
Flame RatingUL94V-0
MaterialUV Stabilized PVC

Codes/Standards

NEC Article388
EIA/TIA569A
UL StandardUL 5A
ListingsE118895 / E119190
CSA StandardC22.2 no. 62
CertifiedLR87514

PlugTrak Specifications

NEC Article(s)380
Receptacle RatingNEMA 5-15R & 5-20R
Wire#12 AWG Stranded
Copper
Receptacle FaceThermoplastic

Nobody delivers like Hubbell Commercial Solutions



Hubbell SystemOne. The only Floor Box and FRPT system that uses common covers for a seamless look.




Hubbell provides a complete offering of Fire-Rated Poke-Throughs including flush, pedestal and Hubbell SystemOne options.



Hubbell provides a full offering of Floor Box products including large capacity and Hubbell SystemOne options.



Hubbell offers a line of raised access floor products for computer room environments.



Hubbell Premise Wiring's full line catalog provides complete information on a wide range of Connectivity Solutions and Fiber System products and services.



Hubbell's full line catalog provides the widest variety of industrial and commercial products available.



Hubbell Wiring Device-Kellems
Hubbell Incorporated (Delaware)
185 Plains Road • Milford, CT 06461-2420
(203) 882-4800 • Fax (800) 255-1031
Internet site: www.hubbell-wiring.com

Hubbell Premise Wiring

Hubbell Incorporated (Delaware)
14 Lord's Hill Road • Stonington, CT 06378-0901
(860) 535-8326 • (800) 626-0005 • Fax (860) 535-8328
Internet site: www.hubbell-premise.com

Hubbell Canada Inc.

870 Brock Road South • Pickering, Ontario L1W 1Z8
(800) 263-4622 • (905) 839-1138 • Fax (905) 839-9108
Internet site: www.hubbell-canada.com

Hubbell De Mexico, S.A. de C.V.

Ave. Coyoacan No. 1051 • Col. Del Valle C.P. 03100 Mexico D. F.
(01 55) 91 51 99 99 • Fax (01 55) 91 51 99 88
Internet site: www.hubbell.com.mx