






LOC		DIST		REVISIONS					
CM	00	P	LTR	DESCRIPTION			DATE	DWN	APVD
			CI	REVISED PER ECO-11-005027			15MAR2011	RK	HMR



- △ NYLON, UL94V-0, NATURAL.
2. DIMENSIONS IN BRACKETS ARE IN INCHES.
3. FEMALE CONTACTS MUST BE INSERTED SO THAT THE TOP OF THE WIRE AND INSULATION CRIMPS ARE FACING THE CIRCUIT NUMBER OF THE POSITION INTO WHICH IT IS BEING INSERTED OR 180° FROM THE CIRCUIT NUMBER FOR THAT POSITION.



4032.2	24	46.2[1.82]	51.7[2.04]	2-794657-4
3717.6	22	42[1.65]	47.5[1.87]	2-794657-2
3403	20	37.8[1.49]	43.3[1.71]	2-794657-0
3088.5	18	33.6[1.32]	39.1[1.54]	1-794657-8
2774	16	29.4[1.16]	34.9[1.37]	1-794657-6
2459.5	14	25.2[0.99]	30.7[1.21]	1-794657-4
2144.9	12	21[0.83]	26.5[1.04]	1-794657-2
1830.4	10	16.8[0.66]	22.3[0.88]	1-794657-0
1515.9	8	12.6[0.5]	18.1[0.71]	794657-8
1201.3	6	8.4[0.33]	13.9[0.55]	794657-6
886.8	4	4.2[0.17]	9.7[0.38]	794657-4
575.1	2	0[0]	5.5[0.22]	794657-2
VOLUME mm ³		NO. OF POSITIONS		PART NUMBER
		B		A±0.2[.01]

THIS DRAWING IS A CONTROLLED DOCUMENT.				DWN R. WHITAKER 27JUN2007		CASH C. CASH 27JUN2007		APVD C. CASH 27JUN2007		NAME RECEPTACLE HOUSING, 2 TO 24 POSITION, AMP-DUAC(TM) POWER CONNECTOR	
DIMENSIONS: mm[INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC		APPLICATION SPEC		SIZE		CAGE CODE	
9 PLC 1 PLC 2 PLC 3 PLC 4 PLC ANGLES FINISH		±0.2[.01] ±0.2[.01] ±0.13[.005] ± ± ±0°30'		WEIGHT		CUSTOMER DRAWING		A100779		C=794657	
MATERIAL		FINISH		SCALE		SHEET		OF		REV	
				4:1		1		1		C	