


Item no.: 750-613
Product description: POWER SUPPLY PASSIVE DC 24 V



Produkt kann von Bild abweichen / product may differ

Packing unit 1 piece

RoHS compliant

Product group	15 (I/O System)
Voltage supply	DC 24 V (-25% / + 30%)
Current supply (typ)	500 mA
Total current for I/O modules	2000 mA
Voltage supply via power jumper contacts (max)	DC 24 V (-25% / + 30%)
Current via power jumper contacts (max)	10
Operating temperature	0 °C ... + 55 °C
Storage temperature	-25 °C ... +85 °C
Relative air humidity	95 %
Vibration resistance	acc. IEC 60068-2-6
Shock resistance	acc. IEC 60068-2-27
Degree of protection	IP 20
EMC marine applications - noise proof	gem. Germanischer Lloyd (2003)
EMC marine applications - noise transmission	gem. Germanischer Lloyd (2003)
Conformity marking	CE
Approvals	ATEX
Cross section [mm²]	0.08 - 2.5 mm²
Cross section [AWG]	28 - 14 AWG
Connection method	CAGE CLAMP® CONNECTION

Weight
Color
Height

58.5 g
light gray
64 mm



Height	2.52 in
Width	12 mm
Width	0.472 in
Depth	100 mm
Depth	3.937 in
Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35

Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
750-613	ABS	03-HG374860/3-PDA			
750-613	BSH	Bescheinigung Nr. 467			
750-613	BV	13453/C0 BV			
750-613	DNV	A-12306			
750-613	GL	26 898 - 05 HH			
750-613	IECEX	IECEX PTB 07.0064X			
750-613	KR	HMB05880-AC004			
750-613	LR	02/20026 (E2)			
750-613	NK	TA06190M			
750-613	PRS	TE/1720/880590/08			
750-613	Rina	ELE153207CS001			
750-613	UL	E175199 Sec.1			
750-613	UL	E198726 Sec.1			
750-613	UL DEMKO A/S	08 ATEX 142851 X			

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected