




Home: Crimp Housings >

Part Number: 46064-0034

Mini-Fit® H2O Sealed Receptacle Housing Assembly, 4.20mm Pitch, 4 Circuits, Black



Series image - Reference only

Status: **OBsolete**

Replacement: Contact Molex

Series: **46064**

Category: Crimp Housings

Overview: [Mini-Fit® H2O Sealed](#)[Interconnect System](#)

CHECK DISTRIBUTOR INVENTORY

Add to My Parts

Email this page

Go to [Part Detail](#) ▾

Mates With Part(s):

[46065-0034](#) Plug Assembly

Use With Part(s):

[46055-0005](#) Terminal, [46055-0006](#) Terminal**Product Environmental Compliance**[EU ELV](#): Product not active[EU RoHS](#): Product not active[EU RoHS Phthalates](#): Product not active[China RoHS](#):[REACH SVHC](#): Product not active[Low-Halogen Status](#): Product not active

EU RoHS Certificate of Compliance (PDF)

Multiple Part Product Compliance Statements

EU RoHS, REACH SVHC, & Low-Halogen

Multiple Part Industry Compliance Documents

*IPC 1752A Class C

*IPC 1752A Class D

*Molex Product Compliance Declaration

Application Tooling**FAQ**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

Previously Available Application Tooling[Check our list of old tooling that used to be available for this part](#)Questions on Product Environmental Compliance? Email ProductCompliance@molex.comRequest Molex's CMRT from conflictminerals@molex.com**Part Detail****COLLAPSE ALL****▼ General**

Status	Obsolete
Category	Crimp Housings
Series	46064
Application	Power
Overview	Mini-Fit® H2O Sealed Interconnect System
Product Name	Mini-Fit® H2O
UPC	800756695440

▼ Physical

Circuits (maximum)	4
Color - Resin	Orange
Flammability	94V-0
Gender	Receptacle
Glow-Wire Compliant	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Net Weight	6.828/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	4.20mm
Pitch - Termination Interface	4.20mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40°C to +105°C

▼ Electrical

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	9.0A
-------------------------------	------

▼ Agency Certification

Please find UL Certificates by searching the UL Database using the Molex Series Number.

[Click here to visit the UL Database](#)

CSA	LR19980
UL	E29179

▼ Solder Process Data

Solderability Shelf Life Statement	
Lead-free Process Capability	N/A

Molex is a registered trademark of Molex, LLC in the United States of America and may be registered in other countries; all other trademarks listed herein belong to their respective owners.

© Copyright 2017

Molex.com

Molex.com