



DB25F PIN-OUT VIEW

DB25F AND XLRF WIRING CHART					
XLR (CHANNEL)	XLR (DESC.)	CABLE (COLOR)	PIN 2 (RED)	PIN 3 (BLACK)	PIN 1 (BARE)
1	XLRF	BROWN	24	12	25
2	XLRF	RED	10	23	11
3	XLRF	ORANGE	21	9	22
4	XLRF	YELLOW	7	20	8
5	XLRF	GREEN	18	6	19
6	XLRF	BLUE	4	17	5
7	XLRF	PURPLE	15	3	16
8	XLRF	GRAY	1	14	2

NOTES:

1. BREAKOUT CABLE LENGTH: 18 +/- 0.75 INCHES. SEE TABLE FOR COLOR.

B 2. THIS PRODUCT COMES COILED AND PACKAGED IN BAG.

B 3. MATERIALS:
XLR FEMALE CONNECTOR:
HANDLE - ZINC ALLOY, NICKEL PLATED
HOUSING AND LATCH - ZINC ALLOY, NICKEL PLATED
INSULATOR - THERMOPLASTIC, GREEN
SOCKET CONTACTS - SPECIAL COPPER ALLOY, SILVER PLATED
H.S. TUBING - THERMOPLASTIC
DSUB:
CABLE CLAMP - COPPER, NICKEL PLATED
SHELL - STEEL, TIN PLATED
INSULATORS - THERMOPLASTIC
SCREW LOCKS - BRASS, NICKEL PLATED

4. THIS PRODUCT IS RoHS COMPLIANT.

CUSTOMER DRAWING

					<div>UNLESS OTHERWISE SPECIFIED</div> <div>1. ALL DIMENSIONS IN INCHES [mm]</div> <div>- TWO PLACE DECIMALS ±0.02 [0.5]</div> <div>- THREE PLACE DECIMALS ±0.005 [0.13]</div>	THIS DRAWING DESCRIBES A DESIGN CONSIDERED PROPRIETARY IN NATURE, DEVELOPED AND MANUFACTURED BY SWITCHCRAFT INC. AND IS RELEASED ON A CONFIDENTIAL BASIS FOR IDENTIFICATION PURPOSES ONLY.																	
						SIZE	WIDTH		MULT		LBS/M		TEMPER										
						FINISH SPEC No.						MATERIAL SPEC No.											
C	27520	06/08/15	PC	TJK		FIRST USED ON				SCALE 1:2				<div>Switchcraft®</div>									
B	26637	10/4/10	RS	TJK		DATE DRAWN	BY	CHKD		APVD													
A	26568	7/20/10	RS	TJK		7/16/09	JGK	RS 12/1/10		TJK 12/1/10		SHEET 1 OF 1											
REV	ECO NUMBER	DATE	BY	APVD	NAME						PART No.						REV						
REVISIONS					DO NOT SCALE DRAWING					DB25F TO 8-XLRF, RoHS						DB25FXLRF						C	