




Power Wirewound Resistors, ceramic case, radial

Specifications

Type		KWP 330-3/5/7	KWP 331-3/5/7	KWP 332-3/5/7	KWP 333-3/5/7	KWP 335-3/5/7	KWP 336-3/5/7	KWP 337-3/5/7	KWP 338-3/5/7
Nominal Power rating P_{25}		3,0	4,0	5,0	7,0	9,0	10,0	15,0	20,0
P_{70}	W	2,0	2,2	2,5	3,0	4,5	4,5	5,5	8,0
Resistance range	Ω	0R2 ... 2K4	0R22 ... 3K	0R3 ... 3K6	0R43 ... 4K7	0R56 ... 5K6	0R68 ... 6K8	0R62 ... 7K5	0R91 ... 10K
E-series		E24 (5%), E12 (10%)							
Tolerances	%	± 5 , ± 10							
Temperature coefficient	$10^{-6} \cdot K^{-1}$	- 80 ... +500 depends on value							
Max. cont. working voltage	V_{RMS}	$\sqrt{P_{70} \cdot R}$ for all styles							
Insulation voltage (1min.)	V_{RMS}	2000							
Insulation resistance	Ω	$> 10^4 M$							
Derating linear	$^{\circ}C$	Linear 70 ... 275 (0W)							
Climatic category		55/200/56							
Temperature range	$^{\circ}C$	-55...275							
Thermal resistance	KW^{-1}	37	35	35	35	35	30	20	14
Failure Rate (Total ϑ_0 max, 60% conf. lev.)	$10^{-9} \cdot h^{-1}$	Apr. 100, depends on value							
Endurance (P_{70} , @70 $^{\circ}C$, 1000h)	$[\Delta R/R]$ %	$\pm 3,0$ average							
Damp heat, steady state (40 $^{\circ}C$, 93% r.h., 56d)	$[\Delta R/R]$ %	$\pm 2,0$							
Resistance to soldering heat (260 $^{\circ}C$, 10s)	$[\Delta R/R]$ %	$\pm 0,5$							
Solderability	S	2,5 Flowtime, solderglobule test, IEC 60068-2-20-T							
Marking		printed in clear							

Dimensions in mm:



Type	L	B	RM
KWP 330-3/5/7	23,0	10,0	10,0
KWP 331-3/5/7	25,0	10,0	12,5
KWP 332-3/5/7	28,0	10,0	15,0
KWP 333-3/5/7	35,5	10,0	22,5
KWP 335-3/5/7	43,0	10,0	30,0
KWP 336-3/5/7	48,0	10,0	35,0
KWP 337-3/5/7	50,0	13,0	32,5
KWP 338-3/5/7	65,0	13,0	47,5

Packaging:

Type	Packaging	Pieces	Pack.-Code
KWP 330-3/5/7	bulk	144	B
KWP 331-3/5/7	bulk	100	B
KWP 332-3 KWP 332-5/7	bulk	112 128	B
KWP 333-3 KWP 333-5/7	bulk	120 100	B
KWP 335-3 KWP 335-5/7	bulk	150 105	B
KWP 336-3 KWP 336-5 KWP 336-7	bulk	150 120 100	B
KWP 337-3 KWP 337-5 KWP 337-7	bulk	128 50 64	B
KWP 338-3 KWP 338-5/7	bulk	100 48	B

Ordering example: KWP333-3 5 B 0R43
Type Tolerance Pack.-Code R- value

Revision 201201