



Trench gate field-stop 600 V, 20 A high speed IGBT in a TO-247 package


TO-247


NG1E3C2T



Features

- Maximum junction temperature: $T_J = 175\text{ }^{\circ}\text{C}$
- High speed switching
- Tight parameter distribution
- Safe paralleling
- Low thermal resistance
- Short-circuit rated
- Soft and fast recovery antiparallel diode

Applications

- Industrial motor control
- PFC converters, single phase input
- Uninterruptable power supplies (UPS)

Description

This device is an IGBT developed using an advanced proprietary trench gate field-stop structure. This device is part of the H series of IGBTs, which represents an optimum compromise between conduction and switching losses to maximize the efficiency of high switching frequency converters. Furthermore, a slightly positive $V_{CE(sat)}$ temperature coefficient and very tight parameter distribution result in safer paralleling operation.

Product status link

[STGW20H60DF](#)

Product summary

Order code	STGW20H60DF
Marking	GW20H60DF
Package	TO-247
Packing	Tube

1 Electrical ratings

Table 1. Absolute maximum ratings

Symbol	Parameter	Value	Unit
V_{CES}	Collector-emitter voltage ($V_{GE} = 0$)	600	V
I_C	Continuous collector current at $T_C = 25\text{ °C}$	40	A
	Continuous collector current at $T_C = 100\text{ °C}$	20	
$I_{CP}^{(1)}$	Pulsed collector current	80	A
V_{GE}	Gate-emitter voltage	± 20	V
I_F	Continuous forward current $T_C = 25\text{ °C}$	40	A
	Continuous forward current at $T_C = 100\text{ °C}$	20	
I_{FP}	Pulsed forward current	80	A
P_{TOT}	Total power dissipation at $T_C = 25\text{ °C}$	167	W
T_{STG}	Storage temperature range	-55 to 150	°C
T_J	Operating junction temperature range	-55 to 175	

1. Limited by maximum junction temperature.
2. Pulse width limited by maximum junction temperature and turn-off within RBSOA.

Table 2. Thermal data

Symbol	Parameter	Value	Unit
R_{thJC}	Thermal resistance, junction-to-case, IGBT	0.9	°C/W
R_{thJC}	Thermal resistance, junction-to-case, diode	2.5	°C/W
R_{thJA}	Thermal resistance, junction-to-ambient	50	°C/W

2 Electrical characteristics

$T_C = 25\text{ °C}$ unless otherwise specified.

Table 3. Static

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$V_{(BR)CES}$	Collector-emitter breakdown voltage	$V_{GE} = 0\text{ V}$, $I_C = 2\text{ mA}$	600	-	-	V
$V_{CE(sat)}$	Collector-emitter saturation voltage	$V_{GE} = 15\text{ V}$, $I_C = 20\text{ A}$	-	1.6	2.0	V
		$V_{GE} = 15\text{ V}$, $I_C = 20\text{ A}$, $T_J = 125\text{ °C}$	-	1.75	-	
		$V_{GE} = 15\text{ V}$, $I_C = 20\text{ A}$, $T_J = 175\text{ °C}$	-	1.8	-	
$V_{GE(th)}$	Gate threshold voltage	$V_{CE} = V_{GE}$, $I_C = 1\text{ mA}$	5	6	7	V
I_{CES}	Collector cut-off current	$V_{CE} = 600\text{ V}$, $V_{GE} = 0\text{ V}$	-	-	25	μA
I_{GES}	Gate-emitter leakage current	$V_{GE} = \pm 20\text{ V}$, $V_{CE} = 0\text{ V}$	-	-	± 250	nA

Table 4. Dynamic

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
C_{ies}	Input capacitance	$V_{CE} = 25\text{ V}$, $f = 1\text{ MHz}$, $V_{GE} = 0\text{ V}$	-	2750	-	pF
C_{oes}	Output capacitance			110		
C_{res}	Reverse transfer capacitance			65		
Q_g	Total gate charge	$V_{CC} = 400\text{ V}$, $I_C = 20\text{ A}$, $V_{GE} = 0\text{ to }15\text{ V}$ (see the Figure 20. Gate charge test circuit)	-	115	-	nC
Q_{ge}	Gate-emitter charge			22		
Q_{gc}	Gate-collector charge			45		

Table 5. Switching characteristics (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
$t_{d(on)}$	Turn-on delay time	$V_{CE} = 400\text{ V}$, $I_C = 20\text{ A}$, $R_G = 10\text{ }\Omega$, $V_{GE} = 15\text{ V}$ (see the Figure 19. Test circuit for inductive load switching and Figure 21. Switching waveform)	-	42.5	-	ns
t_r	Current rise time			11.9		
$(di/dt)_{on}$	Turn-on current slope			1345		A/ μs
$t_{r(Voff)}$	Off voltage rise time			20		ns
$t_{d(off)}$	Turn-off delay time			177		
t_f	Current fall time			55		
$t_{d(on)}$	Turn-on delay time	$V_{CE} = 400\text{ V}$, $I_C = 20\text{ A}$, $R_G = 10\text{ }\Omega$, $V_{GE} = 15\text{ V}$, $T_J = 175\text{ °C}$ (see the Figure 19. Test circuit for inductive load switching and Figure 21. Switching waveform)	-	42.5	-	ns
t_r	Current rise time			13.4		
$(di/dt)_{on}$	Turn-on current slope			1180		A/ μs
$t_{r(Voff)}$	Off voltage rise time			26		ns
$t_{d(off)}$	Turn-off delay time			173		
t_f	Current fall time			86		
t_{sc}	Short-circuit withstand time	$V_{CC} \leq 360\text{ V}$, $V_{GE} = 15\text{ V}$, $R_G = 10\text{ }\Omega$	3	5	-	μs

Table 6. Switching energy (inductive load)

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
E _{on} ⁽¹⁾	Turn-on switching energy	V _{CE} = 400 V, I _C = 20 A, R _G = 10 Ω, V _{GE} = 15 V	-	209	-	μJ
E _{off} ⁽²⁾	Turn-off switching energy			261		
E _{ts}	Total switching energy			470		
E _{on} ⁽¹⁾	Turn-on switching energy	V _{CE} = 400 V, I _C = 20 A, R _G = 10 Ω, V _{GE} = 15 V, T _J = 175 °C		480		
E _{off} ⁽²⁾	Turn-off switching energy			416		
E _{ts}	Total switching energy			896		

1. Including the reverse recovery of the diode.

2. Including the tail of the collector current.

Table 7. Collector-emitter diode

Symbol	Parameter	Test conditions	Min.	Typ.	Max.	Unit
V_F	Forward on-voltage	$I_F = 20\text{ A}$	-	1.8	2.2	V
		$I_F = 20\text{ A}$, $T_J = 175\text{ }^\circ\text{C}$	-	1.3	-	
t_{rr}	Reverse recovery time	$V_r = 60\text{ V}$; $I_F = 20\text{ A}$; $di_F/dt = 100\text{ A}/\mu\text{s}$	-	90	-	ns
Q_{rr}	Reverse recovery charge		-	110	-	nC
I_{rrm}	Reverse recovery current		-	2.4	-	A
t_{rr}	Reverse recovery time	$V_{CC} = 400\text{ V}$; $I_F = 20\text{ A}$; $di_F/dt = 100\text{ A}/\mu\text{s}$, $T_J = 175\text{ }^\circ\text{C}$	-	180	-	ns
Q_{rr}	Reverse recovery charge		-	466	-	nC
I_{rrm}	Reverse recovery current		-	5.2	-	A

2.1 Electrical characteristics (curves)







Figure 1. Total power dissipation vs temperature

Figure 2. Collector current vs case temperature

Figure 3. Output characteristics ($T_J = 25^\circ\text{C}$)

Figure 4. Output characteristics ($T_J = 175^\circ\text{C}$)

Figure 5. Collector current vs. switching frequency

Figure 6. Capacitance variation















Figure 7. $V_{CE(sat)}$ vs junction temperature

Figure 8. $V_{CE(sat)}$ vs collector current

Figure 9. Forward bias safe operating area

Figure 10. Thermal impedance for IGBT

Figure 11. Transfer characteristics

Figure 12. Diode V_F vs forward current


Figure 13. Normalized $V_{GE(th)}$ vs junction temperature

Figure 14. Short-circuit time and current vs V_{GE}

Figure 15. Gate charge vs. gate-emitter voltage

Figure 16. Switching energy vs collector current

Figure 17. Switching energy vs gate resistance

Figure 18. Switching energy vs temperature



3 Test circuits

Figure 19. Test circuit for inductive load switching




AM01504v1

Figure 20. Gate charge test circuit




AM01505v1

Figure 21. Switching waveform



AM01506v1

Figure 22. Diode reverse recovery waveform




AM01507v1

4 Package information

To meet environmental requirements, ST offers these devices in different grades of **ECOPACK** packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions, and product status are available at: www.st.com. ECOPACK is an ST trademark.

4.1 TO-247 package information

Figure 23. TO-247 package outline



0075325_10

Table 8. TO-247 package mechanical data

Dim.	mm		
	Min.	Typ.	Max.
A	4.85		5.15
A1	2.20		2.60
b	1.0		1.40
b1	2.0		2.40
b2	3.0		3.40
c	0.40		0.80
D	19.85		20.15
E	15.45		15.75
e	5.30	5.45	5.60
L	14.20		14.80
L1	3.70		4.30
L2		18.50	
ØP	3.55		3.65
ØR	4.50		5.50
S	5.30	5.50	5.70
aaa		0.04	0.10

Revision history

Table 9. Document revision history

Date	Version	Changes
06-Jun-2013	1	First release.
25-Jun-2024	2	Removed part number STGWT20H60DF. Updated Section 4: Package information .

Contents

1	Electrical ratings	2
2	Electrical characteristics.....	3
2.1	Electrical characteristics (curves)	5
3	Test circuits	8
4	Package information.....	9
4.1	TO-247 package information	9
	Revision history	11

IMPORTANT NOTICE – READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgment.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, refer to www.st.com/trademarks. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2025 STMicroelectronics – All rights reserved