


## Advanced IGBT/MOSFET driver

### Features

- 1.7 A sink / 1.3 A source (typ) current capability
- Active Miller clamp feature
- Two-level turn-off with adjustable level and delay
- Input compatible with pulse transformer or optocoupler
- UVLO protection
- 2 kV ESD protection



The TD351 is compatible with both pulse transformer and optocoupler signals.

### Applications

- 1200 V 3-phase inverters
- Motor control systems
- UPS

### Description

This device is an advanced gate driver for IGBT and power MOSFETs. Control and protection functions are included and allow the design of high reliability systems.

The innovative active Miller clamp function eliminates the need for negative gate drive in most applications and allows the use of a simple bootstrap supply for the high side driver.

The TD351 includes a two-level turn-off feature with adjustable level and delay. This function protects against excessive overvoltage at turn-off in case of overcurrent or short-circuit conditions. The same delay is applied at turn-on to prevent pulse width distortion.

**Table 1. Device summary**


| Order codes | Temperature range | Package | Packaging     |
|-------------|-------------------|---------|---------------|
| TD351ID     | -40°C, +125°C     | SO-8    | Tube          |
| TD351IDT    |                   |         | Tape and reel |

# Contents

|           |                                   |           |
|-----------|-----------------------------------|-----------|
| <b>1</b>  | <b>Block diagram</b>              | <b>3</b>  |
| <b>2</b>  | <b>Pin connections</b>            | <b>4</b>  |
| <b>3</b>  | <b>Absolute maximum ratings</b>   | <b>5</b>  |
| <b>4</b>  | <b>Electrical characteristics</b> | <b>6</b>  |
| <b>5</b>  | <b>Functional description</b>     | <b>8</b>  |
| 5.1       | Input stage                       | 8         |
| 5.2       | Voltage reference                 | 8         |
| 5.3       | Active Miller clamp               | 8         |
| 5.4       | Two level turn-off                | 8         |
| 5.5       | Minimum input ON-time             | 9         |
| 5.6       | Output stage                      | 9         |
| 5.7       | Undervoltage protection           | 9         |
| <b>6</b>  | <b>Timing diagrams</b>            | <b>12</b> |
| <b>7</b>  | <b>Typical performance curves</b> | <b>14</b> |
| <b>8</b>  | <b>Application diagrams</b>       | <b>16</b> |
| <b>9</b>  | <b>Package mechanical data</b>    | <b>17</b> |
| <b>10</b> | <b>Revision history</b>           | <b>18</b> |

# 1 Block diagram

Figure 1. TD351 block diagram



## 2 Pin connections

Figure 2. Pin connections (top view)




Table 2. Pin description

| Pin n° | Name  | Type             | Function               |
|--------|-------|------------------|------------------------|
| 1      | IN    | Analog input     | Input                  |
| 2      | VREF  | Analog output    | +5 V reference voltage |
| 3      | CD    | Timing capacitor | Turn on/off delay      |
| 4      | LVOFF | Analog input     | Turn off level         |
| 5      | CLAMP | Analog output    | Miller clamp           |
| 6      | VL    | Power supply     | Signal ground          |
| 7      | OUT   | Analog output    | Gate drive output      |
| 8      | VH    | Power supply     | Positive supply        |

### 3 Absolute maximum ratings

**Table 3. Absolute maximum ratings**

| Symbol             | Parameter                                                 | Value                                      | Unit |
|--------------------|-----------------------------------------------------------|--------------------------------------------|------|
| V <sub>H</sub> L   | Maximum supply voltage (V <sub>H</sub> - V <sub>L</sub> ) | 28                                         | V    |
| V <sub>out</sub>   | Voltage on OUT, CLAMP, LVOFF pins                         | V <sub>L</sub> -0.3 to V <sub>H</sub> +0.3 | V    |
| V <sub>other</sub> | Voltage on other pins (IN, CD, VREF)                      | -0.3 to 7                                  | V    |
| P <sub>d</sub>     | Power dissipation                                         | 500                                        | mW   |
| T <sub>stg</sub>   | Storage temperature                                       | -55 to 150                                 | °C   |
| T <sub>j</sub>     | Maximum junction temperature                              | 150                                        | °C   |
| R <sub>thJA</sub>  | Thermal resistance junction-ambient                       | 150                                        | °C/W |
| ESD                | Electrostatic discharge (HBM)                             | 2                                          | kV   |

**Table 4. Operating conditions**

| Symbol            | Parameter                                  | Value      | Unit |
|-------------------|--------------------------------------------|------------|------|
| V <sub>H</sub>    | Positive supply voltage vs. V <sub>L</sub> | UVLO to 26 | V    |
| T <sub>oper</sub> | Operating free air temperature range       | -40 to 125 | °C   |

## 4 Electrical characteristics

$T_A = -20$  to  $125^\circ\text{C}$ ,  $V_H = 16\text{ V}$ , unless otherwise specified.

**Table 5. Electrical characteristics**

| Symbol                                  | Parameter                                 | Test condition                                                                                             | Min         | Typ   | Max        | Unit                |
|-----------------------------------------|-------------------------------------------|------------------------------------------------------------------------------------------------------------|-------------|-------|------------|---------------------|
| <b>Input</b>                            |                                           |                                                                                                            |             |       |            |                     |
| $V_{\text{ton}}$                        | IN turn-on threshold voltage              |                                                                                                            | 0.8         | 1.0   |            | V                   |
| $V_{\text{toff}}$                       | IN turn-off threshold voltage             |                                                                                                            |             | 4.0   | 4.2        | V                   |
| $t_{\text{onmin}}$                      | Minimum pulse width                       |                                                                                                            | 100         | 135   | 220        | ns                  |
| $I_{\text{inp}}$                        | IN input current                          | IN input voltage < 4.5V                                                                                    |             |       | 1          | $\mu\text{A}$       |
| <b>Voltage reference <sup>(1)</sup></b> |                                           |                                                                                                            |             |       |            |                     |
| $V_{\text{ref}}$                        | Voltage reference                         | $T = 25^\circ\text{C}$                                                                                     | 4.85        | 5.00  | 5.15       | V                   |
| $I_{\text{ref}}$                        | Maximum output current                    |                                                                                                            | 10          |       |            | mA                  |
| <b>Clamp</b>                            |                                           |                                                                                                            |             |       |            |                     |
| $V_{\text{tclamp}}$                     | CLAMP pin voltage threshold               |                                                                                                            |             | 2.0   |            | V                   |
| $V_{\text{CL}}$                         | Clamp low voltage                         | $I_{\text{csink}} = 500\text{mA}$                                                                          |             |       | 2.5        | V                   |
| <b>Delay</b>                            |                                           |                                                                                                            |             |       |            |                     |
| $V_{\text{tdel}}$                       | Voltage threshold                         |                                                                                                            |             | 2.5   |            | V                   |
| $R_{\text{del}}$                        | Discharge resistor                        | $I = 1\text{mA}$                                                                                           |             |       | 500        |                     |
| <b>Off Level</b>                        |                                           |                                                                                                            |             |       |            |                     |
| $I_{\text{blvoff}}$                     | LVOFF peak input current (sink)           | LVOFF = 12V                                                                                                |             | 90    | 200        | $\mu\text{A}$       |
| $V_{\text{iolv}}$                       | Offset voltage                            | LVOFF = 12V                                                                                                | -0.3        | -0.15 | 0          | V                   |
| <b>Output</b>                           |                                           |                                                                                                            |             |       |            |                     |
| $I_{\text{sink}}$                       | Output sink current                       | $V_{\text{out}} = 6\text{V}$                                                                               | 1000        | 1700  |            | mA                  |
| $I_{\text{src}}$                        | Output source current                     | $V_{\text{out}} = V_H - 6\text{V}$                                                                         | 750         | 1300  |            | mA                  |
| $V_{\text{OL1}}$                        | Output low voltage 1                      | $I_{\text{osink}} = 20\text{mA}$                                                                           |             |       | 0.35       | V                   |
| $V_{\text{OL2}}$                        | Output low voltage 2                      | $I_{\text{osink}} = 500\text{mA}$                                                                          |             |       | 2.5        | V                   |
| $V_{\text{OH1}}$                        | Output high voltage 1                     | $I_{\text{osource}} = 20\text{mA}$                                                                         | $V_H - 2.5$ |       |            | V                   |
| $V_{\text{OH2}}$                        | Output high voltage 2                     | $I_{\text{osource}} = 500\text{mA}$                                                                        | $V_H - 4.0$ |       |            | V                   |
| $t_r$                                   | Rise time                                 | $C_L = 1\text{nF}$ , 10% to 90%                                                                            |             |       | 100        | ns                  |
| $t_f$                                   | Fall time <sup>(2)</sup>                  | $C_L = 1\text{nF}$ , 90% to 10%                                                                            |             |       | 100        | ns                  |
| $t_{\text{don}}$                        | Turn on propagation delay                 | 10% OUT change:<br>$R_d = 4.7\text{k}\Omega$ , no $C_d$<br>$R_d = 10\text{k}\Omega$ , $C_d = 220\text{pF}$ | 1.8         | 2.0   | 600<br>2.2 | ns<br>$\mu\text{s}$ |
| $t_{\text{doff}}$                       | Turn off propagation delay <sup>(2)</sup> | 10% OUT change                                                                                             |             |       | 550        | ns                  |

Table 5. Electrical characteristics (continued)

| Symbol                              | Parameter                        | Test condition                                       | Min | Typ | Max | Unit |
|-------------------------------------|----------------------------------|------------------------------------------------------|-----|-----|-----|------|
| $\Delta t_w$                        | Input to output pulse distortion | 10% OUT change,<br>$\Delta t_w = T_{wout} - T_{win}$ |     | 50  | 100 | ns   |
| <b>Under voltage lockout (UVLO)</b> |                                  |                                                      |     |     |     |      |
| UVLOH                               | UVLO top threshold               |                                                      | 10  | 11  | 12  | V    |
| UVLOL                               | UVLO bottom threshold            |                                                      | 9   | 10  | 11  | V    |
| $V_{hyst}$                          | UVLO hysteresis                  | UVLOH-UVLOL                                          | 0.5 | 1   |     | V    |
| <b>Supply current</b>               |                                  |                                                      |     |     |     |      |
| $I_{in}$                            | Quiescent current                | OUT = 0V; no load                                    |     |     | 2.5 | mA   |

1. Recommended capacitor range on VREF pin is 10 nF to 100 nF
2. 2 step turn-off disabled.

## 5 Functional description

### 5.1 Input stage

The TD351 input is compatible with optocouplers or pulse transformers. The input is triggered by the signal edge and allows the use of low-sized, low-cost pulse transformers. Input is active low and output is driven high when input is driven low. The IN input is internally clamped at about 5 V to 7 V. When using an open collector optocoupler, the resistive pull-up resistor can be connected to either VREF or VH. Recommended pull-up resistor value with  $V_H = 16\text{ V}$  is from 4.7 k $\Omega$  to 22 k $\Omega$ . When driven by a pulse transformer, the input positive and negative pulse widths at the  $V_{\text{ton}}$  and  $V_{\text{toff}}$  threshold voltages must be larger than the minimum pulse width  $t_{\text{onmin}}$  (see [Figure 6](#)). This feature acts as a filter against invalid input pulses smaller than  $t_{\text{onmin}}$ .

### 5.2 Voltage reference

A voltage reference is used to create accurate timing for the turn-on delay with external resistor and capacitor. The same circuitry is also used for the two-level turn-off delay. A decoupling capacitor (10 nF to 100 nF) on the VREF pin is required to ensure good noise rejection.

### 5.3 Active Miller clamp

The TD351 offers an alternative solution to the problem of Miller current in IGBT switching applications. Instead of driving the IGBT gate to a negative voltage to increase the safety margin, the TD351 uses a dedicated CLAMP pin to control the Miller current. When the IGBT is off, a low impedance path is established between the IGBT gate and emitter to carry the Miller current, and the voltage spike on the IGBT gate is greatly reduced. During turn-off, the gate voltage is monitored and the clamp output is activated when the gate voltage goes below 2 V (relative to VL). The clamp voltage is  $V_L + 4\text{ V}$  max for a Miller current up to 500 mA. The clamp is disabled when the IN input is triggered again.

The CLAMP function does not affect the turn-off characteristic, but only keeps the gate at low level throughout the OFF-time. The main benefit is that negative voltage can be avoided in many cases, allowing a bootstrap technique for the high side driver supply.

### 5.4 Two-level turn-off

During turn-off, the gate voltage can be reduced to a programmable level in order to reduce the IGBT current (in the event of overcurrent). This action prevents both dangerous overvoltages across the IGBT and RBSOA problems, especially at short-circuit turn-off.

The turn-off ( $T_a$ ) delay is programmable through external resistor  $R_d$  and capacitor  $C_d$  for accurate timing.

$T_a$  is approximately given by (see [Figure 5](#)):

$$T_a(\mu s) = 0.7 \cdot R_d(k\Omega) \cdot C_d(nF)$$

The turn-off delay ( $T_a$ ) is also used to delay the input signal to prevent distortion of input pulse width.

The two-level turn-off sequence can be disabled by connecting the LVOFF pin to VH and connecting the CD pin to VREF with a 4.7 k $\Omega$  resistor.

## 5.5 Minimum input ON-time

Input signals with ON-time smaller than  $T_a$  are ignored.

ON-time signals larger than  $T_a + 2 \cdot R_{del} \cdot C_d$  ( $R_{del}$  is the internal discharge switch resistance,  $C_d$  is the external timing capacitor) are transmitted to the output stage after the  $T_a$  delay, with minimum width distortion ( $\Delta T_w = T_{wout} - T_{win}$ ).

For ON-time input signals close to  $T_a$  (between  $T_a$  and  $T_a + 2 \cdot R_{del} \cdot C_d$ ), the two-level duration is slightly reduced and the total output width can be smaller than the input width (see [Figure 7](#)).

## 5.6 Output stage

The output stage is able to sink/source 1.7 A/1.3 A (typical) at 25 °C and 1.0 A/0.75 A min. over the full temperature range. This current capability is specified near the usual IGBT Miller plateau.

## 5.7 Undervoltage protection

Undervoltage detection protects the application in the event of a low VH supply voltage (during startup or a fault situation). During undervoltage, the OUT pin is driven low (active pull-down for  $V_H > 2V$ , and passive pull-down for  $V_H < 2V$ ).

The diagram illustrates the timing characteristics of the AM02827 during a voltage ramp-up and ramp-down. The input voltage (VH) is shown as a ramp that rises above the UVLOH threshold, remains there for a period, then falls below the UVLOL threshold, and finally returns above UVLOH. The output (OUT) is high when the input is above UVLOH and low when it is below UVLOL. The fault signal (FAULT) is active-low, going high when the input is between UVLOL and UVLOH, and low when the input is above UVLOH or below UVLOL. The 2V level is indicated as a reference for the output signal.



# 6 Timing diagrams

Figure 5. General turn-on and two-level turn-off sequence






Figure 6. Input and output waveform dynamic parameters



**Figure 7. Minimum ON-time**

# 7 Typical performance curves

Figure 8. Quiescent current vs temperature




Figure 9. Rdel resistance vs temperature




Figure 10. Low level output voltage vs temp.




Figure 11. High level output voltage vs temp.




Figure 12. Sink current vs temperature





Figure 13. Source current vs temperature



## 8 Application diagrams

Figure 14. Single supply IGBT drive with active Miller clamp and opto input signal




Figure 15. Single supply IGBT drive with active Miller clamp and pulse transformer input signal





Figure 16. Large IGBT drive with negative voltage gate drive and optional current buffers




## 9 Package mechanical data

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: [www.st.com](http://www.st.com). ECOPACK® is an ST trademark.

**Table 6. SO-8 mechanical data**

| Dim. | mm.      |      |      | inch  |       |       |
|------|----------|------|------|-------|-------|-------|
|      | Min.     | Typ  | Max. | Min.  | Typ.  | Max.  |
| A    | 1.35     |      | 1.75 | 0.053 |       | 0.069 |
| A1   | 0.10     |      | 0.25 | 0.04  |       | 0.010 |
| A2   | 1.10     |      | 1.65 | 0.043 |       | 0.065 |
| B    | 0.33     |      | 0.51 | 0.013 |       | 0.020 |
| C    | 0.19     |      | 0.25 | 0.007 |       | 0.010 |
| D    | 4.80     |      | 5.00 | 0.189 |       | 0.197 |
| E    | 3.80     |      | 4.00 | 0.150 |       | 0.157 |
| e    |          | 1.27 |      |       | 0.050 |       |
| H    | 5.80     |      | 6.20 | 0.228 |       | 0.244 |
| h    | 0.25     |      | 0.50 | 0.010 |       | 0.020 |
| L    | 0.40     |      | 1.27 | 0.016 |       | 0.050 |
| k    | (max.) 8 |      |      |       |       |       |
| ddd  |          |      | 0.1  |       |       | 0.04  |

**Figure 17. SO-8 mechanical drawing**



## 10 Revision history

**Table 7. Document revision history**

| Date        | Revision | Changes                    |
|-------------|----------|----------------------------|
| 01-Nov-2004 | 1        | Initial release            |
| 16-Jun-2011 | 2        | Removed order code TD351IN |

**Please Read Carefully:**

Information in this document is provided solely in connection with ST products. STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, modifications or improvements, to this document, and the products and services described herein at any time, without notice.

All ST products are sold pursuant to ST's terms and conditions of sale.

Purchasers are solely responsible for the choice, selection and use of the ST products and services described herein, and ST assumes no liability whatsoever relating to the choice, selection or use of the ST products and services described herein.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted under this document. If any part of this document refers to any third party products or services it shall not be deemed a license grant by ST for the use of such third party products or services, or any intellectual property contained therein or considered as a warranty covering the use in any manner whatsoever of such third party products or services or any intellectual property contained therein.

**UNLESS OTHERWISE SET FORTH IN ST'S TERMS AND CONDITIONS OF SALE ST DISCLAIMS ANY EXPRESS OR IMPLIED WARRANTY WITH RESPECT TO THE USE AND/OR SALE OF ST PRODUCTS INCLUDING WITHOUT LIMITATION IMPLIED WARRANTIES OF MERCHANTABILITY, FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION), OR INFRINGEMENT OF ANY PATENT, COPYRIGHT OR OTHER INTELLECTUAL PROPERTY RIGHT.**

**UNLESS EXPRESSLY APPROVED IN WRITING BY AN AUTHORIZED ST REPRESENTATIVE, ST PRODUCTS ARE NOT RECOMMENDED, AUTHORIZED OR WARRANTED FOR USE IN MILITARY, AIR CRAFT, SPACE, LIFE SAVING, OR LIFE SUSTAINING APPLICATIONS, NOR IN PRODUCTS OR SYSTEMS WHERE FAILURE OR MALFUNCTION MAY RESULT IN PERSONAL INJURY, DEATH, OR SEVERE PROPERTY OR ENVIRONMENTAL DAMAGE. ST PRODUCTS WHICH ARE NOT SPECIFIED AS "AUTOMOTIVE GRADE" MAY ONLY BE USED IN AUTOMOTIVE APPLICATIONS AT USER'S OWN RISK.**

Resale of ST products with provisions different from the statements and/or technical features set forth in this document shall immediately void any warranty granted by ST for the ST product or service described herein and shall not create or extend in any manner whatsoever, any liability of ST.

ST and the ST logo are trademarks or registered trademarks of ST in various countries.

Information in this document supersedes and replaces all information previously supplied.

The ST logo is a registered trademark of STMicroelectronics. All other names are the property of their respective owners.

© 2011 STMicroelectronics - All rights reserved

STMicroelectronics group of companies

Australia - Belgium - Brazil - Canada - China - Czech Republic - Finland - France - Germany - Hong Kong - India - Israel - Italy - Japan - Malaysia - Malta - Morocco - Philippines - Singapore - Spain - Sweden - Switzerland - United Kingdom - United States of America

[www.st.com](http://www.st.com)