

# $\mu$ PG2411T7C

## GaAs Integrated Circuit SPDT Switch for 2 GHz to 6 GHz

### Data Sheet

R09DS0004EJ0100  
Rev.1.00  
Jun 17, 2010

#### DESCRIPTION

The  $\mu$ PG2411T7C is a GaAs MMIC SPDT (Single Pole Double Throw) switch which was designed for 2 GHz to 6 GHz applications, including dual-band wireless LAN.

This device can operate at frequencies from 2 GHz to 6 GHz, having the low insertion loss and high isolation.

This device is housed in a 6-pin plastic RTSON (Rectangle Thin Small Out-line Non-leaded) package. And this package is suitable for high-density surface mounting.

#### FEATURES

- Switch control voltage :  $V_{\text{cont (H)}} = 3.0$  V TYP.  
:  $V_{\text{cont (L)}} = 0$  V TYP.
- Low insertion loss :  $L_{\text{ins}} = 0.50$  dB TYP. @  $f = 2.5$  GHz  
:  $L_{\text{ins}} = 0.70$  dB TYP. @  $f = 6.0$  GHz
- High isolation :  $ISL = 25$  dB TYP. @  $f = 2.5$  GHz  
:  $ISL = 25$  dB TYP. @  $f = 6.0$  GHz
- Handling power :  $P_{\text{in (1 dB)}} = +30.5$  dBm TYP. @  $f = 2.5$  GHz  
:  $P_{\text{in (1 dB)}} = +30.5$  dBm TYP. @  $f = 6.0$  GHz
- High-density surface mounting : 6-pin plastic RTSON package ( $2.0 \times 1.3 \times 0.37$  mm)

#### APPLICATIONS

- Wireless LAN (IEEE802.11a/b/g/n)

#### ORDERING INFORMATION

Part Number	Order Number	Package	Marking	Supplying Form
$\mu$ PG2411T7C-E3	$\mu$ PG2411T7C-E3-A	6-pin plastic RTSON (Pb-Free)	G6G	<ul style="list-style-type: none"> <li>• Embossed tape 8 mm wide</li> <li>• Pin 1, 2, 3 face the perforation side of the tape</li> <li>• Qty 3 kpcs/reel</li> </ul>


**Remark** To order evaluation samples, please contact your nearby sales office.

Part number for sample order:  $\mu$ PG2411T7C-A

#### CAUTION

Although this device is designed to be as robust as possible, ESD (Electrostatic Discharge) can damage this device. This device must be protected at all times from ESD. Static charges may easily produce potentials of several kilovolts on the human body or equipment, which can discharge without detection. Industry-standard ESD precautions must be employed at all times.

## PIN CONNECTIONS AND INTERNAL BLOCK DIAGRAM



## SW TRUTH TABLE

ON Path	V <sub>cont</sub> 1	V <sub>cont</sub> 2
RFC-RF1	High	Low
RFC-RF2	Low	High

## ABSOLUTE MAXIMUM RATINGS (T<sub>A</sub> = +25°C, unless otherwise specified)

Parameter	Symbol	Ratings		Unit
Switch Control Voltage	V <sub>cont</sub>	+6.0 <sup>Note</sup>		V
Input Power	P <sub>in</sub>	+31.0		dBm
Power Dissipation	P <sub>D</sub>	150		mW
Operating Ambient Temperature	T <sub>A</sub>	-40 to +90		°C
Storage Temperature	T <sub>stg</sub>	-55 to +150		°C

Note: |V<sub>cont</sub>1 - V<sub>cont</sub>2| ≤ 6.0 V

## RECOMMENDED OPERATING RANGE (T<sub>A</sub> = +25°C, unless otherwise specified)

Parameter	Symbol	MIN.	TYP.	MAX.	Unit
Operating Frequency	f	2.0	—	6.0	GHz
Switch Control Voltage (H)	V <sub>cont</sub> (H)	2.8	3.0	3.3	V
Switch Control Voltage (L)	V <sub>cont</sub> (L)	-0.2	0	0.2	V
Control Voltage Difference	ΔV <sub>cont</sub> (H), ΔV <sub>cont</sub> (L) <sup>Note</sup>	-0.1	0	0.1	V

Note: ΔV<sub>cont</sub> (H) = V<sub>cont</sub>1 (H) - V<sub>cont</sub>2 (H)

ΔV<sub>cont</sub> (L) = V<sub>cont</sub>1 (L) - V<sub>cont</sub>2 (L)

## ELECTRICAL CHARACTERISTICS

( $T_A = +25^\circ\text{C}$ ,  $V_{\text{cont(H)}} = 3.0 \text{ V}$ ,  $V_{\text{cont(L)}} = 0 \text{ V}$ ,  $Z_0 = 50 \Omega$ , DC blocking capacitors = 8 pF, unless otherwise specified)

Parameter	Symbol	Test Conditions	MIN.	TYP.	MAX.	Unit
Insertion Loss	$L_{\text{ins}}$	$f = 2.4 \text{ to } 2.5 \text{ GHz}$	—	0.50	0.8	dB
		$f = 4.9 \text{ to } 6.0 \text{ GHz}$	—	0.70	1.0	dB
Isolation	ISL	$f = 2.4 \text{ to } 2.5 \text{ GHz}$	20	25	—	dB
		$f = 4.9 \text{ to } 6.0 \text{ GHz}$	20	25	—	dB
Return Loss	RL	$f = 2.4 \text{ to } 2.5 \text{ GHz}$	11	17	—	dB
		$f = 4.9 \text{ to } 6.0 \text{ GHz}$	11	17	—	dB
1 dB Loss Compression Input Power <sup>Note</sup>	$P_{\text{in}}(1 \text{ dB})$	$f = 2.5 \text{ GHz}$	—	+30.5	—	dBm
		$f = 6.0 \text{ GHz}$	—	+30.5	—	dBm
2nd Harmonics	2f0	$f = 2.5 \text{ GHz}, P_{\text{in}} = +20 \text{ dBm}$	—	80	—	dBc
		$f = 6.0 \text{ GHz}, P_{\text{in}} = +20 \text{ dBm}$	—	70	—	dBc
3rd Harmonics	3f0	$f = 2.5 \text{ GHz}, P_{\text{in}} = +20 \text{ dBm}$	—	80	—	dBc
		$f = 6.0 \text{ GHz}, P_{\text{in}} = +20 \text{ dBm}$	—	70	—	dBc
Switch Control Current	$I_{\text{cont}}$	No RF input	—	0.1	1.0	$\mu\text{A}$
Switch Control Speed	$t_{\text{sw}}$	50% CTL to 90/10% RF	—	20	100	ns


Note:  $P_{\text{in}}(1 \text{ dB})$  is the measured input power level when the insertion loss increases 1 dB more than that of the linear range.

### CAUTION

It is necessary to use DC blocking capacitors with this device.

The value of DC blocking capacitors should be chosen to accommodate the frequency of operation, bandwidth, switching speed and the condition with actual board of your system.


## EVALUATION CIRCUIT



Note: C1: 8 pF

The application circuits and their parameters are for reference only and are not intended for use in actual design-ins.

## APPLICATION INFORMATION




- C1 are DC blocking capacitors external to the device.  
The value may be tailored to provide specific electrical responses.
- The RF ground connections should be kept as short as possible and connected to directly to a good RF ground for best performance.
- $L_{ESD}$  provides a means to increase the ESD protection on a specific RF port, typically the port attached to the antenna.


## TYPICAL CHARACTERISTICS

( $T_A = +25^\circ\text{C}$ ,  $V_{\text{cont(H)}} = 3.0\text{ V}$ ,  $V_{\text{cont(L)}} = 0\text{ V}$ ,  $Z_0 = 50\text{ }\Omega$ , DC blocking capacitors = 8 pF, unless otherwise specified)


RFC-RF1/RF2  
INSERTION LOSS vs. FREQUENCY




RFC-RF1/RF2  
ISOLATION vs. FREQUENCY




RFC RETURN LOSS vs. FREQUENCY




RF1/RF2 RETURN LOSS vs. FREQUENCY





RFC-RF1/RF2  
INSERTION LOSS,  $I_{\text{cont}}$  vs. INPUT POWER



RFC-RF1/RF2  
INSERTION LOSS,  $I_{\text{cont}}$  vs. INPUT POWER




**Remark** The graphs indicate nominal characteristics.



**Remark** The graphs indicate nominal characteristics.

## PACKAGE DIMENSIONS

6-PIN PLASTIC RTSON (UNIT: mm)



**Remark**  $A > 0$

( ): Reference value

## **RECOMMENDED SOLDERING CONDITIONS**

This product should be soldered and mounted under the following recommended conditions. For soldering methods and conditions other than those recommended below, contact your nearby sales office.

<b>Soldering Method</b>	<b>Soldering Conditions</b>	<b>Condition Symbol</b>
Infrared Reflow	Peak temperature (package surface temperature) : 260°C or below Time at peak temperature : 10 seconds or less Time at temperature of 220°C or higher : 60 seconds or less Preheating time at 120 to 180°C : 120±30 seconds Maximum number of reflow processes : 3 times Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	IR260
Partial Heating	Peak temperature (terminal temperature) : 350°C or below Soldering time (per side of device) : 3 seconds or less Maximum chlorine content of rosin flux (% mass) : 0.2%(Wt.) or below	HS350

### **CAUTION**

Do not use different soldering methods together (except for partial heating).

<b>Caution</b>	GaAs Products	<p>This product uses gallium arsenide (GaAs). GaAs vapor and powder are hazardous to human health if inhaled or ingested, so please observe the following points.</p> <ul style="list-style-type: none"><li>• Follow related laws and ordinances when disposing of the product. If there are no applicable laws and/or ordinances, dispose of the product as recommended below.</li><li>1. Commission a disposal company able to (with a license to) collect, transport and dispose of materials that contain arsenic and other such industrial waste materials.</li><li>2. Exclude the product from general industrial waste and household garbage, and ensure that the product is controlled (as industrial waste subject to special control) up until final disposal.</li><li>• Do not burn, destroy, cut, crush, or chemically dissolve the product.</li><li>• Do not lick the product or in any way allow it to enter the mouth.</li></ul>
----------------	---------------	---

**Revision History** **$\mu$ PG2411T7C Data Sheet**

<b>Rev.</b>	<b>Date</b>	<b>Description</b>	
		<b>Page</b>	<b>Summary</b>
1.00	Jun 17, 2010	–	First edition issued

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

CEL:

[UPG2411T7C-A](#) [UPG2411T7C-E3-A](#) [UPG2411T7C-EVAL-A](#)