



THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 ALL RIGHTS RESERVED.

LOC		DIST		REVISIONS				
P	LTR	DESCRIPTION	DATE	DWN	APVD			
	F	REVISED PER ECO-11-013132	13JUL2011	HMR	MH			









CONTACT QTY: 30

DETAIL M  
SCALE 8:1



HOUSING QTY: 1



- 1 CONTACT MATING AREA MEETS THE PERFORMANCE REQUIREMENTS OF TE CONNECTIVITY PRODUCT SPECIFICATION 108-1957; BASED ON TELCORDIA GR-1217-CORE, APPLICATIONS IN UNCONTROLLED ENVIRONMENTS.
- 2 0.76µm MIN TIN-LEAD OVER 1.27µm MIN NICKEL
- 3 MATERIAL:  
 CONTACT - COPPER ALLOY  
 SHIELD - PHOSPHOR BRONZE  
 HOUSING - LCP, UL94V-0  
 CHICKLET - GLASS FILLED POLYESTER
- 4 REFERENCE APPLICATION SPEC 114-13020 FOR RECOMMENDED THRU HOLE DIAMETER AND PLATING THICKNESSES
- 5 DATUM AND BASIC DIMENSION ESTABLISHED BY CUSTOMER.
- 6 SEATING HEIGHT TO BOARD SURFACE.
- 7 CONTACT AREA LUBRICATED WITH BELLCORE APPROVED LUBRICANT. TECHNICAL REFERENCE: GR-1217-CORE, ISSUE 1, NOVEMBER 1995.
- 8 DATE CODE
- 9 OPTIONAL POWER CONTACT PN 535875-X
- 10 PART NUMBER

120789-1  
 PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	JCB	18JAN00
DIMENSIONS: mm		CHK	MDL	17JUL00
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD	-	-
0 PLC	±	PRODUCT SPEC		
1 PLC	±	108-1957		
2 PLC	±0.13	APPLICATION SPEC		
3 PLC	±0.050	114-13020		
4 PLC	±	WEIGHT		
ANGLES	±	-		
MATERIAL	3	FINISH SOLDER TAIL: 2		
CONTACT: 1		CUSTOMER DRAWING		

**OBSELETE** TE Connectivity  
 RECEPTACLE ASSEMBLY, 30 POSITION  
 LEFT HAND, 6 ROW, DUAL BEAM,  
 Z BACK HS3  
 NOT THE LATEST REVISION