

General Specifications

Allowable Ambient Temperature Range:

-10°C ~ +60°C (Operating)

-40°C ~ +70°C (Storage)


(non-condensing environment)

Expected Life


Failure Rate: 10%

25°C 100,000 Hours (00)

Outline

Units: $\frac{\text{inch}}{(\text{mm})}$ 

Characteristic Curves



Material

Casing : Plastic (Black) 94V-0

Impeller : Plastic (Black) 94V-0

Bearing : Ball Bearing

Lead Wire : UL1007, AWG26, +Red, -Black

Specifications

MODEL		Rated Voltage	Operating Voltage	Current	Input Power	Speed	Max. Air Flow		Max. Static Pressure		Noise	Mass
		Product No.	(V)	(V)	(A)*1	(W)*1	(min ⁻¹)*1	CFM*1	(m³/min)*1	in H2O	(Pa)*1	(dB)*1
BG0903- B042 -000-	00	12	8 ~ 13.8	0.40	4.80	2700	20.5	0.58	.61	152	47.5	210
BG0903- B043 -000-	00	12	8 ~ 13.8	0.64	7.68	3200	24.7	0.70	.90	225	51.5	210
BG0903- B044 -000-	00	12	8 ~ 12.8	1.03	12.40	3700	28.6	0.81	1.4	342	54.5	210
BG0903- B052 -000-	00	24	10 ~ 27.6	0.21	5.04	2700	20.5	0.58	.61	152	47.5	210
BG0903- B053 -000-	00	24	10 ~ 27.6	0.33	7.92	3200	24.7	0.70	.90	225	51.5	210
BG0903- B054 -000-	00	24	10 ~ 25.0	0.49	11.80	3700	28.6	0.81	1.4	342	54.5	210
HIGH SPEED												
BG0903- B047 -000-	00	12	10.8 ~ 12.6	1.6	19.20	5200	38.1	1.08	1.9	482	—	210