




	NIL	NIL	14	7	16	16	5-		-3
	NIL	NIL	38	19	40	40	5-		-2
	5, 16		14	7	16	16	5-		-1
	3, 16		14	7	16	16	5-		-0
	1, 8		6	3	8	8	4-		-9
	NIL		48	24	50	50	4-		-8
			46	23	48	48	4-		-7
			44	22	46	46	4-		-6
			40	20	42	42	4-		-4
			36	18	38	38	4-		-2
			34	17	36	36	4-		-1
			32	16	34	34	4-		-0
			30	15	32	32	3-		-9
			26	13	28	28	3-		-7
			20	10	22	22	3-		-4
			18	9	20	20	3-		-3
			16	8	18	18	3-		-2
			12	6	14	14	3-		-0
			4	2	6	6	2-		-6
		0.76 μm	2	1	4	4	2-		-5
			48	24	50	50	2-		-4
			46	23	48	48	2-		-3
			44	22	46	46	2-		-2
			42	21	44	44	2-		-1
			40	20	42	42	2-		-0
			38	19	40	40	1-		-9
			36	18	38	38	1-		-8
			30	15	32	32	1-		-5
			28	14	30	30	1-		-4
			24	12	26	26	1-		-2
			16	8	18	18			-8
			14	7	16	16			-7
			12	6	14	14			-6
			10	5	12	12			-5
			8	4	10	10			-4
			6	3	8	8			-3
		0.2 μm	2	1	4	4	5176837-1		
FINISH	PIN OMITTED	"D"	"C"	"B" SPACES	"A" REF	NO OF POS	ASS'Y P/N		

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN WYLEE 07MAR2005		tyco Electronics Tyco Electronics Singapore Pte. Ltd.	
DIMENSIONS: mm 		TOLERANCES, UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.25 1 PLC ±0.2 2 PLC ±0.2 3 PLC ± 4 PLC ± ANGLES ± MATERIAL FINISH		CHK VINCENT TAN APVD SE LFONG PRODUCT SPEC - APPLICATION SPEC - WEIGHT - CUSTOMER DRAWING	
GENERAL TOLERANCE 0<+/- 10 : ±0.2 10<+/- 30 : ±0.25 30<+/- 100 : ±0.3 ANGLES : ±3°		  		NAME AMPMODU 2mm PITCH POST HDR, HORIZONTAL TYPE, L=2.6 SIZE A2 CAGE CODE 00779 DRAWING NO C=5176837	
				SCALE -	SHEET 1 OF 1
				REV 03	