



### Product Description



SILVYN® LGEF-M



SILVYN® LGES-M



### Application

Spiral-wound, flexible protective conduit made of stainless steel (quality class 316) for applications in the fields of measuring technology, device equipment and safety.

- high mechanical strength
- high flexibility
- Corrosion resistant

Sizes 10.12 with double-linked

### Technical Data

#### Approvals

Rail: UNDERGROUND Link-up

#### Note

Sizes 10, 12 with double-linked

#### Material

Stainless steel AISI 316

#### Degree of protection

IP 40

#### Range of temperature

-100°C bis +400°C

### Article List

| Part number | Part designation / size | Internal Ø x External Ø in mm | Bending radius mm | Suitable for SILVYN® LGEF-M/LGES-M | PU ring in m |
|-------------|-------------------------|-------------------------------|-------------------|------------------------------------|--------------|
| 61804600    | 10                      | 6,8 x 9                       | 25                | M 12 x 1,5                         | 25           |
| 61804601    | 12                      | 10,2 x 13                     | 30                | M 16 x 1,5/1                       | 25           |
| 61804602    | 16                      | 13 x 16                       | 40                | M 16 x 1,5/2                       | 25           |
| 61804603    | 20                      | 16,9 x 20,5                   | 45                | M 20 x 1,5/1                       | 25           |
| 61804604    | 25                      | 21,1 x 25                     | 55                | M 25 x 1,5                         | 25           |



## Product Information

Page 2 of 2

Protective cable conduit system SILVYN® SSUE

Valid: 27.03.2008

|          |    |           |    |            |    |
|----------|----|-----------|----|------------|----|
| 61804605 | 32 | 28,1 x 32 | 70 | M 32 x 1,5 | 25 |
|----------|----|-----------|----|------------|----|