



(1,27 mm) .050"

SPECIFICATIONS

Yes

Reflowed solder forced into lock notch

Plated Through-hole

Plastic Solder Lock

RV[®]
FILE NO. E111594

FCF	1	NO. PINS PER ROW	LEAD STYLE	PLATING OPTION	D	CARD SLOT	TAIL OPTION	SL

20, 30, 40 & 50
(Standard sizes)

Specify LEAD STYLE from chart

PLATING OPTION

-L
μ" (0,25 μm)
ld on post,
e Tin on tail

–S
μ" (0,76 μm)
ld on post,
e Tin on tail


**CARD
SLOT**

-01
= Accepts
(0,80 mm)
.031"
thick
card

TAIL OPTION

–RA
= Right Angle
(Leave blank for
vertical version.
Style –02 only)

LEAD STYLE	Y	CARD-TO-BOARD SPACE (X)
-02	(6,35) .250	(2,60) .1025
-03	(9,53) .375	(9,53) .375



EMF

1	NO. PINS PER ROW
2	1
3	1
4	1
5	1
6	1
7	1
8	1
9	1
10	1
11	1
12	1
13	1
14	1
15	1
16	1
17	1
18	1
19	1
20	1
21	1
22	1
23	1
24	1
25	1
26	1
27	1
28	1
29	1
30	1
31	1
32	1
33	1
34	1
35	1
36	1
37	1
38	1
39	1
40	1
41	1
42	1
43	1
44	1
45	1
46	1
47	1
48	1
49	1
50	1
51	1
52	1
53	1
54	1
55	1
56	1
57	1
58	1
59	1
60	1
61	1
62	1
63	1
64	1
65	1
66	1
67	1
68	1
69	1
70	1
71	1
72	1
73	1
74	1
75	1
76	1
77	1
78	1
79	1
80	1
81	1
82	1
83	1
84	1
85	1
86	1
87	1
88	1
89	1
90	1
91	1
92	1
93	1
94	1
95	1
96	1
97	1
98	1
99	1
100	1

20, 30, 40 & 50
(Standard sizes)

CARD THICKNESS

-01
= (0,80 mm) .031"
thick board

PLATING OPTION

-L
= 10μ" (0,25 μm)
Gold on contact,
Matte Tin on tail

-S
= 30μ" (0,76 μm)
Gold on contact,
Matte Tin on tail

