




LOC	DIST	REVISIONS				
		P	LTR	DESCRIPTION	DATE	OWN
AA	22	A1		REV PER ECR-09-004284	16APR2009	TY SY



- 1 MATERIAL:HOUSING PCT POLYESTER, BLACK, IR COMPATIBLE, UL 94V-0.
TERMINALS-0.33[.013] THICK PHOS BRONZE PLATED WITH 1.27 μ m [.000050] MINIMUM THICK HARD GOLD IN LOCALIZED AREA AND 3.81 μ m [.000150] MINIMUM THICK MATTE TIN IN SOLDER AREA OVER 1.27 μ m [.000050] MINIMUM THICK NICKEL UNDERPLATE.
SHIELDS-0.254 [.010] THICK COPPER ALLOY PLATED WITH 1.27 μ m [.000050] MINIMUM NICKEL AND 2.03 μ m [.000080] MINIMUM HOT TIN DIP ON PCB GROUND TABS.
- 2 JACK CAVITY CONFORMS TO FCC RULES AND REGULATIONS, PART 68 SUBPART F.
3. ALL DIMENSIONS SHOWN ARE NOMINAL UNLESS OTHERWISE SPECIFIED.
- 4 USE #30 DRILL BIT OR 3.25mm DRILL BIT WHEN PRODUCING THESE PCB HOLES.



SUGGESTED PC BOARD LAYOUT
COMPONENT SIDE



SUGGESTED PANEL CUTOUT
SCALE 4:1

5558310-1
PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN A. FERNANDEZ	07JUN2005	Tyco Electronics Corporation Harrisburg, PA 17105-3608	
DIMENSIONS: mm[inches]		CHK J. WESTMAN	07JUN2005	NAME S. FLICKINGER	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD S. FLICKINGER	07JUN2005	PRODUCT SPEC 108-1163	
0 PLC $\pm$ -		APPLICATION SPEC 114-2048		SIZE A2	
1 PLC $\pm$ -		WEIGHT -		CAGE CODE -	
2 PLC $\pm$ 0.254[.01]		CUSTOMER DRAWING		DRAWING NO C=5558310	
3 PLC $\pm$ 0.127[.005]		SCALE 2:1		RESTRICTED TO -	
4 PLC $\pm$ -		SHEET 1 OF 1		REV A1	
ANGLES $\pm$ -					
MATERIAL 1					
FINISH 1					