








RECOMMENDED P.C.B. LAYOUT



CIRCUIT: SPST



NOTES:

1. ALL DIMENSIONS IN MM [INCH]
2. GENERAL TOLERANCE: X.X=±0.4
X.XX=±0.25
3. TERM. NOS. FOR REF. ONLY
4. RATING: 50mA, @12V DC
5. TRAVEL: 0.30±0.15mm
6. OPERATING FORCE: 260±50gf
7. CONTACT RESISTANCE: 100 MILLIOHMS Max.
8. ELECTRICAL LIFE: 100,000 CYCLES MIN.

E-SWITCH®				
TITLE				
TL 1100 D F260 Q				
SCALE	DATE	DR	DWG	REV
2:1	2/22/01	CJB	P001107	A
REV.	ECN NO.	DESCRIPTION		
A	11261	RELEASED FOR PRODUCTION		
		DATE	CHKD	
		2/22/01	CJB	
THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED				