











ARRANGEMENT OF CONTACTS

PARTS	3P	4P	5P			6P	7P	8P	
ANGLE	180°	216°	180°	240°	360°	240°	270°	270°	262°
POSITION OF VIEWS									
SPECIFICATIONS									
Dielectric strength		1,000V AC/1 Minute							
Contact resistance		20mΩ Max.							
Insulation resistance		100MΩ Min. at 500V DC							
Rating		100V AC 2A							



9	LOCK RING	1	DIECAST	NICKEL	30-50U"
8	HEAD SCREW	1	2AAR1050	NICKEL	30-50U"
7	PLASTIC TRAIL	1	PVC		UL94
6	CLIP-RING	1	BSR-H (0.8t)	NICKEL	30-50U"
5	BODY (R)	1	DIECAST	NICKEL	30-50U"
4	BODY (L)	1	DIECAST	NICKEL	30-50U"
3	CARRIER SLEEVE	1	DIECAST	NICKEL	30-50U"
2	CONTACT TERMINAL	3	HSR-H (1.5D) [R-35]	SILVER PLATED	30-50U"
1	PLASTIC CORE	1	NYLON [101]		UL94V2
P/N	PART NAME	Q'TY	MATERIAL	PLATING	REMARKS
DATE 990909	SCALE 1 : 1	UNIT M/M	MODEL NO. B-9007	5 P	180° PLUG
VARIOUS DIN CONNECTORS					
FILE NO. B9007-5P					
DESIGN H. S. P.	DRAFTSMAN C. C. U.	APPROVE T. S. L.			