




REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	3	REVISED	18FEB2017	D.Z	S.L



SECTION: A-A
SCALE 2:1

NOTES:

1. MATERIAL:

- 1.1 HOUSING: HIGH TEMPERATURE THERMO PLASTIC,UL94V-0,COLOR:BLACK.
1.2 CONTACT: COPPER ALLOY.
1.3 SOLDER PEG AND LATCH:STAINLESS STEEL.


2. FINISH:

SOLDER PEG: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.

CONTACT SOLDER AREA: GOLD FLASH ON SOLDER TAIL.

- 2.1 CONTACT AREA: GOLD FLASH ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
2.2 CONTACT AREA: 5u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
2.3 CONTACT AREA: 10u" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
2.4 CONTACT AREA: 15U" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.
2.5 CONTACT AREA: 30U" ON 50u" MIN NICKEL UNDERPLATED ALL OVER.



3. COPLANARITY: 0.10 MAX. (BEFORE SOLDERING)



MATING: ① INSERTING(25°) → ② ROTATING → ③ FIXED

UNMATING: ④ UNFIXED → ⑤ ROTATING → ⑥ WITHDRAWING

TAPE&REEL	BLACK	1.2V	30u"	260	2309411-5
TAPE&REEL	BLACK	1.2V	15u"	260	2309411-4
TAPE&REEL	BLACK	1.2V	10u"	260	2309411-3
TAPE&REEL	BLACK	1.2V	5u"	260	2309411-2
TAPE&REEL	BLACK	1.2V	GF	260	2309411-1
PACKING TYPE	HOUSING COLOR	POWER SUPPLY	FINISH	POS	PART NO.




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016 CHK RICHARD MA 09SEP2016		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± - 1 PLC ± 0.25 2 PLC ± 0.15 3 PLC ± 0.10 4 PLC ± - ANGLES ± -		NAME APVD SIMON LI 09SEP2016 PRODUCT SPEC 108-115122 APPLICATION SPEC -	
		WEIGHT -		SIZE A2	
MATERIAL 		FINISH 		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-2309411	
				RESTRICTED TO -	
				SCALE 1:1	
				SHEET 1 of 3	
				REV 3	

D


C

B


A



DETAIL:C
SCALE 2:1



RECOMMEND PCB LAYOUT
THE TOLERANCE UNLESS SPECIFIED IS ±0.05MM



DETAIL:D
SCALE 2:1

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	TE Connectivity		
CHK RICHARD MA 09SEP2016		NAME			
APVD SIMON LI 09SEP2016		PRODUCT SPEC		DDR4 SODIMM SOCKET 0.5mm PITCH 260POS 8.0mm HEIGHT STANDARD TYPE	
APPLICATION SPEC		WEIGHT		SIZE A2	CAGE CODE 00779
CUSTOMER DRAWING		SCALE 1:1		SHEET 2 OF 3	REV 3


REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	-	-	-	-

D



C

B




A



PULL OUT DIRECTION ➡



REEL
TOTAL
2 LAYERS



250	2	500	*-2309411-*
PCS/ REEL	REEL/ CARTON	PCS/ CARTON	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN DAVID ZHAO 09SEP2016	TE Connectivity	
DIMENSIONS: mm		CHK RICHARD MA 09SEP2016		
		APVD SIMON LI 09SEP2016	NAME	
		PRODUCT SPEC	DDR4 SODIMM SOCKET 0.5mm PITCH 260POS 8.0mm HEIGHT STANDARD TYPE	
TOLERANCES UNLESS OTHERWISE SPECIFIED		APPLICATION SPEC	SIZE	CAGE CODE
0 PLC ± -		WEIGHT	A2	00779
1 PLC ± -		CUSTOMER DRAWING	DRAWING NO	
2 PLC ± -			C=2309411	
3 PLC ± -			RESTRICTED TO	
4 PLC ± -			-	
ANGLES ± -			SCALE	
FINISH			1:1	
			SHEET	
			3 of 3	
			REV	
			3	