


REV.	DATE	ECR NO.	DESCRIPTION
NC	02/03/09	—	INITIAL RELEASE



LENGTH TABLE	
PART NUMBER	LENGTH (IN.)
135104-01-06.00	6.00
135104-01-12.00	12.00
135104-01-24.00	24.00
135104-01-36.00	36.00

NOTE:

1. PERFORM CONTINUITY AND HI-POT TESTING.
2. PACKAGED INDIVIDUALLY IN HEAT SEALED POLY BAG.

4		
3	009-954-341	HEAT SHRINK TUBING, BLACK, 3/16" DIAMETER
2	009-881-205	COAXIAL CABLE, RG316/U
1	132123	CONNECTOR, SMA R/A PLUG, GOLD
	PN	DESCRIPTION
		QTY

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY.

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE:
0.5 - 8mm ± 0.20 mm
8 - 30mm ± 0.40 mm
30 - 120mm ± 0.50 mm

UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE:
.020 - .315 = ± 0.007 "
.315 - 1.180 = ± 0.015 "
1.180 - 4.724 = ± 0.020 "

DO NOT SCALE DRAWING

APPROVALS		DATE
DRAWN	G.R.S.	02/03/09
CHECKED		
ISSUED		
SHEET	1 OF 1	
CAD FILE	C:/135/135104-01-XX.XX.DWG	

Amphenol Connex

PART DESCRIPTION			
SMA R/A PLUG TO SMA R/A PLUG RG316			
PART NO.			
135104-01-XX.XX			
DWG. NO.	135104-01-XX.XX.DWG	REV.	NC
SIZE	A	SCALE	NA