



PART AFTER
UNRESTRICTED RECOVERY

TABLE OF DIMENSIONS:

PART NUMBER	H		J			P	R	S	T	JO	HW	JW	U
	Min a	Max b	POLY Min a	VITON Min a	Max b	±10% b	±15% b	±10% b	±20% b	±10% b	±20% b	±20% b	±20% b
202D211-X-32	.88 (22,3)	.45 (11,5)	.88 (22,3)	.55 (13,9)	.25 (6,4)	3.00 (76,2)	.46 (11,7)	.12 (3,05)	.040 (1,02)	2.23 (56,6)	.06 (1,52)	.045 (1,14)	.55 (14,0)
202D221-X-32	1.01 (25,6)	.59 (15,0)	1.01 (25,6)	.63 (16,0)	.29 (7,4)	3.25 (82,6)	.48 (12,2)	.12 (3,05)	.040 (1,02)	2.36 (59,9)	.06 (1,52)	.045 (1,14)	.59 (15,0)
202D232-X-32	1.16 (29,4)	.74 (18,8)	1.16 (29,4)	.72 (18,2)	.33 (8,4)	3.50 (88,9)	.48 (12,2)	.12 (3,05)	.040 (1,02)	2.48 (63,0)	.07 (1,78)	.045 (1,14)	.60 (15,2)
202D242-X-32	1.34 (34,0)	.90 (22,9)	1.34 (34,0)	.84 (21,3)	.38 (9,7)	4.00 (101,6)	.48 (12,2)	.12 (3,05)	.040 (1,02)	2.87 (72,9)	.07 (1,78)	.045 (1,14)	.62 (15,7)
202D253-X-32	1.47 (37,3)	1.16 (29,5)	1.47 (37,3)	.91 (23,1)	.41 (10,5)	4.25 (108,0)	.55 (14,0)	.12 (3,05)	.065 (1,65)	2.85 (72,4)	.08 (2,03)	.045 (1,14)	.70 (17,8)
202D263-X-32	1.72 (43,6)	1.34 (34,1)	1.72 (43,6)	1.07 (27,1)	.48 (12,2)	4.50 (114,3)	.60 (15,2)	.12 (3,05)	.065 (1,65)	2.92 (74,2)	.08 (2,03)	.045 (1,14)	.78 (19,8)
202D274-X-32	1.97 (50,0)	1.62 (41,2)	1.97 (50,0)	1.24 (31,4)	.56 (14,3)	4.65 (118,1)	.60 (15,2)	.12 (3,05)	.065 (1,65)	2.86 (72,6)	.09 (2,29)	.055 (1,40)	.78 (19,8)
202D285-X-32	2.47 (62,7)	1.85 (47,0)	2.47 (62,7)	1.54 (39,1)	.69 (17,6)	4.75 (120,7)	.63 (16,0)	.12 (3,05)	.08 (2,03)	2.78 (70,6)	.10 (2,54)	.055 (1,40)	.81 (21,0)
202D296-X-32	2.73 (69,3)	2.35 (59,7)	2.73 (69,3)	1.70 (43,1)	.77 (19,6)	5.00 (127,0)	.63 (16,0)	.12 (3,05)	.08 (2,03)	2.64 (67,1)	.10 (2,54)	.055 (1,40)	.81 (21,0)
202D299-X-32	3.22 (81,7)	2.64 (67,1)	3.22 (81,7)	2.01 (51,0)	.90 (22,9)	5.25 (133,4)	.63 (16,0)	.12 (3,05)	.08 (2,03)	2.70 (68,6)	.10 (2,54)	.055 (1,40)	.81 (21,0)

NOTES:

1. All dimensions are in inches (millimeters)
2. Dimensions appearing in Table are as follows:
a - As supplied
b - After unrestricted recovery
3. Part shall have injection and vent ports, located as shown.

ORDERING INFORMATION:

Base part number 202D221 -4 -32
Material dash number _____
-3 Polyolefin, semi-rigid (RT-301/7)
-4 Polyolefin, flexible (RT-1304)
-12 Viton (RT-1312)
-25 Elastomer, fluid-resistant (RT-1325)
Modification number _____

SPECIFICATION CONTROL DRAWING (LIMITED DISTRIBUTION)

THIS DRAWING AND THE INFORMATION SET FORTH HEREON ARE THE PROPERTY OF RAYCHEM CORPORATION, AND ARE TO BE HELD IN TRUST AND CONFIDENCE. PUBLICATION, DUPLICATION, DISCLOSURE, OR USE FOR ANY PURPOSE NOT EXPRESSLY AUTHORIZED IN WRITING BY RAYCHEM CORPORATION IS PROHIBITED.

DO NOT SCALE THIS DRAWING

DRAWN	<i>R. Watson</i> 10-8-80
CHECKED	<i>Phyllis</i> 10/10/80
DESIGN APPD	<i>Phyllis</i> 10/10/80
MFG APPD	<i>Paul</i> 10/10/80
QC APPD	<i>Long</i> 10/10/80
MKTG APPD	<i>W. Rotman</i> 10/10/80
Title Service	<i>R. Watson</i> 10/10/80
PROJECT	

Raychem

RAYCHEM CORPORATION
300 CONSTITUTION DRIVE
SHELBO PARK, CALIFORNIA 94086

TITLE

BOOT, STRAIGHT, WITH LIP

CODE IDENT.

NO. 00000

DRWG. NO.

202D2XX-X-32

SIZE 8

SCALE

SHEET 1 OF 1

If this document is printed it becomes uncontrolled.
Check for the latest revision.