


LOC	DIST	REVISIONS			
		P	LTR	DESCRIPTION	DAP
G	14		C3	REVISED PER ECO-11-004917	11MAR11RKHMR



AMP WIRE RANGE	Listed FILE E13288	LR7189 Certified
8 AWG SOLID OR STRANDED	8 AWG STRANDED	8 AWG SOLID OR STRANDED

- 1
- STAMP AMP 8W* APPROX AS SHOWN

2

3

4

5

AMP INCORPORATED CUSTOMER SERVICE SYSTEMS			MAX RECOMMENDED OPERATING TEMPERATURE: 170°C MAX
FOR ADDITIONAL PRODUCT INFORMATION OR COPIES OF DRAWINGS AND TECHNICAL DOCUMENTS	PRODUCT INFORMATION CENTER 1-800-522-6752		VOLTAGE RATING: N/A
FOR APPLICATION TOOLING INFORMATION	TOOLING ASSISTANCE CENTER 1-800-722-1111		CIRCULAR MIL AREA: 6.64-10.5mm ² [13,100-20,800] SOLID OR STRANDED
FOR ORDER ENTRY	1-800-526-5142	THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED. IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.	

25	LOOSE PIECE, BAG	8-34321-5
25	LOOSE PIECE, BOX	8-34321-3
1500	ON TAPE	5 2-34321-1
----	LOOSE PIECE	34321
QTY	PACKAGING TYPE	PART NO.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN JR RUTH 19JAN07	TE Connectivity			
DIMENSIONS: INCHES		CHK M SPICER 19JAN07				
		APVD M SPICER 19JAN07	NAME			
		PRODUCT SPEC	SPLICE, BUTT, STANDARD, SOLISTRAND			
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APPLICATION SPEC	SIZE		CAGE CODE	DRAWING NO
0 PLC ± -		—	A2		00779	C-34321
1 PLC ± -		—	WEIGHT		—	RESTRICTED TO
2 PLC ± -		—	CUSTOMER DRAWING		SCALE 8:1	SHEET 1 of 1
3 PLC ± -		—	MATERIAL		REV C3	
4 PLC ± -		—	FINISH			
ANGLES ± -		—	3			
		—	4			