


FJPF5555

FJPF5555

High Voltage Switch Mode Application

- Fast Speed Switching
- Wide Safe Operating Area
- Suitable for Electronic Ballast Application



NPN Silicon Transistor

Absolute Maximum Ratings $T_C=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Value	Units
V_{CBO}	Collector-Base Voltage	1050	V
V_{CEO}	Collector-Emitter Voltage	400	V
V_{EBO}	Emitter-Base Voltage	14	V
I_C	Collector Current (DC)	5	A
I_{CP}	Collector Current (Pulse)	10	A
P_C	Collector Dissipation	40	W
T_J	Junction Temperature	150	$^\circ\text{C}$
T_{STG}	Storage Temperature	- 55 ~ 150	$^\circ\text{C}$

Electrical Characteristics $T_C=25^\circ\text{C}$ unless otherwise noted

Symbol	Parameter	Test Condition	Min.	Typ.	Max.	Units
BV_{CBO}	Collector-Base Breakdown Voltage	$I_C=500\mu\text{A}$, $I_E=0$	1050			V
BV_{CEO}	Collector-Emitter Breakdown Voltage	$I_C=5\text{mA}$, $I_B=0$	400			V
BV_{EBO}	Emitter-Base Breakdown Voltage	$I_E=500\mu\text{A}$, $I_C=0$	14			V
h_{FE}	* DC Current Gain	$V_{CE}=5\text{V}$, $I_C=10\text{mA}$	10			
		$V_{CE}=3\text{V}$, $I_C=0.8\text{A}$	20		40	
$V_{CE(sat)}$	Collector-Emitter Saturation Voltage	$I_C=1\text{A}$, $I_B=0.2\text{A}$			0.5	V
		$I_C=3.5\text{A}$, $I_B=1.0\text{A}$			1.5	V
$V_{BE(sat)}$	Base-Emitter Saturation Voltage	$I_C=3.5\text{A}$, $I_B=1.0\text{A}$			1.2	V
C_{ob}	Output Capacitance	$V_{CB}=10\text{V}$, $f=1\text{MHz}$		45		pF
t_{ON}	Turn On Time	$V_{CC}=125\text{V}$, $I_C=0.5\text{A}$			1.0	μs
t_{STG}	Storage Time	$I_{B1}=45\text{mA}$, $I_{B2}=0.5\text{A}$			1.2	μs
t_F	Fall Time	$R_L=250\Omega$			0.3	μs
t_{ON}	Turn On Time	$V_{CC}=250\text{V}$, $I_C=2.5\text{A}$			2.0	μs
t_{STG}	Storage Time	$I_{B1}=0.5\text{A}$, $I_{B2}=1.0\text{A}$			2.5	μs
t_F	Fall Time	$R_L=100\Omega$			0.3	μs

* Pulse test: $PW \leq 300\mu\text{s}$, Duty Cycle $\leq 2\%$

Typical Characteristics




Figure 1. Static Characteristics




Figure 2. DC Current Gain




Figure 3. Saturation Voltage




Figure 4. Saturation Voltage




Figure 5. Resistive Load Switching




Figure 6. Resistive Load Switching

Typical Characteristics (Continued)




Figure 7. Reverse Biased Safe Operating Area




Figure 8. Power Derating




Figure 9. Forward Biased Safe Operating Area

Technical drawing of a 2.54mm pitch connector, showing three views: front, side, and top.

Front View Dimensions:

- Overall width: 10.16 ± 0.20
- Top section width: (7.00)
- Top section height: 3.30 ± 0.10
- Main body height: 15.80 ± 0.20
- Pin length (from main body): 9.75 ± 0.30
- Pin diameter: 0.35 ± 0.10
- Pin tip angle: (30°)
- Pin pitch: 2.54 TYP [2.54 ± 0.20]
- Pin diameter tolerance: $\varnothing 3.18 \pm 0.10$
- Pin length tolerance: 0.80 ± 0.10
- Pin length tolerance: $\text{MAX} 1.47$
- Pin length tolerance: 0.35 ± 0.10
- Pin length tolerance: 2.54 TYP [2.54 ± 0.20]

Side View Dimensions:

- Top section height: 6.68 ± 0.20
- Main body height: 15.87 ± 0.20
- Pin length: 2.76 ± 0.20
- Pin diameter tolerance: $0.50^{+0.10}_{-0.05}$
- Pin length tolerance: 2.76 ± 0.20
- Pin length tolerance: 2.54 TYP [2.54 ± 0.20]

Top View Dimensions:

- Overall width: 9.40 ± 0.20
- Overall height: 4.70 ± 0.20

©2004 Fairchild Semiconductor Corporation

TRADEMARKS

The following are registered and unregistered trademarks Fairchild Semiconductor owns or is authorized to use and is not intended to be an exhaustive list of all such trademarks.

ACE [™]	FAST [®]	ISOPLANAR [™]	Power247 [™]	SuperFET [™]
ActiveArray [™]	FAST [™]	LittleFET [™]	PowerSaver [™]	SuperSOT [™] -3
Bottomless [™]	FPS [™]	MICROCOUPLER [™]	PowerTrench [®]	SuperSOT [™] -6
CoolFET [™]	FRFET [™]	MicroFET [™]	QFET [®]	SuperSOT [™] -8
CROSSVOLT [™]	GlobalOptoisolator [™]	MicroPak [™]	QS [™]	SyncFET [™]
DOMET [™]	GTO [™]	MICROWIRE [™]	QT Optoelectronics [™]	TinyLogic [®]
EcoSPARK [™]	HiSeC [™]	MSX [™]	Quiet Series [™]	TINYOPTO [™]
E ² CMOS [™]	I ² C [™]	MSXPro [™]	RapidConfigure [™]	TruTranslation [™]
EnSigna [™]	i-Lo [™]	OCX [™]	RapidConnect [™]	UHC [™]
FACT [™]	ImpliedDisconnect [™]	OCXPro [™]	μSerDes [™]	UltraFET [®]
FACT Quiet Series [™]		OPTOLOGIC [®]	SILENT SWITCHER [®]	VCX [™]
Across the board. Around the world. [™]		OPTOPLANAR [™]	SMART START [™]	
The Power Franchise [®]		PACMAN [™]	SPM [™]	
Programmable Active Droop [™]		POP [™]	Stealth [™]	

DISCLAIMER

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

As used herein:

1. Life support devices or systems are devices or systems which, (a) are intended for surgical implant into the body, or (b) support or sustain life, or (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.
2. A critical component is any component of a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

PRODUCT STATUS DEFINITIONS

Definition of Terms

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data, and supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice in order to improve design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild semiconductor. The datasheet is printed for reference information only.