




PRODUCT NUMBER
SEE TABLE



mat'l code				surface ISO 1302	tolerance ISO 406 ISO 1101	projection ISO 1302	product family LATCH-N-LOK	
ltr	ecn no	dr	date	tolerances unless otherwise specified		INCH/MM	scale 1:1	title 2X3 LNL VERTICAL HEADER ASSEMBLY
A	-	MRC	6/20/90	angles	linear			
B	-	RDS	10/18/90					
C	V01053	TFG	6/9/00	0°±2'				
D	V10985	TFG	2/21/01	dr	M. CORNMANN	6/20/90		
E	M05-0050	ERE	3/15/06	engr	D. HORCHLER	6/20/90		
F	M06-0365	AGS	9/20/06	chr	D. HORCHLER	6/20/90		
G	M09-0048	MHT	3/12/09	appd	D. HORCHLER	6/20/90		
sheet	revision	G	G					
index	sheet	1	2					




78065-XXXLF

LEAD FREE OPTION ⑥ ⑦

	COLOR ④	
1	70343 LT GRAY	OBS
2	80166 OFF WHITE	
3	70634 DK GRAY	OBS
4	701 BLACK	
5	70511 SLATE GRAY	OBS
7	70455 SILVER GRAY	
8	80189 PEARL WHITE	OBS
9	70419 PEBBLE GRAY	

	PLATING ⑧
0	30u" GXT
3	30u" AU OVER 50u" NI
5	50u" AU OVER 50u" NI

	PIN LENGTH
	DIM L
0	.130/3.30
1	.230/5.84
2	.318/8.08



RECOMMENDED PCB LAYOUT

NOTES:

1. HEADER SHROUD
MATERIAL: POLYCARBONATE,
94V-0 RATED.
2. GROUND CONTACT
MATERIAL: COPPER ALLOY
PLATING: 100-160u"/2.54-4.06u" TIN
3. SIGNAL CONTACT
MATERIAL: COPPER ALLOY
PLATING: SEE TABLE
- ④ NUMBERS SHOWN ARE FOR G.E. LEXAN AND ARE FOR REFERENCE ONLY.
5. THIS ASSEMBLY UL APPROVED PER FILE E66906 VOL. 1, SEC. 84
AND CSA APPROVED PER MASTER FILE LR46923.
- ⑥ ADD LF SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ⑦ THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
- ⑧ PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.

mat'l. code		surface ISO 1302	tolerance ISO 406 ISO 1101	projection ISO 1001	product family LATCH-N-LOK
ltr	ecn no	dr	date	tolerances unless otherwise specified	title
G				linear XX±.01/XX±0.3 XXX±.005/XX±0.13 XXXX±.0020/XXX±0.051	2X3 LNL VERTICAL HEADER ASSEMBLY
				scale 1:1	dwg no
					78065
					sheet 2 of 2 size A3
					type Product Customer Drawing
sheet index	revision sheet				