

# Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number :

744871004

LF



Bezeichnung :


DOPPELDROSSEL WE-DD

description :


POWER-CHOKE WE-DD

DATUM / DATE : 2006-03-15

## A Mechanische Abmessungen / dimensions:




|   | Typ L     |    |
|---|-----------|----|
| A | 12,5 max. | mm |
| B | 6,5 max   | mm |
| C | 1,5 ± 0,2 | mm |
| D | 4,9 ± 0,2 | mm |
| E | 7,3 ± 0,5 | mm |



## B Elektrische Eigenschaften / electrical properties:

| Eigenschaften / properties                                    | Testbedingungen / test conditions |                                   | Wert / value | Einheit / unit | tol. |
|---------------------------------------------------------------|-----------------------------------|-----------------------------------|--------------|----------------|------|
| Induktivität (je Wicklg.) / inductance (each wdg.)            | 1 kHz / 0,25V                     | L <sub>1</sub> , L <sub>2</sub>   | 4,7          | μH             | ±20% |
| DC-Widerstand (je Wicklg.) / DC-resistance (each wdg)         | @ 20°                             | R <sub>DC1,2 typ</sub>            | 0,023        | Ω              | typ. |
| DC-Widerstand (je Wicklg.) / DC-resistance (each wdg)         | @ 20°                             | R <sub>DC1,2 max</sub>            | 0,028        | Ω              | max. |
| Nennstrom (je Wicklg.) / rated Current (each wdg.)            | ΔT = 40 K                         | I <sub>N1</sub> , I <sub>N2</sub> | 3,00         | A              | max. |
| Sättigungsstrom (je Wicklg.) / saturation current (each wdg.) | ΔL/L <sub>0</sub> = -10%          | I <sub>sat</sub>                  | 8,00         | A              | typ. |
| Eigenres.-Frequenz / self-res.-frequency                      |                                   | SRF                               | 20           | MHz            | typ. |
| Nennspannung / rated Voltage                                  |                                   | U <sub>DC</sub>                   | 80           | V              | max. |

## C Lötpad / soldering spec.:



## D Prüfgeräte / test equipment:

HP 4274 A für/for L und/and Q  
HP 34401 A für/for I<sub>DC</sub> und/and R<sub>DC</sub>

## E Testbedingungen / test conditions:

Luftfeuchtigkeit / humidity: 33%  
Umgebungstemperatur / temperature: +20°C

## F Werkstoffe & Zulassungen / material & approvals:

Basismaterial / base material: Ferrit/ ferrite  
Draht / wire: 2 SFBW; 155°C

## G Eigenschaften / general specifications:

Betriebstemperatur / operating temperature: -40°C - + 125°C  
Umgebungstemp. / ambient temperature: -40°C - + 85°C  
It is recommended that the temperature of the part does not exceed 125°C under worst case operating conditions.

Freigabe erteilt / general release:

Kunde / customer

SSt

Version 6

06-03-15

SST

Version 5

05-03-29

MST

Version 4

04-10-11

SST

Version 3

04-09-24

SST

Version 3

04-03-09

AG

Version 2

03-06-11

AG

Version 1

02-11-23

Name

Änderung / modification

Datum / date

Datum / date

Unterschrift / signature

Würth Elektronik

Geprüft / checked

Kontrolliert / approved

Würth Elektronik eiSos GmbH & Co.KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400  
http://www.we-online.com

# Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 744871004

LF




Bezeichnung : DOPPELDROSSEL WE-DD

description : POWER-CHOKE WE-DD

DATUM / DATE : 2006-03-15

## H Induktivitätskurve / Inductance curve:

Induktivität vs Strom (typ.) /  
Inductance vs Current (typ.)



|                                     |                          |      |                         |              |
|-------------------------------------|--------------------------|------|-------------------------|--------------|
| Freigabe erteilt / general release: | Kunde / customer         |      |                         |              |
|                                     |                          | SST  | Version 6               | 06-03-15     |
|                                     |                          | SST  | Version 5               | 05-03-29     |
|                                     |                          | MST  | Version 4               | 04-10-11     |
| Datum / date                        | Unterschrift / signature | SST  | Version 3               | 04-09-24     |
|                                     |                          | SST  | Version 3               | 04-03-09     |
|                                     |                          | AG   | Version 2               | 03-06-11     |
|                                     |                          | AG   | Version 1               | 02-11-23     |
| Geprüft / checked                   | Kontrolliert / approved  | Name | Änderung / modification | Datum / date |
|                                     |                          |      |                         |              |

### Würth Elektronik eiSos GmbH & Co.KG

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400  
http://www.we-online.com

# Spezifikation für Freigabe / specification for release

Kunde / customer :

Artikelnummer / part number : 744871004

LF




Bezeichnung : DOPPELDROSSEL WE-DD

description : POWER-CHOKE WE-DD


DATUM / DATE : 2006-03-15

## I Rollenspezifikation / tape and reel specification:

## Gurtspezifikation / Tape specification:




|   |                     |    |
|---|---------------------|----|
| A | 12,55 ± 0,1         | mm |
| B | 16,0 ± 0,1          | mm |
| C | 24,0 ± 0,3          | mm |
| D | 1,50 ± 0,1<br>- 0,0 | mm |
| E | 4,00 ± 0,1          | mm |
| F | 2,00 ± 0,1          | mm |
| G | 1,75 ± 0,1          | mm |
| H | 11,5 ± 0,1          | mm |
| I | 12,55 ± 0,1         | mm |
| J | 6,60 ± 0,1          | mm |
| T | 0,40 ± 0,05         | mm |



## Rollenspezifikation / Reel specification:

|   |             |    |
|---|-------------|----|
| a | 330,0 ± 2,0 | mm |
| b | 21,00 ± 0,8 | mm |
| c | 13,00 ± 0,5 | mm |
| d | 100,0 ± 1,0 | mm |



The force for tearing off cover tape is 20 to 70 grams in arrow direction

Freigabe erteilt / general release:

Kunde / customer

|      |                         |              |
|------|-------------------------|--------------|
| SST  | Version 6               | 06-03-15     |
| SST  | Version 5               | 05-03-29     |
| MST  | Version 4               | 04-10-11     |
| SST  | Version 3               | 04-09-24     |
| SST  | Version 3               | 04-03-09     |
| AG   | Version 2               | 03-06-11     |
| AG   | Version 1               | 02-11-23     |
| Name | Änderung / modification | Datum / date |

Datum / date

Unterschrift / signature

Würth Elektronik

Geprüft / checked

Kontrolliert / approved

This electronic component is designed and developed with the intention for use in general electronics equipments. Before incorporating the components into any equipments in the field such as aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and reliability are especially required or if there is possibility of direct damage or injury to human body. In addition, even electronic component in general electronic equipments, when used in electrical circuits that require high safety, reliability functions or performance, the sufficient reliability evaluation-check for the safety must be performed before use. It is essential to give consideration when to install a protective circuit at the design stage.

**Würth Elektronik eiSos GmbH & Co.KG**

D-74638 Waldenburg · Max-Eyth-Strasse 1 - 3 · Germany · Telefon (+49) (0) 7942 - 945 - 0 · Telefax (+49) (0) 7942 - 945 - 400  
http://www.we-online.com