

Thursday, 29 November 2012

**HIRSCHMANN®**
Test & Measurement
A BRAND OF SKS

www.sks-kontakt.de

News

contact

sitemap

Login

main menu

[home](#)
[products](#)
[skills](#)
[download](#)

online catalogue T&M

[clamp-type test probes](#)
[crocodile clips](#)
[test probes](#)
[oscilloscope test probes](#)
[measuring leads](#)
[plugs](#)
 ▶ 2 mm system
 ▶ 2 mm safety system
 ▶ 4 mm system
 ▶ 4 mm sliding sleeve system
 ▶ 4 mm safety system
[sockets](#)
[sets](#)
[miscellaneous](#)

company

[portrait](#)
[corporate association](#)
[location maps](#)
[fairs and exhibitions](#)
[jobs](#)
[imprint](#)
[terms and conditions](#)[Home](#) ▶ [plugs](#) ▶ [plugs](#) ▶ [BSB 20 K](#)

BSB 20 K

datasheet for BSB 20 K
article number: 930 729 103[View Full-Size Image](#)

search online catalogue

Search

Messetermine

SPS / IPC / DRIVES
29. 11. 2012 - 29. 11.
2012Newsletter
Anmeldung☒ Test &
Measurement

QR-Code



product description:	order number: 930 729-103
description:	Multiple-spring wire plug with longitudinal or transverse cable entry in tower construction. Screw connection up to maximum cable cross-section of 2.5 mm ² and external diameter of 4 mm. Nickel-plated brass contact material.
typ:	BSB 20 K gelb/yellow
system:	4mm system
order number:	930 729-103
color	
other color versions:	
technical data	
measurement category acc. to IEC 61010:	CAT I
pin dimensions	4 mm
type of contact:	pin (spring loaded)
type of termination:	screw
rated voltage:	30 VAC / 60 VDC
rated current:	30 A
Please consider derating curve!	
contact resistance:	3 mOhm
material	
contact material:	brass
contact surface material:	nickel
housing material:	PP
environmental conditions:	
temperature range:	-25 °C to +100 °C
inflammable class:	
housing (basic material):	UL 94 HB
drawing	

© 2012 www.sks-kontakt.de

Joomla! is Free Software released under the GNU General Public License.