

LOC E	DIST B	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	ECR-05-013423	15JUN06	JMS	FWK

NOTES:

- 1

PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 2

100 TRAY PACK IN ACCORDANCE WITH AMP SPEC 107-3275
- 3

Ag PLATING
- 4

Ni PLATING
- 5

THIS ITEM MUST BE WHITE
- 6

ELECTRICAL CHARACTERISTICS

FREQUENCY RANGE:DC - 2 GHz

NOMINAL IMPEDANCE:75 Ohm

INSULATION RESISTANCE:5000 MOhm

WORKING VOLTAGE:500 Volts RMS at Sea Level

DIELECTRIC WITHSTAND VOLTAGE:1500 Volts RMS Max

CONTACT RESISTANCE:1.50 mOhm Max

CENTRE CONTACT:0.20 mOhm Max

OUTER CONTACT:N/A

VSWR @ xGHz:N/A

INSERTION LOSS xdb:N/A
- 7

MECHANICAL CHARATERISTICS

COUPLING RETENTION FORCE:445N Min

CABLE RETENETION FORCE:N/A




DURABILITY:500 Cycles Min
- 8

ENVIRONMENTAL CHARACTERISTICS


OPERATING TEMPERATURE:-65 to +165 DegC
- 9

FOR TECHNICAL DATA REFER TO YOUR LOCAL TYCO ELECTRONICS SALES OFFICE
- 10

ALL DIMENSIONS ARE NOMINAL FOR REFERENCE ONLY UNLESS OTHERWISE STATED



		1	1	BRASS	3	FLANGE	9
		1	1	BRASS	3	SHELL	8
		1	1	SILICON RUBBER	5	GASKET	7
		1	1	BRASS	4	RETAINING RING	6
		1	1	SPRING STEEL	4	SPRING	5
		1	1	BRASS	3	WASHER	4
		1	1	BRASS	3	BODY	3
		1	1	PTFE		INSULATION	2
		1	1	BRASS	3	CONTACT	1
		6--0	1--0	MATERIAL		DESCRIPTION	ITEM
		3	3				
QUANTITY PER ASSY				PARTS LIST			

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J.SANDWELL 15JUN06	tyco Electronics Tyco Electronics Corporation Bideford EX39 4HE					
DIMENSIONS: mm		CHK S.PARLOW 15JUN06						
0 PLC ± - 1 PLC ± - 2 PLC ± - 3 PLC ± - 4 PLC ± - ANGLES ± - 		APVD F.WHEELER-KING 15JUN06	NAME BNC PANEL PLUG 75 OHM — —					
		PRODUCT SPEC —						
		APPLICATION SPEC —						
		MATERIAL SEE TABLE	FINISH —	WEIGHT —	SIZE A3	CAGE CODE 00779	DRAWING NO C-1478052	RESTRICTED TO —
CUSTOMER DRAWING						SCALE NTS	SHEET 1 OF 1	REV B