




PCB Layout

Dimensions : Millimetres (Inches)

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

Ashok

DATE:

19/01/12

CHECKED BY:

Jagan

DATE:

19/01/12

APPROVED BY:
DATE:

02/02/12

DRAWING TITLE:
Dual In Line Switches - End Stackable
SIZE

A

DWG NO.

M10000814

ELECTRONIC FILE

EI(M)R-V_DWG

REV

A

SCALE: NTS

U.O.M.: mm (Inches)

SHEET: 1 OF 3



PART NO.

MCEMR Series

REVISIONS

ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Ashok	19/01/12	Jagan	19/01/12	Farnell	02/02/12

Specifications:**Mechanical:**

Mechanical life : 2,000 operations
Maximum operating force : 1,000 gf
Stroke : 1.0 mm
Operating temperature : -20°C to +85°C
Storage temperature : -40°C to +85°C

Electrical:

Electrical life : 2,000 cycles
Rating : 25 mA, 24 V dc
Minimum Contact resistance : 100 mΩ at 500 V dc
Maximum Insulation resistance : 100 MΩ at 500 V dc
Dielectric strength : 500 V ac/1 minute
Circuit : 1 pole throw

Material:

Base and cover : UL 94V-0 Nylon high temperature thermoplastic
Colour : Black
Actuator : UL 94V-0 LCP high temperature thermoplastic
Colour : White
Contact : Alloy copper with gold plated
Terminal : Brass with gold plated
Tape : Kapton


Soldering Process:

Wave soldering : Recommended solder temperature at 500°F (260°C) maximum 5 seconds for through hole type

Hand soldering : Use a soldering iron of 30 watts, controlled at 350°C approximately maximum 5 seconds while applying

Reflow Soldering : When applying reflow soldering, the peak temperature or the reflow oven should be set at 260°C maximum

Do not wash the switch except top tape sealed type, which suitable for spray cleaning method from top of the s/w

Reflow Temperature Profile

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

TOLERANCES:

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.

DRAWN BY:

Ashok

DATE:

19/01/12

CHECKED BY:

Veena

DATE:

19/01/12

APPROVED BY:**DATE:**

02/02/12

DRAWING TITLE:**Dual In Line Switches - End Stackable****SIZE**
A

DWG NO.

M10000814ELECTRONIC FILE
EI(M)R-V_DWGREV
A

SCALE: NTS

U.O.M.: mm (Inches)

SHEET: 2 OF 3



PART NO.

MCEMR Series

REVISIONS


ECN #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
-	A	RELEASED	Ashok	19/01/12	Jagan	19/01/12	Farnell	02/02/12

Specifications Table

Number of Positions	A	B	Part Number
2	4.98 (0.196)	2.54 (0.1)	MCEMR-02-T
3	7.52 (0.296)	5.08 (0.2)	MCEMR-03-T
4	10.06 (0.396)	7.62 (0.3)	MCEMR-04-T
5	12.6 (0.496)	10.16 (0.4)	MCEMR-05-T
6	15.14 (0.596)	12.7 (0.5)	MCEMR-06-T
7	17.68 (0.696)	15.24 (0.6)	MCEMR-07-T
8	20.22 (0.796)	17.78 (0.7)	MCEMR-08-T
9	22.76 (0.896)	20.32 (0.8)	MCEMR-09-T
10	25.3 (0.996)	22.86 (0.9)	MCEMR-10-T
12	30.38 (1.196)	27.94 (1.1)	MCEMR-12-T

Dimensions: Millimetres (Inches)

Part Number Explanation



Terminal Type : M = SMT Type
Actuator Type : R = Recessed Actuator
Number of Positions : 02, 03, 04 05, 06, 07, 08, 09, 10, 12 Positions
Seal Tape : T = Top Tape Sealed (For Recessed Actuator only)

www.element14.com
www.farnell.com
www.newark.com

Important Notice : This data sheet and its contents (the "Information") belong to the members of the Premier Farnell group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp is the registered trademark of the Group. © Premier Farnell plc 2012.

TOLERANCES:

UNLESS OTHERWISE
SPECIFIED,
DIMENSIONS ARE
FOR REFERENCE
PURPOSES ONLY.

DRAWN BY:

Ashok

DATE:

19/01/12

CHECKED BY:

Veena

DATE:

19/01/12

APPROVED BY:

DATE:

02/02/12

DRAWING TITLE:

Dual In Line Switches - End StackableSIZE
A

DWG NO.

M10000814ELECTRONIC FILE
EI(M)R-V_DWGREV
A

SCALE: NTS

U.O.M.: mm (Inches)

SHEET: 3 OF 3