




AC Adapter 12VDC/500mA

412-112053

Dimensions: mm (in.)



Mechanical Specifications:

- Primary voltage: 120VAC 60Hz 15W
- Exciting current, open circuit: 60mA max. (no load)
180mA max. (full load)
- Secondary, voltage ($\pm 5\%$): 17.7VDC (no load)
12VDC/500mA (full load)
- DC resistance $\pm 15\%$: 127 Ω
- Insulation resistance: 100M Ω @ 500VDC
- Dielectric strength: primary-secondary: 1,500VAC for 1 minute
primary-core: 1,500VAC for 1 minute
secondary-core: 500VAC for 1 minute
- 2.5mm plug: center positive
- Cord length: 6ft.

Specifications are subject to change without notice. No liability or warranty implied by this information. Environmental compliance based on producer documentation.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Xicon:

412-112053