






PART NUMBER	SML-LX0805UWC-TR	REV.	F
DATE	E.C.N. NUMBER AND REVISION COMMENTS		REV.
05.09.02	E.C.N. #10862.		A
03.14.03	E.C.N. #10967.		B
01.17.05	E.C.N. #11148.		C
03.06.09	E.C.N. #11508.		D
05.07.12	E.C.N. #10BRDR. & REDRAWN.		E
08.25.14	E.C.N. #11917.		F



ANODE  CATHODE



RECOMMENDED SOLDER PAD LAYOUT



ELECTRO-OPTICAL CHARACTERISTICS Ta=25°C If=350mA					
PARAMETER	MIN	TYP	MAX	UNITS	TEST COND
FORWARD VOLTAGE		2.9	3.6	Vf	If=20mA
REVERSE VOLTAGE	5.0			Vr	Ir=10μA
AXIAL INTENSITY*	112		360	mcđ	If=20mA
VIEWING ANGLE		120		2x theta	
EMITTED COLOR:	WHITE				
LENS FINISH:	YELLOW DIFFUSED				

LIMITS OF SAFE OPERATION AT 25°C				
PARAMETER	SYMBOL	MAX	UNITS	
PULSE FORWARD CURRENT	Ip	100	mA	
STEADY CURRENT	If	25	mA	
POWER DISSIPATION	Id	95	mW	
OPERATING TEMP.	ToPR	-40 TO +85	°C	
STORAGE TEMP.	Sstg	-40 TO +90	°C	



*DUTY 1/10 PULSE WIDTH 10ms

CAUTION: MOISTURE SENSITIVE DEVICE
PER JEDEC LEVEL 2 STANDARDS

CAUTION: STATIC SENSITIVE DEVICE
FOLLOW PROPER E.S.D. HANDLING PROCEDURES
WHEN WORKING WITH THIS PART.

*UNLESS OTHERWISE SPECIFIED TOLERANCES PER DECIMAL PRECISION ARE: X=±1 (±0.039), X.X=±0.5 (±0.020), X.XX=±0.25 (±0.010), X.XXX=±0.127 (±0.005). LEAD SIZE=±0.05 (±0.002), LEAD LENGTH=±0.75 (±0.030). MIN.= +DECIMAL PRECISION -0.00 DECIMAL PRECISION MAX.= +0.00 DECIMAL PRECISION -DECIMAL PRECISION

PART NUMBER	SML-LX0805UWC-TR	REV.	F
DATE	E.C.N. NUMBER AND REVISION COMMENTS		REV.
05.09.02	E.C.N. #10862.		A
03.14.03	E.C.N. #10967.		B
01.17.05	E.C.N. #11148.		C
03.06.09	E.C.N. #11508.		D
05.07.12	E.C.N. #10BRDR. & REDRAWN.		E
08.25.14	E.C.N. #11917.		F



NOTES:

1. POLARITY MARK IS ORIENTED TOWARDS TAPE SPROCKET HOLE.