

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0009652048](#)
Status: **Active**
Overview:
Description: 3.96mm (.156") Pitch SPOX™ and KK® Wire-to-Board Header, Vertical, with Friction Lock, 4 Circuits

Documents:


- | | |
|---|---|
| 3D Model | Product Specification PS-5239-006 (PDF) |
| Drawing (PDF) | Product Specification PS-5239-007 (PDF) |
| Product Specification PS-5195-001 (PDF) | Product Specification PS-5273-003 (PDF) |
| Product Specification PS-5195-005 (PDF) | Product Specification PS-5273-004 (PDF) |
| Product Specification PS-5239-002 (PDF) | RoHS Certificate of Compliance (PDF) |
| Product Specification PS-5239-004 (PDF) | |

General

Product Family	PCB Headers
Series	5273
Application	Wire-to-Board
Overview	KK®
Product Name	KK®
Product Name	SPOX™

Physical

Breakaway	No
Circuits (Loaded)	4
Circuits (maximum)	4
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Flammability	94V-2
Glow-Wire Compliant	No
Guide to Mating Part	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Number of Rows	1
Orientation	Vertical
PC Tail Length (in)	0.142 In
PC Tail Length (mm)	3.60 mm
PCB Locator	No
PCB Retention	None
PCB Thickness Recommended (in)	0.062 In
PCB Thickness Recommended (mm)	1.60 mm
Packaging Type	Bag
Pitch - Mating Interface (in)	0.156 In
Pitch - Mating Interface (mm)	3.96 mm
Plating min: Mating (µin)	200
Plating min: Mating (µm)	5
Plating min: Termination (µin)	200
Plating min: Termination (µm)	5
Polarized to PCB	No
Shrouded	Partial
Stackable	No
Surface Mount Compatible (SMC)	No



Series image - Reference only

EU RoHS

**ELV and RoHS
Compliant**
**REACH SVHC
Contains SVHC: No**
**Halogen-Free
Status**

China RoHS



Not Reviewed

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

Search Parts in this Series

[5273 Series](#)

Mates With

[5195](#) SPOX™ Crimp Housing. [5239](#) KK®
Crimp Housing

Temperature Range - Operating

Termination Interface: Style

-40°C to +105°C

Through Hole

Electrical

CSA

Current - Maximum

TUV

UL

Voltage - Maximum

LR19980

7A

R72090224

E29179

250V

Material Info

Old Part Number

5273-04A

Reference - Drawing Numbers

Product Specification

Product Specification

Product Specification

Product Specification

Product Specification

Product Specification

Product Specification

Product Specification

Product Specification

Product Specification

Product Specification

Product Specification

Sales Drawing

PS-5195-001

PS-5195-005

PS-5239-002

PS-5239-004

PS-5239-006

PS-5239-007

PS-5273-003

PS-5273-004

RPS-5195-002

RPS-5239-001

RPS-5273-002

SD-5273-NA

This document was generated on 11/05/2009

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION