

**Part Number: 87204-7364**

D-Subminiature Shielded I/O PCB Female Receptacle, Right Angle, Through Hole, 25 Circuits, M2.6 Inner Thread Screws Assembled, Gold (Au) Flash

Image not available

<b>Status:</b>	<b>OBsolete</b>
<b>Replacement:</b>	NONE
<b>Series:</b>	<a href="#">87204</a>
<b>Category:</b>	I/O Connectors

*Series image - Reference only*

**Mates With Part(s):**  
[87203](#)

**Product Environmental Compliance**

[EU RoHS](#): Not RoHS Compliant

[China RoHS](#):

[REACH SVHC](#):

[Low-Halogen Status](#): Not Reviewed

**Part Detail****General**

<b>Status</b>	<b>Obsolete</b>
Category	I/O Connectors
Series	<a href="#">87204</a>
Application	Wire-to-Board
Comments	Shell: Steel
Component Type	Receptacle
Obsolete Date	2006/06/01
Product Name	D-Sub
Type	N/A

**Physical**

Circuits (Loaded)	25
Circuits (maximum)	25
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Orientation	Right Angle
PC Tail Length	3.18mm
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.77mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-55°C to +85°C
Termination Interface: Style	Through Hole
Wire Size AWG	N/A

**Electrical**

(Please review the Product Specification for specific details.)

Current - Maximum per Contact	1A
Shielded	Yes
Voltage - Maximum	300V

**Material Info**

UPC	800753685505
-----	--------------

**Application Tooling**

Tooling specifications and manuals are found by selecting the products below.

Crimp Height Specifications are then contained in the Application Tooling Specification document.

**Previously Available Application  
Tooling**  
[Check our list of old tooling that used to be  
available for this part](#)