

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0877343003](#)
Status: **Active**
Overview: EXTreme PowerPlus™ (SSI)
Description: 6.35mm Pitch, Power, 2.54mm Pitch, Signal, EXTreme PowerPlus™ AC/DC Receptacle, P(A)AC-S-P(B)DC, Through Hole, Vertical, 0.76µm Gold (Au), 32 Circuits, Recessed Power Pins at all locations except A1, without Beveled Metal Pins, Lead

Documents:
[3D Model](#) [Application Specification AS-87631-018-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Product Specification PS-87663-006-001 \(PDF\)](#)

Agency Certification

CSA	LR19980
UL	E29179

General


Product Family	PCB Receptacles
Series	87734
Application	Board-to-Board, Power
Overview	EXTreme PowerPlus™ (SSI)
Product Name	EXTreme PowerPlus™
UPC	822350288576

Physical

(p)ower-(s)ignal Configuration	5p - 24s - 3p
Circuits (Loaded)	32
Circuits (maximum)	32
Color - Resin	Black
Flammability	94V-0
Glow-Wire Compliant	No
Guide to Mating Part	Yes
Lock to Mating Part	None
Material - Metal	Copper Alloy
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	16.093/g
Number of Rows	4
Orientation	Vertical
PC Tail Length	3.43mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	2.40mm
Packaging Type	Tray
Pitch - Mating Interface	2.54mm, 6.35mm, 7.62mm
Pitch - Termination Interface	2.54mm, 3.18mm, 3.81mm, 5.08mm
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Stackable	No
Temperature Range - Operating	-20°C to +105°C
Termination Interface: Style	Through Hole

Electrical

Current - Maximum per Contact	2.5A, 30.0A, 50.0A
-------------------------------	--------------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Low-Halogen

**Need more information on product
environmental compliance?**

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

[87734](#) Series

Mates With

[87663](#) PCB Header

Voltage - Maximum	250V (RMS)
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	SMC&WAVE
Max. Cycles at Max. Process Temperature	003
Process Temperature max. C	260
Material Info	
Reference - Drawing Numbers	
Application Specification	AS-87631-018-001
Product Specification	PS-87663-006-001
Sales Drawing	SD-87734-001

This document was generated on 11/29/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION