

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

N/A , N/A ,

© COPYRIGHT

N/A

BY TYCO ELECTRONICS CORPORATION.

ALL RIGHTS RESERVED.

COMPONENT

MATERIAL

FINISH

HOUSING  
CAP  
COUPLING NUT

STAINLESS STEEL PER  
ASTM-A-484 OR ASTM-A-582  
TYPE 303

PASSIVATED PER  
ASTM-A-380  
—

—  
DIELECTRIC

PTFE FLUORCARBON  
PER ASTM-D-1457  
—

—  
—  
—

—  
CENTER  
CONTACT

BRASS PER ASTM-B-16  
HALF HARD  
—

GOLD PLATED PER  
ASTM-B-488  
—

—  
—  
—

—  
—  
—

—  
—  
—

—  
GASKET

SILICONE RUBBER  
PER ZZ-R-765  
—

—  
—  
—

—  
FERRULE

COPPER OR BRASS  
ALLOY, ROCKWELL  
F65 MAX

GOLD PLATED PER  
ASTM-B-488  
—

—  
RETAINING RING

BERYLLIUM COPPER PER  
ASTM-B-194  
ALLOY C17200, CONDITION H

—  
—  
—

—  
—  
—

—  
—  
—

—  
—  
—

ENVIRONMENTAL

TEMPERATURE RATING: -65°C TO +165°C

VIBRATION: MIL-STD-202, METHOD 204, CONDITION D

SHOCK: MIL-STD-202, METHOD 213, CONDITION 1

MOISTURE RESISTANCE: MIL-STD-202, METHOD 106

CORROSION: MIL-STD-202, METHOD 101, CONDITION B. 5% SALT SPRAY

THERMAL SHOCK: MIL-STD-202, METHOD 107, CONDITION B  
EXCEPT HIGH TEMP 85°C

MECHANICAL

INTERFACE DIMENSIONS: MIL-STD-348A FIG. 310.1

RECOMMENDED MATING TORQUE: 7-10 IN-LBS

FORCE TO ENGAGE & DISENGAGE (IN-LBS MAX:) 2.0

WEIGHT (GRAMS): TBD

MATING CHARACTERISTICS: INSERTION (MAX LBS) N/A  
WITHDRAWAL (MIN OZ): N/A

CABLE RETENTION: AXIAL FORCE (LBS) 45 MIN  
TORQUE (IN-OZ): N/A

CENTER CONTACT CAPTIVATION: AXIAL (LBS): 6.0  
RADIAL (IN-OZ): N/A

ELECTRICAL

NORMAL IMPEDANCE (OHMS): 50

FREQUENCY RANGE (GHz): DC TO 12.4

VOLT RATING @ SEA LEVEL (VRMS MAX): 335

VSWR: 1.15+.02f(GHz)

INSERTION LOSS: (dB MAX): .06  $\sqrt{f(\text{GHz})}$

RF LEAKAGE (dB MIN): -60 @ 2-3 GHz

CORONA 70,000 FT (VRMS MIN): 250

DIELECTRIC WITHSTANDING VOLTAGE (VRMS MIN) AT SEA LEVEL: 1000

I.R. (MEGOHMS MIN): 5,000

RF HIGH POTENTIAL AT SEA LEVEL (VRMS MIN @ 5 MHz): 670

CONTACT RESISTANCE (MILLIOHMS MAX):  
CENTER CONTACT: 4.0  
OUTER CONTACT: 2.0  
CABLE TO HOUSING: 0.5

LOC

DIST

REVISIONS

DF

X0

P

LTR

DESCRIPTION

DATE

DWN

APVD

O

RELEASED

9-02

JMK

JL

AS SHIPPED TO CUSTOMER

1

Ø.018 [0.46] LOCKWIRE HOLE, 3 PLACES EQUALLY SPACED.

DESIGNED TO USE  
RG-142/U OR EQUIVALENT  
CABLE ENTRY  
DIAMETER MIN

HOUSING: .121 [3.07]

CONTACT SLOT: .041 [1.04]

— —

— —

FERRULE: .216 [5.48]

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:  
INCHES [mm]

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ± —  
1 PLC ± —  
2 PLC ± —  
3 PLC ± .005 [0.13]  
4 PLC ± —  
ANGLES ± —

MATERIAL  
SEE TABLE

FINISH  
SEE TABLE

DWN  
J. KAISER  
CHK  
J.LIPPERT  
APVD  
J.LIPPERT

9/24/02  
10-18-02  
10-18-02

PRODUCT SPEC  
—  
APPLICATION SPEC  
408-4967

WEIGHT  
TBD

tyco  
Electronics

Tyco Electronics Corporation  
Harrisburg, PA 17105

NAME  
SMA RIGHT ANGLE CABLE PLUG-CRIMP  
ATTACHMENT (M39012/56B3022) CAT B

SIZE  
A2

CAGE CODE  
00779

DRAWING NO  
1052168

RESTRICTED TO  
—

CUSTOMER DRAWING

SCALE  
5:1

SHEET  
1

OF  
1

REV  
0

ASSEMBLED VIEW

1052168-1

PART  
NO.

AMP 1471-9 REV 31MAR2000

J:\DEPT1733\U.DIES\john\_lippert\1052168\_1\_c.dwg

MA/COM # 2037-8022-92