

- [Check Distributor Inventory](#)
- [Find Authorized Distributors](#)

. [My Account](#)

- [Sign In](#)
- [Register](#)

. [Customer Support](#)

- [Support](#)
- [RoHS Support Center](#)
- [Glossary of Terms](#)
- [eBulletin Newsletter](#)

[Home](#) > [Products](#) > [By Type](#) > [Terminal Blocks & Strips](#) > [Product Feature Selector](#) > Product Details

1546670-7 Product Details



1546670-7



[Active](#)

Barrier Strips, Barrier Strip Sockets



[Always EU RoHS/ELV Compliant](#) ([Statement of Compliance](#))

Product Highlights:

- Barrier Strip
- Dual Barrier Block Series
- Base Style = Flat With End Mounting Holes
- 11.10 mm Centerline
- Number of Levels = Single

[View all Features](#) | [Find Similar Products](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

Documentation & Additional Information

Product Drawings:

- [DOUBLE ROW BARRIER STRIP W/ BINDING HD SCREW, .437 S...](#) (PDF, English)

Catalog Pages/Data Sheets:

- [BUCHANAN TERMINAL BLOCKS CATALOG - BARRIER STRIPS](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- [Product Type](#) = Barrier Strip
- [Mount Angle](#) = Vertical
- [Mounting Ears](#) = With
- [Number of Circuits](#) = 7
- [Screw Material](#) = Steel
- Screw Size = 6-32 x 1/4

Mechanical Attachment:

- [Mounting Style](#) = Open End Position
- [Screw Plating](#) = Nickel

Electrical Characteristics:

- [Base Style](#) = Flat With End Mounting Holes
- [Number of Levels](#) = Single
- [End Barriers](#) = Without
- [Mounting Insert](#) = Without
- [Top Hardware](#) = Brass Clamp-plate Combo Head Screws
- Current Rating (Amps.) = 25

Body Related Features:

- [Block Series](#) = Dual Barrier
- [Centerline \(mm \[in\]\)](#) = 11.10 [0.4375]
- [Number of Rows](#) = 2
- Length (mm [in]) = 96.90 [3.810]
- Block Material = Thermoplastic
- Block Color = Black
- Wire Range (mm [AWG]) = 0.30-2.00² [22-14]

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = Buchanan

[Provide Website Feedback](#) | [Contact Customer Support](#)

[Home](#) | [Customer Support](#) | [Suppliers](#) | [Site Map](#) | [Privacy Policy](#) | [Browser Support](#)

© 2008 Tyco Electronics Corporation All Rights Reserved

