


ALL RIGHTS RESERVED. NO PORTION OF THIS PUBLICATION, WHETHER IN WHOLE OR IN PART CAN BE REPRODUCED WITHOUT THE EXPRESS WRITTEN CONSENT OF SPC TECHNOLOGY.

REVISIONS			DOC. NO. SPC-F005 * Effective: 12/21/98 * DCP No: 680					
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD	DATE
	A	Redrawn in Autocad	JAP	11/13/91				
1199	B	Redrawn & Renamed	JWM	11/9/01	JC	11/26/01	JC	11/26/01



- NOTES:**
1. MATERIAL: COPPER
PVC INSULATOR
 2. FLAMMABILITY: UL94V-0
 3. FINISH: ELECTRO-TIN PLATED
 4. CONTINUOUS OPERATING TEMPERATURE:
-40 ° F (-40 ° C) TO 220 ° F (105 ° C)
 5. VOLTAGE RATING: 600 V

SPC Part Number	Wire Range (AWG)	Maximum Insulation Diameter	B	L	C	Insulating Material	Color	Seam
CCS-TV-1010	12 ~ 10	.250	.135	1.00	.25	Vinyl (PVC)	Yellow	Butted
CCS-TV-1414	16 ~ 14	.170	.090	1.00	.25		Blue	
CCS-TV-1818	22 ~ 18	.145	.070	1.02	.25		Red	
CCS-ZV-0808	8	.385	.175	1.40	.38		Red	Brazed
CCS-ZV-1010	12 ~ 10	.250	.142	1.26	.38		Yellow	
CCS-ZV-1414	16 ~ 14	.170	.095	1.12	.031		Blue	Seamless
CCS-ZV-1818	22 ~ 18	.145	.062	1.06	.031		Red	



ES918



LR2190M6

OSHA
Acceptable



SPC TECHNOLOGY

Vinyl Insulated Butt Connectors

DISCLAIMER				DRAWING TITLE:			
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.				Vinyl Insulated Butt Connectors			
Tolerances: Unless Otherwise Specified:		DRAWN BY:	DATE:	SIZE		ELECTRONIC FILE	
.X = ±.015		JC	3/4/91	DWG. NO.		REV	
.XX = ±.010		CHECKED BY:	DATE:	TA-442		TA-442.dwg	
.XXX = ±.005		JOHN COLE	11/21/91	A		B	
		APPROVED BY:	DATE:	SCALE: NTS		SHEET: 1 OF 1	
		John Liska	11/21/91	U.O.M.: INCHES [mm]			