


MALE PCB PINS

SOLDER TERMINALS VARIOUS TYPES

2709

2709-X-07-XX-00-00-07-0

Swage mount in .116 hole




Basic Part Number	Board Thickness	Length V	Length A
2709-2	.062	.109	.281
2709-3	.094	.141	.250

8602

8602-1-00-XX-00-00-07-0


Square press-fit in .032 plated through-hole



2115

2115-2-00-XX-00-00-07-0


Swage mount in .043 hole
For a .062 thick board



2326

2326-2-00-XX-00-00-07-0


Swage mount in .055 hole
For a .062 thick board



8831

8831-0-00-XX-00-00-03-0


Press-fit in .057 mounting hole



8835

8835-0-00-XX-00-00-03-0


Press-fit in .057 mounting hole



8836

8836-0-00-XX-00-00-03-0

Press-fit in .075 mounting hole



SPECIFICATIONS:

Pin Material: Brass Alloy 360, 1/2 Hard
(Swage pins are annealed)

Dimensions: Inches

Tolerances On: Lengths: $\pm .005$
Diameters: $\pm .002$
Angles: $\pm 2^\circ$



ORDER CODE: XXXX - X - XX - XX - 00 - 00 - XX - 0

BASIC PART #

SPECIFY PIN FINISH:

- 01 200 μ " TIN/LEAD OVER NICKEL
- ◆ 80 200 μ " TIN OVER NICKEL (RoHS)
- ◆ 44 300 μ " SILVER OVER COPPER (RoHS)
- 50 300 μ " ELECTRO-SOLDER (60/40 SnPb)



Mill-Max Mfg. Corp. • 190 Pine Hollow Road, P.O. Box 300, Oyster Bay, NY 11771 • 516-922-6000 • Fax: 516-922-9253 • www.mill-max.com