



NOTES.

1. MATERIAL : BRASS
2. FINISHES : SEE TABLE
0.8~1.8 μ m TIN PLATING
OVERALL 0.3~0.8 μ m COPPER PLATING
3. PRODUCT SPECIFICATION : PS-35711-001, PS-35112-001
4. MATES WITH : SEE TABLE
5. APPLICABLE WIRE RANGE : AWG #22~#20

MATERIAL NO.	ENG NO.	FINISH	MATING TAB
357110600	35711-0600	UNPLATED	0.5 mm
357110610	35711-0610	ⓈPRE-TIN PLATED	
357110601	35711-0601	UNPLATED	0.45 mm
357110611	35711-0611	ⓈPRE-TIN PLATED	

REVISED EC NO: KOR2009-0111 DRWN: JHPARK01 2009/01/30 CHKD: WY. YANG 2009/01/30 APPR: YUNSIKKIM 2009/01/30	DESCRIPTION	QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 8:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION		
				mm	INCH	DRAWN BY WY. YANG	DATE 1993/04/15	TITLE .110 SLIP-IN RECEPTACLE			
		4 PLACES	± ---	± ---	CHECKED BY BK. CHOI	DATE 1993/04/15					
		3 PLACES	± ---	± ---	APPROVED BY CW. LEE	DATE 1993/04/15	 MOLEX INCORPORATED				
		2 PLACES	± ---	± ---	MATERIAL NO. SEE TABLE				DOCUMENT NO. SD-35711-060	SHEET NO. 1 OF 01	
		1 PLACE	± 0.30	± ---	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION				
		ANGULAR ± ---°									
		REV									