




LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
FT	0		B6	REVISED PER ECO-12-009418	17MAY2012	KH	MS

1. MATERIAL AND FINISH
HOUSING: HIGH TEMPERATURE POLYAMIDE, UL 94V-O RATED,
COLOR: BLACK
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.
2. SUITABLE FOR 1.6-2.4mm PC BOARD THICKNESS
3. END-TO-END STACKABLE WITHOUT LOSS OF CENTERLINE SPACING.
4. WIRE SIZE RANGE: 16-30 AWG.
5. RECOGNIZED UNDER THE COMPONENT PROGRAM OF UNDERWRITERS LABORATORIES IN.. FILE NO. E60677.
6. IMQ CERTIFICATE WITH SURVEILLANCE IN CONFORMITY WITH IEC 998-1/998-2-1.
7. PERMANENT INK MARKING, WHITE.

15.24 ⁺⁰ _{-0.22}	3	2-1776119-1
15.24 ⁺⁰ _{-0.22}	3	2-1776119-0
30.48 ⁺⁰ _{-0.45}	6	1776119-6
25.40 ⁺⁰ _{-0.38}	5	1776119-5
20.32 ⁺⁰ _{-0.30}	4	1776119-4
15.24 ⁺⁰ _{-0.22}	3	1776119-3
10.16 ⁺⁰ _{-0.16}	2	1776119-2
A	NO OF POSN	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN S. WELDON 19NOV2008	STE TE Connectivity			
DIMENSIONS: mm		CHK C. RICHARD 19NOV2008				
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD C. RICHARD 19NOV2008	NAME			
0 PLC ±.2		PRODUCT SPEC	TERMINAL BLOCK ASSEMBLY, PCB MOUNT, STACKING, SIDE WIRE ENTRY, 5.08mm PITCH			
1 PLC ±.15		APPLICATION SPEC	SIZE			
2 PLC ±0.000		WEIGHT	A200779C-1776119			
3 PLC ±0.0000		CUSTOMER DRAWING	SCALE 4:1			
4 PLC ANGLES ±2°			SHEET 1 OF 1			
MATERIAL FINISH			REV B6			